



Technical Data Sheet

3M™ Scotch-Weld™ Pipe Sealant Anaerobic Adhesive PS67



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Scotch-Weld™ Pipe Sealant Anaerobic Adhesives are one-component anaerobic sealants that cure and seal hydraulic and pneumatic pipes and fittings to withstand high temperatures and pressures

Product Features

3M™ Scotch-Weld™ Stainless Steel High Temperature Pipe Sealant PS67 is a fast cure, low breakaway torque strength, high temperature paste pipe sealant for metal connections in applications such as pressure vessels, air compressors, hydraulic, and pneumatic systems. It works on inactive surfaces (such as stainless steel) and provides an almost instant low pressure seal. A high pressure seal results when the bond is fully cured.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Uncured Physical Properties

Attribute Name	Test Method	Value
Color		Off-White ¹
Chemistry		Dimethacrylate
Viscosity		150,000-400,000 cP ²
Fixture Time	ISO 10964	25min (avg time) (<15-30 min range)

¹ Colors may vary from nearly white to yellow/amber. Adhesive performance is not affected by color variation.

² Brookfield Viscometer spindle T-E at 2.5 rpm

Typical Mixed Physical Properties

Temperature: 22 °C (72 °F)

Attribute Name	Value
Time to Full Cure	24 h ¹

¹ The cure time is defined as that time required for the adhesive to achieve a minimum of 80% of the ultimate strength as measured by aluminum-aluminum OLS.

Typical Physical Properties

Attribute Name	Value
Cured Color	White
Appearance	Paste

Typical Cured Characteristics

Attribute Name	Test Condition	Value
Temperature Range	Continuous	-54 — 204 °C
Max Pipe Diameter		3 in

Typical Performance Characteristics

Attribute Name	Test Method	Value
Breakaway Torque	ISO 10964	40in-lb - typical value (20 - 45in-lb range)
Prevailing Torque		30in-lb - typical value (12 - 40in-lb range) ¹
Long Term Temperature Resistance		204 °C (400 °F) ²
Minimum Long Term Temperature Resistance		-54 °C (-65 °F) ²

¹ Reference ISO 10964. To convert to (N.m) divide (in.lb) by 8.851.

² Long Term (day, weeks)

Handling/Application Information

Directions for Use

3MTM Scotch-Weld™ Pipe Sealant Anaerobic Adhesives are not recommended for use on most plastics due to potential cracking of plastic parts. Also, they are not recommended for use in piping systems that contain pure oxygen or an oxygen-rich environment, chlorine, or strong oxidizing substances.

For Assembly:

1. Ensure parts are clean, dry and free from oil, grease and dirt. For best results, clean and dry parts with solvent or 3MTM Scotch-Weld™ Activator. (Activator can also be used on inactive surfaces or to accelerate the cure on active surfaces.) Note: Use of 3MTM Scotch-Weld™ Activator may reduce bond strength depending on substrates and gap. Testing is recommended to evaluate the effect.
2. If not sure of surface type, always use activator. Refer to Material surface Activity and Cure Speed section for more information.
3. Apply sealant onto the second and third threads (not the first thread) of the male fitting so as to avoid introducing uncured sealant into the system. (However, should uncured sealant get into the piping system, it will not cure or cause blockage and can be slushed out.) Avoid touching the metal surfaces with the bottle tip since the metal ions may react with the adhesive upon contact and eventually may clog the bottle tip.
4. Spread adhesive evenly around the male fitting.

For Assembly:

5. Assemble parts and tighten as required.
6. Allow assemblies to set for sufficient time so that handling strength or full cure will occur before further processing or testing.

For Disassembly:

1. Loosen or remove with regular hand tools.
2. If hand tools do not work due to the assembled parts being well tightened, apply localized heat (approximately 490oF / 254oC) to the nut or bolt and disassemble while parts are still hot. Use extreme caution when working with heat sources (e.g. heat gun, flames, etc.)

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) in the original, unopened packaging, out of direct sunlight. For best performance, use this product within 12 months from date of manufacture.

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M and Scotch-Weld are trademarks of 3M Company.
©3M 2024 (6/24)