



# Technical Data Sheet

## 3M™ Metal Primer 3901



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

3M™ Scotch-Weld™ Metal Primer 3901 is a primer for 3M™ Scotch-Weld™ film and liquid adhesives in those applications where it is desired to obtain improved metal and glass adhesion or improved resistance to environmental exposure with epoxy and urethane adhesives.

### Product Features

- Ensures complete wetting of film adhesive to adherend surfaces.
- Simplifies production scheduling by protecting the cleaned surfaces until the bonding operations can be completed.
- Imparts improved corrosion protection to metal.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Uncured Physical Properties

Attribute Name	Temperature	Value
Color		Red
Base		Synthetic Resin
Viscosity	27 °C (80 °F)	5 cP <sup>1</sup>
Net Weight		6.5 ± 0.2 lb/gal

<sup>1</sup> Brookfield, RVF, No. 1 spindle, 20 rpm

### Typical Physical Properties

Attribute Name	Value
Solvent Resistance	Methyl Alcohol (Contains non-photochemically reactive solvent. Consult local air quality regulations which may regulate product use.)
Flash Point	16 °C (60 °F) <sup>1</sup>

<sup>1</sup> Closed Cup

### Typical Performance Characteristics

#### Overlap Shear Strength

Temperature	Substrate	Value
23 °C (73 °F)	Titanium	5,280 lb/in <sup>2</sup>
23 °C (73 °F)	Stainless Steel	6,310 lb/in <sup>2</sup>
-55 °C (-67 °F)	Titanium	6,380 lb/in <sup>2</sup>
-55 °C (-67 °F)	Stainless Steel	10,203 lb/in <sup>2</sup>
82 °C (180 °F)	Titanium	3,650 lb/in <sup>2</sup>
82 °C (180 °F)	Stainless Steel	3,600 lb/in <sup>2</sup>

## **Handling/Application Information**

### **Surface Preparation**

Suggested Cleaning Procedure for Aluminum

1. Alkaline Degrease - Oakite 164 solution (9-11 oz./gallon water) at 190°F ± 10°F (88°C ± 5°C) for 10-20 minutes.

Rinse immediately in large quantities of cold running water.

2. Optimized FPL Etch Solution (1 liter):

Material Amount

Distilled Water 700 ml plus balance of liter (see below)

Sodium Dichromate 28 to 67.3 grams

Sulfuric Acid 2 87.9 to 310.0 grams

Aluminum Chips 1.5 grams/liter of mixed solution

To prepare 1 liter of this solution, dissolve Sodium Dichromate in 700 ml of distilled water. Add sulfuric acid and mix well. Add additional distilled water to fill to 1 liter. Heat mixed solution to 66 to 71°C (150 to 160°F). Dissolve 1.5 grams of 2024 bare aluminum chips per liter of mixed solution. Gentle agitation will help aluminum dissolve in about 24 hours.

Place panels in FPL etch solution for 10 minutes at 155 ± 5°F (68 ± 2°C) for 12 to 15 minutes.

3. Rinse - Rinse panels in clear running water.

4. Dry - Air dry 15 minutes, force dry 10 minutes at 140°F (60°C) maximum.

**Note:** It is advisable to coat the freshly-cleaned surfaces with 3M™ Scotch-Weld™ Metal Primer 3901 within four (4) hours after surface preparation.

Care should be taken to avoid contaminating the cleaned aluminum by any substance which will hinder the wetting action of Scotch-Weld 3901.

Review and follow safety and precautionary recommendations from chemical supplier prior to preparing this etch solution.

### **Primer Application:**

Scotch-Weld 3901 has been successfully applied by spraying and brushing. The following spray equipment is suggested to obtain optimum results:

Spray Gun DeVilbiss JGA

Air Cap No. 78

Needle-Nozzle AV-15-FX

Line Pressure 60-80 psi (4.1-5.5 bar)

Pot Pressure 1-2 psi (.07-.14 bar)

Distance from Panel 14 ± 3 inches (36 ± 8 cm)

Primer Thickness (dry) Less than .0001 inch (2.5 micron)

(**Note:** Only a micro-molecular layer of primer is required.)

### **Primer Dry:**

The following dry cycle is suggested for 3M™ Scotch-Weld™ Metal Primer 3901:

**Air Dry:** Air dry at 75-85°F (24-33°C) for a minimum of one hour.

**Force Dry:** Circulating air oven 190°F (88°C) for 30 minutes.

Air dry cycles for periods as short as 1/2 hour have been used successfully with the force dry cycle. Humidity contributes greatly to satisfactory use of this primer. Relative humidity of 25% or lower may cause difficulties and should be thoroughly evaluated in the customer's application.

The primed surface, after cooling to ambient temperatures, is ready for adhesive bonding. The primed surface should be protected from contamination introduced by dust, fingerprints, oil, etc. Bonding should be completed within 7 days.

### **Primer Cleanup:**

Excess primer and equipment may be cleaned up with ketone-type solvents.\*

**\*Note:** When using solvents, extinguish all ignition sources, and follow the manufacturer's precautions and directions for use.

## **Application Techniques**

A thoroughly cleaned, dry, grease-free surface is essential for maximum performance. Cleaning methods which will produce a break-free water film on metal surfaces are generally satisfactory. Surface preparations should be fully evaluated with the adhesive, especially if resistance to specific environments are anticipated.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) in the original, unopened packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

## **Precautionary Information**

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M and Scotch-Weld are trademarks of 3M Company.  
© 3M 2024 (10/24)