



# Technical Data Sheet

## 3M™ Scotch-Weld™ Toughened Epoxy Adhesive LSB60NS



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

3M™ Scotch-Weld™ Toughened Epoxy Adhesive LSB60NS is a high performance, two-part, toughened epoxy adhesive offering outstanding shear adhesion and very high levels of durability with a choice of flow characteristics. This epoxy has a 90 minute worklife and is a 1:1 mix ratio. Ideal for bulk application through meter mix dispensing equipment and the manufacture of large panel products.

### Product Features

- Toughened
- High shear and peel
- 5 hour handling strength
- Flame, Smoke and Toxicity Tested
- 90 minute work life
- 1:1 mix ratio and easy mixing

**NOTE:**The following data is taken from tests conducted on limited production runs. 3M will continue to test samples from additional product runs and will issue a new data page if the test results change.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Uncured Physical Properties

Attribute Name	Temperature	Value
Color		Gray <sup>1</sup>
Base Color		White
Accelerator Color		Dark Gray
Base Resin		Epoxy
Accelerator Resin		Amine
Mix Ratio by Volume (B:A)		1:1
Mix Ratio by Weight (B:A)		1:1
Base Net Weight		10.1 lb/gal
Accelerator Net Weight		9.8 lb/gal
Base Viscosity	27 °C (80 °F)	24,000 cP <sup>2</sup>
Accelerator Viscosity	27 °C (80 °F)	97,000 cP <sup>2</sup>

<sup>1</sup> Colors may vary from nearly white to yellow/amber. Adhesive performance is not affected by color variation.

<sup>2</sup> Viscosity measured using Brookfield RTV, spindle #7, 20 RPM

### Typical Mixed Physical Properties

Attribute Name	Temperature	Value
Open Time		90 min <sup>1</sup>
Worklife	23 °C (73 °F)	90 min <sup>2</sup>
Time to Handling Strength	23 °C (73 °F)	5 h <sup>3</sup>
Time to Full Cure	23 °C (73 °F)	7 d

<sup>1</sup> Max time allowed after applying adhesive to a substrate before bond must be closed and fixed. Cure times approximate and depend on adhesive temperature. Hotmelts: The approx. bonding range of a 3.2 mm (1/8 in) bead of molten adhesive on a non-metallic surface.

<sup>2</sup> Maximum time that adhesive can remain in a static mixing nozzle and still be expelled without undue force on the applicator. Cure

times are approximate and depend on adhesive temperature.

<sup>3</sup> Minimum time required to achieve 0.3 MPa (50 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

### Typical Physical Properties

Attribute Name	Value
Cured Color	Gray

### Typical Cured Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Shore D Hardness	ASTM D2240	62

### Typical Performance Characteristics

Temperature: 23 °C (73 °F)

Substrate: Cushioned Sleeve A

Attribute Name	Test Method	Value
90° Peel Adhesion	ASTM D3330	3500 N/cm (CF/AF ) <sup>1</sup>

### Overlap Shear Strength

Temperature: 23 °C (73 °F)

Dwell Time: 7 d

Test Method: ASTM D1002, ISO 4587

Substrate	Surface Prep	Value
Aluminum	MEK/Abrade/MEK	3500 lb/in <sup>2</sup> (CF ) <sup>1</sup>
Cold Rolled Steel	MEK/Abrade/MEK	3000 lb/in <sup>2</sup> (CF/AF ) <sup>1</sup>
Galvanized Steel	MEK/Abrade/MEK	3400 lb/in <sup>2</sup> (CF/AF ) <sup>1</sup>
Polycarbonate (PC)	IPA Wipe/Abrade/IPA Wipe	400 lb/in <sup>2</sup> (AF ) <sup>1</sup>
Fiber-Reinforced Plastic	IPA Wipe/Abrade/IPA Wipe	2100 lb/in <sup>2</sup> (AF/CF ) <sup>1</sup>
FRP (Epoxy)	IPA Wipe/Abrade/IPA Wipe	2100 lb/in <sup>2</sup> (AF/CF ) <sup>1</sup>
FRP (Polyester)	IPA Wipe/Abrade/IPA Wipe	2200 lb/in <sup>2</sup> (SF ) <sup>1</sup>

<sup>1</sup> 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)

Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber.

Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)

Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

### Bell Peel

Substrate: Etched Aluminum

Test Method: ASTM D3167

Dwell Time	Temperature	Value
	-55 °C (-67 °F)	3.2 lb/in width (CF ) <sup>1</sup>
	23 °C (73 °F)	11.6 lb/in width (AF/CF ) <sup>1</sup>
4 h	82 °C (180 °F)	11 lb/in width (AF ) <sup>1</sup>

<sup>1</sup> 25 mm (1 in) wide bonds. 0.5 mm (0.02 in) thick, 1.7 mm (0.065 in) bondline  
Jaw separation rate 15 mm/min (6 in/min)

AF: adhesive failure CF: cohesive failure SF: substrate failure

## **Handling/Application Information**

### **Directions for Use**

1. For highest strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. The amount of surface preparation depends on the required bond strength, environmental aging resistance desired by user. For suggested surface preparations on common substrates, see the section on surface preparation.
2. Mix thoroughly by weight or volume in the proportions specified on the product label or in the typical uncured properties section. Mix approximately 15 seconds after a uniform color is obtained.
3. For maximum bond strength, apply adhesive evenly to both surfaces to be joined.
4. Application to the substrates should be made within 60-90 minutes. Larger quantities and/or higher temperatures will reduce this working time.
5. Join the adhesive coated surfaces and allow to cure at 60oF (16oC) or above until completely firm. Heat up to 120oF - 150oF (49oC - 66oC) will speed curing.
6. Keep parts from moving during cure. Apply contact pressure if necessary. Maximum shear strength is obtained with a 3-5 mil bond line.
7. Excess uncured adhesive can be cleaned up with ketone type solvents\*.

\*Note: when using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

### **Surface Preparation**

3M™ Scotch-Weld™ Toughened Epoxy Adhesives LSB60 and LSB60NS is designed to be used on plastic or metal surfaces. For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. The amount of surface preparation depends on the required bond strength, environmental aging resistance desired by the user. The following cleaning methods are suggested for common surfaces:

#### **Steel:**

1. Wipe free of dust with oil-free solvent such as acetone or isopropyl alcohol solvents\*.
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with solvent to remove loose particles\*.
4. If a primer is used, it should be applied within 4 hours after surface preparation.

#### **Aluminum:**

1. Wipe free of dust with oil-free solvent such as acetone or isopropyl alcohol solvents\*.
2. Sandblast or abrade using clean fine grit abrasives
3. Wipe again with oil-free solvent such as acetone or isopropyl alcohol solvents\*

#### **Plastics/Rubber:**

1. Wipe with isopropyl alcohol\*.
2. Abrade using fine grit abrasives.
3. Wipe with isopropyl alcohol\*

#### **Glass:**

1. Solvent wipe surface using acetone or MEK\*.
2. Apply a thin coating (0.0001 in. or less) of 3M™ Scotch-Weld™ Metal Primer EC3901 to the glass surfaces to be bonded and allow the primer to dry before bonding.

\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

## **Industry Specifications**

[NFPA 130 test report for details \(ASTM E1354\)](#)

[NFPA 130 test report for details \(ASTM E162, ASTM E662, SMP 800-C, BSS 7239\)](#)

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 12 months from date of manufacture.

## **Precautionary Information**

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **For Additional Information**

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit [www.3M.com/structuraladhesives](http://www.3M.com/structuraladhesives).

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M, Scotch-Weld and EPX are trademarks of 3M Company.  
©3M 2024 (9/24)