



Technical Data Sheet

3M™ Scotch-Weld™ Epoxy Adhesive DP100 Plus Clear



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Scotch-Weld™ Epoxy Adhesive DP100 Plus Clear is a flexible, fast setting, two-part, 1:1 mix ratio mercaptan-cured epoxy adhesive. It is unique among fast setting mercaptan cure epoxies in that it combines high shear strength with good peel performance properties. Scotch-Weld epoxy adhesive DP100 Plus Clear is clear when cured. Available in bulk containers as 3M™ Scotch-Weld™ Epoxy Adhesive DP100 Plus B/A Clear.

Product Features

- 2-5 minute worklife
- High shear and peel strength
- Flexible
- 1:1 mix ratio
- Recognized as meeting UL 94 HB

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Uncured Physical Properties

Attribute Name	Value
Color	Clear ¹
Mix Ratio by Volume (B:A)	1:1

¹ Colors may vary from nearly white to yellow/amber. Adhesive performance is not affected by color variation.

Attribute Name	Test Method	Temperature	Value
Base Color			Clear
Accelerator Color			Clear
Base Resin			Epoxy
Accelerator Resin			Mercaptan
Base Net Weight			1.16 – 1.19 g/cm ³ (9.65 – 9.9 lb/gal)
Accelerator Net Weight			1.13 – 1.17 g/cm ³ (9.4 – 9.8 lb/gal)
Base Density			1.13 – 1.17 g/cm ³ (9.4 – 9.8 lb/gal)
Accelerator Density			1.16 – 1.19 g/cm ³ (9.65 – 9.9 lb/gal)
Base Viscosity	3M C1d	27 °C (80 °F)	4000 – 11000 cP ¹
Accelerator Viscosity	3M C1d	27 °C (80 °F)	7000 – 13000 cP ¹

¹ Procedure involves Brookfield RVF, #7 spindle, 20 rpm. Measurement taken after 1 minute rotation.

Typical Mixed Physical Properties

Attribute Name	Test Method	Temperature	Value
Viscosity			9,662 cP
Worklife, 20g mixed	3M C3180	23 °C (73 °F)	2 - 5 min ¹
Set Time (min)		23 °C (73 °F)	15 min ²
Time to Structural Strength		23 °C (73 °F)	5 h ³

¹ Procedure involves periodically measuring a 20 gram mixed mass for self leveling and wetting properties. This time will also approximate the usable worklife in an 3M™ EPX™ Applicator mixing nozzle.

² Minimum time required to achieve 0.3 MPa (50 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

³ Minimum time required to achieve 6.9 MPa (1,000 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

Typical Cured Characteristics

Dwell Time: 7 d

Attribute Name	Test Method	Temperature	Value
Young's Modulus	ASTM D638, ISO 527	23 °C (73 °F)	10.413 MPa (1510 lb/in ²) ¹
Shore D Hardness	ASTM D2240	23 °C (73 °F)	64
Poisson's Ratio	ASTM D638, ISO 527		0.39 ¹
Peak Stress	ASTM D638, ISO 527	23 °C (73 °F)	5.04 MPa (731 lb/in ²) ²
Elongation at Break	ASTM D638, ISO 527		68 % ²

¹ Tested in accordance with ASTM D638 test method, Type IV dogbone. Jaw separation 5 mm/min at a strain range between 0.1 and 1.0%. Sample removed from a dry condition and tested after equilibration at 25 °C / 50%RH for 40 hrs.

² Tested in accordance with ASTM D638 test method, Type IV dogbone. Jaw separation 102 mm/min. Sample removed from a dry condition and tested after equilibration at 25 °C / 50%RH for 40 hrs.

Typical Performance Characteristics

Overlap Shear Strength

Temperature: 23 °C (73 °F)

Dwell Time: 7 d

Test Method: ASTM D1002, ISO 4587

Test Condition	Substrate	Surface Prep	Value
	Aluminum	Sandblasted	11.3 MPa (1638 lb/in ²) ¹
	CRS	Acetone/Abrade/Acetone	7.8 MPa (1125 lb/in ²) ¹
	ABS	IPA Wipe	1.4 MPa (203 lb/in ²) ¹
	Polycarbonate (PC)	IPA Wipe	2.7 MPa (395 lb/in ²) ¹
	Acrylic (PMMA)	IPA Wipe	1.7 MPa (241 lb/in ²) ¹
	FRP (Epoxy)	Acetone/Abrade/Acetone	7.2 MPa (1049 lb/in ²) ¹
	FRP (Polyester)	Acetone/Abrade/Acetone	3.2 MPa (466 lb/in ²) ¹
-40 °F	Aluminum	Sandblasted	7.7 MPa (1116 lb/in ²) ²
49 °C (120 °F)	Aluminum	Sandblasted	1.5 MPa (214 lb/in ²) ²
82 °C (180 °F)	Aluminum	Sandblasted	1.1 MPa (160 lb/in ²) ²
200 °C (392°F)	Aluminum	Sandblasted	0.8 MPa (110 lb/in ²) ²

¹ 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)

Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber.
Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)
Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

² Overlap shear (OLS) strengths were measured on 25 mm wide x 13 mm overlap (1 x 0.5 in) specimens on 25 x 102 x 1.5 mm (1 x 4 x 0.06 in) substrates.

Jaw separation 2.5 mm/min (0.1 in/min). 0.25 mm (10 mil) bondline.

Substrate: Aluminum
 Surface Prep: Sandblasted
 Temperature: 23 °C (73 °F)
 Dwell Time: 7 d

Attribute Name	Test Method	Value
Bell Peel	DIN EN 1464	6.59 N/cm (3.76 lb/in width)

Attribute Name	Value
Additional Test notes	The following product performance data was obtained in the 3M laboratory under the conditions specified. The following data show typical results obtained with 3M™ Scotch-Weld™ Epoxy Adhesive DP100 Plus Clear when applied to properly prepared substrates, cured, and tested according to the specifications indicated. This data was generated using the 3M™ EPX™ Applicator System equipped with an EPX static mixer, according to manufacturer's directions. Thorough hand mixing should afford comparable results.

Typical Environmental Performance

Overlap Shear Strength

Substrate: Aluminum
 Surface Prep: Sandblasted
 Temperature: 23 °C (73 °F)
 Dwell Time: 7 d
 Test Method: ASTM D1002, ISO 4587

Environmental Condition	Value
85 °C + 85%RH: 500 hrs	5.8 MPa (840 lb/in ²) ¹
Salt water (5% wt in water): 500 hrs	13.6 MPa (1976 lb/in ²) ¹
Diesel Fuel: 500 hrs	14.6 MPa (2124 lb/in ²) ¹
Gasoline: 500 hrs	12.1 MPa (1757 lb/in ²) ¹
Water: 500 hrs	11.5 MPa (1663 lb/in ²) ¹
49 °C + 80%RH on PVC	4.6 MPa (660 lb/in ²) ¹

¹ 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)
 Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber.
 Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)
 Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

Electrical and Thermal Properties

Temperature: 40 °C (104 °F)

Attribute Name	Test Method	Value
Thermal Conductivity	ASTM E1530	0.198 W/m/K

Handling/Application Information

Directions for Use

1. For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation depends on the required bond strength and the environmental aging resistance desired by user. For specific surface preparations on common substrates, see the section on surface preparation.
2. Use gloves to minimize skin contact. Do not use solvents for cleaning hands.

3. Mixing

For Duo-Pak Cartridges

3M™ Scotch-Weld™ Epoxy Adhesive DP100 Plus Clear is supplied in a dual syringe plastic duo-pak cartridge as part of the 3M™ EPX™ Applicator System. To use, simply insert the duo-pak cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Next, remove the duo-pak cartridge cap and expel a small amount of adhesive to ensure both sides of the duo-pak cartridge are flowing evenly and freely. If automatic mixing of Part A and Part B is desired, attach the EPX applicator mixing nozzle to the duo-pak cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after uniform color is obtained.

For Bulk Containers

Mix thoroughly by weight or volume in the proportions specified in the typical uncured properties section. Mix approximately 15 seconds after uniform color is obtained.

4. For maximum bond strength, apply adhesive evenly to both surfaces to be joined.
5. Application to the substrates should be made within 3 minutes. Larger quantities and/or higher temperatures will reduce this working time.
6. Join the adhesive coated surfaces and allow to cure at 60°F (16°C) or above until completely firm. Heat up to 200°F (93°C), in order to speed curing. These products will cure in 48 hours @ 75°F (24°C).
7. Keep parts from moving during cure. Contact pressure necessary. Maximum shear strength is obtained with a 3-5 mil bond line.

8. Excess uncured adhesive can be cleaned up with methyl ethyl ketone (MEK).*

Adhesive Coverage:A 0.005 in thick bond line will yield a coverage of 320 sqft/gallon.

*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow manufacturer's precautions and directions for use.

Surface Preparation

For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user.

The following cleaning methods are suggested for common surfaces:

Steel:

1. Wipe free of dust with oil-free solvent such as acetone, isopropyl or alcohol solvents.*
2. Sandblast or abrade using clean fine grit abrasives.
3. Wipe again with solvent to remove loose particles.
4. If a primer is used, it should be applied within 4 hours after surface preparation.

Aluminum:

1. Alkaline Degrease: Oakite 164 solution (9-11 oz./gallon water) at 190°F ± 10°F (88°C ± 5°C) for 10-20 minutes. Rinse immediately in large quantities of cold running water.
2. Acid Etch: Place panels in the following solution for 10 minutes at 150°F ± 5°F (66°C ± 2°C).

Sodium Dichromate 4.1 - 4.9 oz./gallon

Sulfuric Acid, 66°Be 38.5 - 41.5 oz./gallon 2024-T3 aluminum (dissolved) 0.2 oz./gallon minimum

Tap water as needed to balance

3. Rinse: Rinse panels in clear running tap water.
4. Dry: Air dry 15 minutes; force dry 10 minutes at 190°F ± 10°F (88°C ± 5°C).
5. If primer is to be used, it should be applied within 4 hours after surface preparation.

Note:Read and follow component supplier's environmental health and safety information prior to preparing this etch solution.

Plastics/Rubber:

1. Wipe with isopropyl alcohol.*
2. Abrade using fine grit abrasives.
3. Wipe with isopropyl alcohol.*

Glass:

1. Solvent wipe surface using acetone or MEK.*

***Note:**When using solvents, extinguish all ignition sources, including pilot lights, and follow manufacturer's precautions and directions for use.

Application Equipment

For small or intermittent applications, the 3M™ EPX™ Applicator is a convenient method of application.

For larger applications, these products may be applied by use of flow equipment.

Two-part meter/mixing/dispensing equipment is available for intermittent or production line use. These systems may be desirable because of their variable shot size and flow rate characteristics and are adaptable to many applications.

Industry Specifications

UL 94 HB

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) in the original, unopened packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M and Scotch-Weld are trademarks of 3M Company.
©3M 2024 (9/24)