



Technical Data Sheet

3M™ Adhesive Transfer Tape 9774WL+



[Product Details](#)

Product Description

3M™ Adhesive Transfer Tape 9774WL+ with 3M™ Adhesive 300MP+ is suitable for bonding to most surfaces including various fabricated foams, fabrics, and other substrates. This tape also meets the highly variable needs of most gasket fabricators.

Product Features

- Double sided acrylic adhesive designed for use on foams, plastics, wood and fabrics
- Humidity resistance
- Performs at higher temperatures

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Value
Adhesive Type	300MP+ Acrylic
Density	0.91 g/cm ³
Total Tape Thickness	0.10 mm (4 mil)

Attribute Name	Value
Liner	96# PCK
Liner Thickness	0.18 mm (7 mil)
Primary Liner Color	White
Liner Print	None

Typical Performance Characteristics

180° Peel Adhesion

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Temperature	Substrate	Value
20 min	23 °C (73 °F)	Stainless Steel	8 N/cm (75 oz/in) ¹
72 h	23 °C (73 °F)	Stainless Steel	12 N/cm (110 oz/in) ¹
72 h	23 °C (73 °F)	ABS	9 N/cm (85 oz/in) ¹
72 h	23 °C (73 °F)	Polypropylene (PP)	6 N/cm (55 oz/in) ¹
72 h	70 °C (158 °F)	Stainless Steel	5 N/cm (50 oz/in) ¹
72 h	70 °C (158 °F)	ABS	10 N/cm (88 oz/in) ¹
72 h	70 °C (158 °F)	Polypropylene (PP)	5 N/cm (50 oz/in) ¹

¹ 300 mm/min (12 in/min)

90° Peel Adhesion

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Temperature	Substrate	Value
72 h	23 °C (73 °F)	Stainless Steel	9 N/cm (85 oz/in) ¹
72 h	70 °C (158 °F)	Stainless Steel	15 N/cm (140 oz/in) ¹
72 h	23 °C (73 °F)	ABS	8 N/cm (70 oz/in) ¹
72 h	23 °C (73 °F)	Polypropylene (PP)	5 N/cm (40 oz/in) ¹
20 min	23 °C (73 °F)	Stainless Steel	7.5 N/cm (65 oz/in) ¹
72 h	70 °C (158 °F)	ABS	5 N/cm (50 oz/in) ¹
72 h	70 °C (158 °F)	Polypropylene (PP)	4 N/cm (35 oz/in) ¹

¹ 300 mm/min (12 in/min)

Static Shear

Substrate: Stainless Steel

Dwell Time: 72 h

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3654

Temperature	Test Condition	Value
23 °C (73 °F)	1000 g	10,000 min ¹
70 °C (158 °F)	500 g	10,000 min ¹
93 °C (200 °F)	1000 g	10,000 min ¹

¹ 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Shear Adhesion Failure Test - SAFT

Substrate: Stainless Steel

Dwell Time: 72 h

Backing: 2 mil Aluminum Foil

Test Method: PSTC 17

Test Condition	Value
1000 g	265 °F (200 min) ¹
500 g	250 min (310 °F) ¹

¹ 25 x 25 mm (1 in x 1 in) Area Contact

Attribute Name	Value
Short Term Temperature Resistance	121 °C (250 °F) ¹
Long Term Temperature Resistance	107 °C (225 °F) ²

¹ Maximum temperature where tape supports 200g load per 6.5cm² (1 in²) in static shear for 60 minutes.

² Maximum temperature where tape supports 200g load per 6.5cm² (1 in²) in static shear for 10,000 minutes.

Typical Environmental Performance

Temperature: 32 °C (90 °F)
Dwell Time: 72 h
Backing: 2 mil Aluminum Foil
Test Method: ASTM D3330
Environmental Condition: 90 %RH

Attribute Name	Substrate	Value
180° Peel Adhesion	Stainless Steel	15.0 N/cm (140.0) ¹
180° Peel Adhesion	ABS	9.3 N/cm (85.0) ¹
180° Peel Adhesion	Polypropylene (PP)	6.2 N/cm (57.0) ¹
90° Peel Adhesion	Stainless Steel	14 N/cm (120 oz/in) ¹
90° Peel Adhesion	ABS	6 N/cm (60 oz/in) ¹
90° Peel Adhesion	Polypropylene (PP)	5 N/cm (43 oz/in) ¹

¹ 300 mm/min (12 in/min)

Dwell Time: 1 h

Attribute Name	Test Method	Value
Fogging (Photometric method)	SAEJ1756	95 % ¹

¹ Fogging condensate on the glass plate determined by measuring the 60o specular gloss. The 60o specular gloss for the same glass plate is used as a reference value. The higher value indicates less fogging.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company.
©3M 2025 (1/25)