



## Technical Data Sheet

### 3M™ Ultra High Temperature 100 HT Adhesive Transfer Tape 9085



[Product Details](#)



[Regulatory Info/SDS](#)

#### **Product Description**

3M™ Ultra High Temperature 100HT Adhesive Transfer Tape 9085 utilizes a high performance and low outgassing adhesive system having excellent heat resistance in high temperature environments. Not only does it have excellent holding power, but also its adhesion strength is significantly higher than typical pressure sensitive tapes.

This adhesive transfer tape is ideal for use in many industrial applications subjected to higher temperature environments. Typical examples are for automotive under-hood applications that require both higher processing and operating temperatures. Other areas include printed circuit boards and heat sink bonding in many electronics applications subjected to high solder reflow temperatures.

#### **Technical Information Note**

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### **Typical Physical Properties**

Attribute Name	Test Method	Value
Color		Clear
Density		0.98 g/cm <sup>3</sup> (0.04 lb/in <sup>3</sup> )
Adhesive Type		Acrylic Adhesive System
Total Tape Thickness	ASTM D3652	0.13 mm (5 mil)
Liner		55# Densified Kraft
Liner Print		3M
Liner Thickness		0.08 mm (3.2 mil)
Primary Liner Color		White, with green “3M” print

#### **Typical Performance Characteristics**

##### **180° Peel Adhesion**

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Temperature	Value
23 °C (73 °F)	10.5 N/cm (96 oz/in) <sup>1</sup>
107 °C (225 °F)	8.8 N/cm (80 oz/in) <sup>2</sup>
149 °C (300 °F)	7 N/cm (64 oz/in) <sup>2</sup>
177 °C (350 °F)	5.3 N/cm (48 oz/in) <sup>2</sup>
230 °C (450 °F)	1.8 N/cm (16 oz/in) <sup>2</sup>

<sup>1</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

<sup>2</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

## Overlap Shear Strength

Substrate: Stainless Steel

Test Method: ASTM D1002, ISO 4587

Temperature	Value
23 °C (73 °F)	550 kPa (80 lb/in <sup>2</sup> ) <sup>1</sup>
107 °C (225 °F)	210 kPa (30 lb/in <sup>2</sup> ) <sup>2</sup>
149 °C (300 °F)	170 kPa (25 lb/in <sup>2</sup> ) <sup>2</sup>
177 °C (350 °F)	100 kPa (15 lb/in <sup>2</sup> ) <sup>2</sup>
230 °C (450 °F)	70 kPa (10 lb/in <sup>2</sup> ) <sup>2</sup>

<sup>1</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

<sup>2</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

## Static Shear

Substrate: Aluminum

Test Condition: Hold weight for 10,000 min

Test Method: ASTM D3654

Temperature	Value
23 °C (73 °F)	1,000 g <sup>1</sup>
93 °C (200 °F)	1,000 g <sup>2</sup>
121 °C (250 °F)	1,000 g <sup>2</sup>
150 °C (300 °F)	1,000 g <sup>2</sup>
175 °C (350 °F)	1,000 g <sup>2</sup>

<sup>1</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

<sup>2</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

## Normal Tensile

Substrate: Aluminum

Test Method: ASTM D897

Temperature	Value
23 °C (73 °F)	345 kPa (50 lb/in <sup>2</sup> ) <sup>1</sup>
107 °C (225 °F)	70 kPa (10 lb/in <sup>2</sup> ) <sup>2</sup>
149 °C (300 °F)	70 kPa (10 lb/in <sup>2</sup> ) <sup>2</sup>
177 °C (350 °F)	70 kPa (10 lb/in <sup>2</sup> ) <sup>2</sup>
230 °C (450 °F)	35 kPa (5 lb/in <sup>2</sup> ) <sup>2</sup>

<sup>1</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

<sup>2</sup> Adhesion performance generally increases with lower temp. At temps lower than -40°F [-40°C], the ability to absorb impact energy is reduced.

Note: Samples were conditioned at the desired temperature for two minutes before testing at that temperature.

Attribute Name	Value
Short Term Temperature Resistance	280 °C (540 °F) <sup>1</sup>
Long Term Temperature Resistance	177 °C (350 °F) <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## **Electrical and Thermal Properties**

Attribute Name	Test Method	Value
Thermal Conductivity	ASTM C177	0.16 W/m/K (1.1 (btu-in)/(h-ft <sup>2</sup> -°F))
Coefficient of Thermal Expansion		770 x 10 <sup>-6</sup> m/m/°C

Attribute Name	Test Method	Temperature	Value
Dielectric Strength	ASTM D149	23 °C (73 °F)	3,000 V
Insulation Resistance	ASTM D1000		>1 x 10 <sup>6</sup> MΩ/in <sup>2</sup>

## **Weight Loss and Outgassing Performance**

Attribute Name	Temperature	Value
Isothermal TGA Analysis	149 °C (300 °F)	0.64 % <sup>1</sup>
Isothermal TGA Analysis	177 °C (350 °F)	1.09 % <sup>1</sup>
Ramped TGA Analysis	107 °C (225 °F)	0.15 % <sup>2</sup>
Ramped TGA Analysis	149 °C (300 °F)	0.21 % <sup>2</sup>
Ramped TGA Analysis	177 °C (350 °F)	0.26 % <sup>2</sup>
Ramped TGA Analysis	230 °C (450 °F)	0.61 % <sup>2</sup>
Ramped TGA Analysis	260 °C (500 °F)	1 % <sup>2</sup>
Ramped TGA Analysis	307 °C (585 °F)	5 % <sup>2</sup>

<sup>1</sup> Testing used constant temp Thermogravimetric Analysis (TGA). TA Instruments 2950 HI-RES Modulated Thermogravimetric, air atmosphere, standard mode. Temp ramp at highest rate and maintained for 3.5hr. Results: % weight loss at desired temp.

<sup>2</sup> The testing is done using a constant temperature Thermogravimetric Analysis (TGA). TA Instruments 2950 HI-RES Modulated Thermogravimetric, air atmosphere, standard mode. Temp 70 to 1,000°F (537°C), 10°C/min. Results: % weight loss at desired temp.

## **Handling/Application Information**

### **Application Techniques**

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry, and well unified. Some typical surface cleaning solvents are isopropyl alcohol/water mixture or heptane.\*

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

\*Note: Be sure to follow the manufacturer's precautions and directions for use when using solvents.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes**

Attribute Name	Width	Value
Maximum Length	1/2 in width	54.9 m (60 yd)
Maximum Length	1/2 in to 1 in widths	110 m (120 yd)
Maximum Length	1 in to 3 in	110 m (120 yd)
Maximum Length	3 in and wider	165 m (180 yd)
Normal Slitting Tolerance		± 0.8 mm (± 1/32 in)

Attribute Name	Width	Value
Note		Subject to Minimum Order Requirements
Standard Roll Length		54.9 m (60 yd)

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M is a trademark of 3M Company.  
©3M 2025 (4/25)