



Technical Data Sheet

3M[™] Splicing Tape 469

English-US **Last Revision Date:** June, 2024

Supersedes: June, 2003





Product Details

Regulatory Info/SDS

Product Description

 $3M^{\text{TM}}$ Splicing Tapes utilize an acrylic pressure sensitive adhesive system that offers a balance of initial adhesion and good holding power.

Product Features

3M™ Splicing Tape 469 has high initial adhesion, high contact heat resistance and good adhesion to a variety of paper grades and thicknesses and is ideal for bonding a variety of similar or dissimilar materials.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Performance Characteristics

Temperature: 22 °C (72 °F)

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	5.2 N/cm (60 oz/in) ¹

^{1 12} in/min (300 mm/min)

Attribute Name	Value
Short Term Temperature Resistance	180 °C (350 °F) ¹
Long Term Temperature Resistance	94 °C (200 °F) ²

¹ Short Term (minutes, hour)

Typical Environmental Performance

Attribute Name	Value
Solvent Resistance	Medium/High
UV Resistance	Excellent

² Long Term (day, weeks)

Handling/Application Information

Application Examples

3M tape 469 is a high tack, high temperature double coated tissue tape which is light red in color for visible splices. The medium firm adhesive features good quick stick for high-speed flying splices on most grades of paper and excellent heat resistance for many high temperature drying ovens.

Application Techniques

- · Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
- To obtain optimum adhesion, the bonding surfaces must be clean, dry, and well unified.
 Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Core Size (ID)	76.2 mm (3 in)
Limitations	3M tape 469 only comes in 1/2", 3/4", 1" and 11/2" widths
Littications	with maximum length of 60 yds (54.9 m)
Maximum Available Width	50.8 mm (2 in)
Minimum Available Width	12.7 mm (1/2 in)
Normal Slitting Tolerance	± 0.8 mm (± 1/32 in)
Standard Roll Length	54.9 m (60 yd)

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/adhesives.

 $3M^{\,\text{\tiny M}}$ Industrial Adhesives and Tapes Division 3M Center, St. Paul, MN 55144-1000 3M.com/iatd

©3M 2024 (6/24)