



# Technical Data Sheet

3M™ Scotch-Weld™ Epoxy Adhesive 2216  
B/A Translucent



[Product Details](#)



[Regulatory Info/SDS](#)

## Product Description

3M™ Scotch-Weld™ Epoxy Adhesive 2216 B/A is a flexible, two-part, room temperature curing epoxy with high peel and shear strength, available in three versions. 2216 B/A Gray meets DOD-A-82720.

## Product Features

- Excellent for bonding many metals, woods, plastics, rubbers, and masonry products.
- Base and Accelerator are contrasting colors.
- Good retention of strength after environmental aging.
- Resistant to extreme shock, vibration, and flexing.
- Excellent for cryogenic bonding applications.
- Excellent for potting parts subject to thermal cycling.
- The tan NS Adhesive is non-sag for greater bond-line control.
- The translucent can be injected.
- Meets DOD-A-82720.

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Uncured Physical Properties

Attribute Name	Value
Mix Ratio by Weight (B:A)	1:1
Mix Ratio by Volume (B:A)	1:1

Attribute Name	Temperature	Value
Base Color		Translucent
Accelerator Color		Amber
Base Resin		Modified Epoxy
Accelerator Resin		Modified Amine
Base Net Weight		9.4 to 9.8 lb/gal
Accelerator Net Weight		8.0 to 8.5 lb/gal
Base Viscosity	22 °C (72 °F)	11,000-15,000 cP <sup>1</sup>
Accelerator Viscosity	22 °C (72 °F)	5,000-9,000 cP <sup>1</sup>

<sup>1</sup> Brookfield RVF #7 spindle at 20 rpm.

## Typical Mixed Physical Properties

Attribute Name	Temperature	Value
Open Time		120 min <sup>1</sup>
Time to Full Cure	66 °C (150 °F)	240 min
Time to Full Cure	93 °C (200 °F)	60 min
Worklife, 100g mixed	22 °C (72 °F)	120 min
Time to Handling Strength	22 °C (72 °F)	12 to 16 h
Time to Full Cure	22 °C (72 °F)	30 d

<sup>1</sup> Max time allowed after applying adhesive to a substrate before bond must be closed and fixed. Cure times approximate and depend

on adhesive temperature. Hotmelts: The approx. bonding range of a 1/8" bead of molten adhesive on a non-metallic surface.

### **Typical Physical Properties**

Attribute Name	Value
Cured Color	Translucent

### **Typical Cured Characteristics**

#### **Shear Modulus**

Substrate: Etched Aluminum  
 Temperature: 66 °C (150 °F)  
 Dwell Time: 2 h  
 Test Method: ASTM D1002  
 Environmental Condition: +2 psi

Test Condition	Value
@ -148°F(-100°C)	2745 MPa (398000 lb/in <sup>2</sup> )
@ -76°F(-60°C)	2199 MPa (318855 lb/in <sup>2</sup> )
@ -40°F(-40°C)	1947 MPa (282315 lb/in <sup>2</sup> )
@ 22°C (72°F)	342 MPa (49580 lb/in <sup>2</sup> )
@ 32°F(0°C)	1500 MPa (218805 lb/in <sup>2</sup> )

Temperature: 22 °C (72 °F)

Attribute Name	Test Method	Value
Shore D Hardness	ASTM D2240	42

### **Typical Performance Characteristics**

Temperature: 22 °C (72 °F)

Attribute Name	Test Method	Value
T-Peel Adhesion	ASTM D1876	25 lb/in

### **Electrical and Thermal Properties**

Attribute Name	Test Condition	Value
Coefficient of Thermal Expansion	-50°C to 0°C	81 x 10 <sup>-6</sup> m/m/°C
Coefficient of Thermal Expansion	60°C to 150°C	207 x 10 <sup>-6</sup> m/m/°C
Thermal Conductivity		0.114 (btu-ft)/(h-ft <sup>2</sup> -°F)

Temperature: 22 °C (72 °F)

Attribute Name	Test Method	Test Condition	Value
Dielectric Constant	ASTM D150	1 KHz	6.3
Dissipation Factor	ASTM D150	1 KHz	0.119
Volume Resistivity	ASTM D257		3.0 x 10 <sup>12</sup> Ω-cm

### **Handling/Application Information**

#### **Directions for Use**

1. For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user. For suggested surface preparations of common substrates, see the following section on surface preparation.
2. These products consist of two parts. Mix thoroughly by weight or volume in the proportions specified on the product label and in the uncured properties section. Mix approximately 15 seconds after a uniform color is obtained.

3. For maximum bond strength, apply product evenly to both surfaces to be joined.
  4. Application to the substrates should be made within 90 minutes. Larger quantities and/or higher temperatures will reduce this working time.
  5. Join the adhesive coated surfaces and allow to cure at 60°F (16°C) or above until firm. Heat, up to 200°F (93°C), will speed curing.
  6. Keep parts from moving until handling strength is reached. Contact pressure is necessary. Maximum shear strength is obtained with a 3-5 mil bond line. Maximum peel strength is obtained with a 17-25 mil bond line.
  7. Excess uncured adhesive can be cleaned up with ketone type solvents.\* Adhesive Coverage: A 0.005 in thick bondline will typically yield a coverage of 320 sq. ft/gallon
- \*When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use. Use solvents in accordance with local regulations.

### Surface Preparation

For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user.

The following cleaning methods are suggested for common surfaces.

Steel or Aluminum (Mechanical Abrasion)

1. Wipe free of dust with oil-free solvent such as acetone or alcohol solvents.
2. Sandblast or abrade using clean fine grit abrasives (180 grit or finer).
3. Wipe again with solvents to remove loose particles.
4. If a primer is used, it should be applied within 4 hours after surface preparation.

Aluminum (Chemical Etch)

Aluminum alloys may be chemically cleaned and etched as per ASTM D 2651. This procedure states to:

1. Alkaline Degrease - Oakite 164 solution (9-11 oz/gal of water) at 190°F ± 10°F (88°C ± 5°C) for 10-20 minutes. Rinse immediately in large quantities of cold running water.
2. Optimized FPL Etch Solution (1 liter):

Material Amount

Distilled Water 700 ml plus balance of liter (see below)

Sodium Dichromate 28 to 67.3 grams

Sulfuric Acid 287.9 to 310.0 grams

Aluminum Chips 1.5 grams/liter of mixed solution

To prepare 1 liter of this solution, dissolve sodium dichromate in 700 ml of distilled water. Add sulfuric acid and mix well. Add additional distilled water to fill to 1 liter. Heat mixed solution to 66 to 71°C (150 to 160°F). Dissolve 1.5 grams of 2024 bare aluminum chips per liter of mixed solution. Gentle agitation will help aluminum dissolve in about 24 hours. To etch aluminum panels, place them in FPL etch solution heated to 66 to 71°C (150 to 160°F). Panels should soak for 12 to 15 minutes.

3. Rinse: Rinse panels in clear running tap water.
4. Dry: Air dry 15 minutes; force dry 10 minutes (minimum) at 140°F (60°C) maximum.
5. If primer is to be used, it should be applied within 4 hours after surface preparation.

Plastics/Rubber

1. Wipe with isopropyl alcohol.
2. Abrade using fine grit abrasives (180 grit or finer).
3. Wipe with isopropyl alcohol.

Glass

1. Solvent wipe surface using acetone or MEK.
2. Apply a thin coating (0.0001 in. or less) of 3M™ Scotch-Weld™ Structural Adhesive Primer EC-3901 to the glass surfaces to be bonded and allow the primer to dry a minimum of 30 minutes @ 75°F (24°C) before bonding.

**Note:** When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use. Use solvents in accordance with local regulations.

### Application Techniques

These products may be applied by spatula, trowel or flow equipment. Two-part mixing/proportioning/dispensing equipment is available for intermittent or production line use. These systems are ideal because of their variable shot size and flow rate characteristics and are adaptable to many applications.

### Industry Specifications

UL 94 HB  
DOD-A-82720

### Storage and Shelf Life

Store products at 60-80°F (16-27°C) for maximum storage life.

When stored at the recommended temperatures in the original, unopened containers, the shelf life is 24 months from date of manufacture from 3M.

## **Precautionary Information**

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

## **Automotive Disclaimer**

**Select Automotive Applications:** This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M  
Industrial Adhesives and Tapes Division  
3M Center, Building 225-35-06  
St. Paul, MN 55144-1000  
800-362-3550

3M and Scotch-Weld are trademarks of 3M Company.  
© 3M 2022 (5/22)