



Technical Data Sheet

3M™ Scotch® ATG Tape 926



Additional Info



Regulatory
Info/SDS

Product Description

3M™ Scotch® ATG 926 with 3M™ Adhesive 350 is a reverse wound version of standard 3M Adhesive Transfer Tape 9485PC for use in the Scotch® ATG hand-held dispensers. It is a modified acrylic adhesive ideal for very high-bond strength to many surfaces. It offers excellent shear and peel resistance even at elevated temperatures. This tape is reinforced with discrete glass fibers, which limits elongation, provides structure and is important for roll stability in narrow widths and resists edge oozing. 926 is designed for temperature exposure to 177°C (350°F) for short periods of time and up to 149 °C (300°F) over long time frames.

Product Features

- A quick & controlled method of applying Scotch® ATG adhesive transfer tapes while simultaneously rewinding the liner into the applicator.
- Intended for metal, high surface energy and low surface energy plastics.
- Designed for chemical resistance and shear and peel strength even at elevated temperatures.
- Reinforced with (or contains) discrete glass fibers, which limits elongation, provide structure and is important for roll stability in narrow widths and resists edge oozing.
- Low odor for improved working environment.
- Available in non-ATG format as well, also using the 350 adhesive.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		350 Fibered Acrylic
Color		Clear
Total Tape Thickness	ASTM D3652	0.127 mm (5 mil)
Primary Liner Color		Tan
Liner Thickness		0.09 mm (3.5 mil)
Liner		60# Super Calendered Kraft paper

Typical Performance Characteristics

180° Peel Adhesion

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Temperature	Substrate	Value
20 min	23 °C (73 °F)	Stainless Steel	13.3 N/cm (121 oz/in) ¹
72 h	23 °C (73 °F)	Stainless Steel	14.9 N/cm (136 oz/in) ¹
72 h	23 °C (73 °F)	ABS	14.1 N/cm (129 oz/in) ¹
72 h	23 °C (73 °F)	Polypropylene (PP)	16.3 N/cm (149 oz/in) ¹
72 h	70 °C (158 °F)	Stainless Steel	19.3 N/cm (176 oz/in) ¹

¹ 300 mm/min (12 in/min)

Substrate: Stainless Steel
 Temperature: 32 °C (90 °F)
 Dwell Time: 72 h
 Backing: 2 mil Aluminum Foil
 Environmental Condition: 90 %RH

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	17.3 N/cm (158 oz/in) ¹

¹ 300 mm/min (12 in/min)

90° Peel Adhesion

Backing: 2 mil Aluminum Foil
 Test Method: ASTM D3330

Dwell Time	Temperature	Substrate	Value
20 min	23 °C (73 °F)	Stainless Steel	9.9 N/cm (90 oz/in) ¹
72 h	23 °C (73 °F)	Stainless Steel	11.0 N/cm (101 oz/in) ¹
72 h	23 °C (73 °F)	ABS	9.5 N/cm (87 oz/in) ¹
72 h	23 °C (73 °F)	Polypropylene (PP)	9.1 N/cm (83 oz/in) ¹
72 h	70 °C (158 °F)	Stainless Steel	14.4 N/cm (132 oz/in) ¹

¹ 300 mm/min (12 in/min)

Substrate: Stainless Steel
 Test Condition: 500 g
 Test Method: ASTM D3654

Attribute Name	Value
Long Term Temperature Resistance	149 °C (300 °F) ¹
Short Term Temperature Resistance	177 °C (350 °F) ²

¹ Maximum temperature where tape supports indicated load per 6.5cm² (1 in²) in static shear for 10,000 minutes.

² Maximum temperature where tape supports indicated load per 6.5cm² (1 in²) in static shear for 60 minutes.

Substrate: Stainless Steel
 Temperature: 23 °C (73 °F)
 Test Condition: 1000 g
 Dwell Time: 72 h
 Backing: 2 mil Aluminum Foil

Attribute Name	Test Method	Value
Static Shear	ASTM D3654	10,000 min ¹

¹ 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Shear Adhesion Failure Test - SAFT

Substrate: Stainless Steel
 Dwell Time: 72 h
 Backing: 2 mil Aluminum Foil
 Test Method: PSTC 17

Test Condition	Value
500 g	205 °C (401 °F) ¹
1000 g	122 °C (251 °F) ¹

¹ 25 x 25 mm (1 in x 1 in) Area Contact

Typical Environmental Performance

90° Peel Adhesion

Substrate: Stainless Steel
 Backing: 2 mil Aluminum Foil
 Test Method: ASTM D3330

Dwell Time	Temperature	Environmental Condition	Value
72 h	23 °C (73 °F)	Control	100 % ¹
1 h	23 °C (73 °F)	Isopropyl alcohol	89 % of control ¹
1 h	23 °C (73 °F)	Gasoline	75 % of control ¹
1 h	23 °C (73 °F)	Acetone	73 % of control ¹
4 h	23 °C (73 °F)	Weak Acid (pH 4)	89 % of control ¹
4 h	23 °C (73 °F)	Weak Base (pH 10)	87 % of control ¹
72 h	23 °C (73 °F)	Water	102 % of control ¹
72 h	23 °C (73 °F)	Salt Water (5% by weight)	80 % of control ¹
72 h	32 °C (90 °F)	90 %RH	106 % of control ¹
72 h	49 °C (120 °F)	Oil (10W30)	146 % of control ¹
96 h		Temperature Cycling: 4 Hours at 70 °C (158 °F). 4 Hours at -29 °C (-20 °F). 16 Hours at 23 °C (73 °F). Repeat four times	140 % of control ¹

¹ 300 mm/min (12 in/min)

Electrical and Thermal Properties

Midpoint Tg

Attribute Name	Test Method	Value
Glass Transition Temperature (Tg)	ASTM E1356	-28 °C ¹

¹ Glass Transition Temperature (Tg) determined using DSC Analyzer with a heating rate of 10 °C per minute. Second heat values given.

Handling/Application Information

Application Examples

Tape 926 is ideal for applications requiring high bond strength, high shear strength and high temperature performance. Some application ideas are:

- Nameplates on award plaques.
- Long term bonding of graphic nameplates and overlays to surfaces such as metal and low surface energy plastics in the aerospace, medical and industrial equipment, automotive, appliance and electronic markets.
- Bonding metal nameplates and rating plates in the aerospace, medical and industrial equipment, automotive, appliance and electronic markets.
- Lamination to foam for gasket application.
- Bonding folders and boxes that have a higher degree of memory.

Application Techniques

- Ideal tape application temperature range is 21°C to 38°C (70°F to 100°F). Initial tape application to surfaces at temperatures below 10°C (50°F) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory. For more specific information, contact our toll free 3M sales assistance number at 1-800-362-3550.
- For maximum bond strength, the surface should be thoroughly cleaned and dried, and well unified. Typical surface cleaning solvents are isopropyl alcohol and water (rubbing alcohol) or heptane. Consult manufacturer's Material Safety Data Sheet for proper handling and storage instructions.
- Bond strength is dependent upon the amount of adhesive-to-surface contact developed and can be improved with firm application pressure and moderate heat (for metal surfaces only), from 38°C (100°F) to 54°C (130°F), promoting intimate contact with the bonding surfaces.
- 2 mil thick tapes may generally be used for joining materials that are relatively smooth, thin and have low residual stress. For materials with a rough or textured surface, the thicker adhesive film of the 5 mil tapes would be more appropriate for evaluation.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight.
For best performance, use this product within 24 months from date of manufacture.

Available Sizes

ATG roll dimensions is limited by applicator type and product thickness. Products are available in 1/4", 1/2", 3/4", and 2" widths.

Applicators available: ATG 700, ATG 714, ATG 752C, ATG 3662

Attribute Name	Value
Core Size (ID)	25.4 mm (1 in)
Normal Slitting Tolerance	± 0.8 mm (± 1/32 in)
Maximum Length	Available in 18 yd (m), 36 yd, 60 yd (60 yd only for 2 mil)
Available Width	6.35 mm (0.25 in), 12.7 mm (0.5 in), 19.05 mm (0.75 in), 50.8 mm (2 in)

Recognition/Certification

TSCA: These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

MSDS: These products are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, these products should not present a health and safety hazard. However, use or processing of these products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

UL: This product is UL recognized under the following files:

- File QQQW2.MH17478, Polymeric Adhesive Systems, Electrical Equipment - Component, UL 746C
- File PGGU2.MH26206, Marking & Labeling System Materials - Component, UL 969
- File PGGU8.MH26206, Marking and Labeling System Materials Certified for Canada - Component, CSA-C22.2 No.

0.15.

If you require official recognition of any 350 adhesive under either UL 969 or UL 746C, please contact 3M-customer service at 1-800-362-3550.

For more information on the UL Certification, please visit the website at <http://www.3m.com/converter>, select UL Recognized Materials, and then select the specific product area.

Note: One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information

including that for OSHA, USCPSI, FDA, California Proposition 65, REAYD and RoHS, can be found at 3M.com/regs.

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/converter.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

©3M 2026 (6/26)