



Technical Data Sheet

3M™ Adhesive Transfer Tape 9466B



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Adhesive Transfer Tape 9466B is a double adhesive, double lined laminating system designed to attach bar-code labels to blood bags and pharmaceutical containers.

Product Features

- 3M™ Adhesive 300 is excellent for bonding to a variety of surfaces including plastic.
- Polypropylene film liner provides a flexible base for kiss-cutting and support of bar coded labels.
- 3M™ Adhesive 400 is excellent for bonding to glass and smooth plastic surfaces.
- Controlled release silicone coated paper liner for flatbed or rotary die-cutting of labels.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Test Condition	Value
Adhesive Type		Faceside	300 Acrylic ¹
Adhesive Type		Backside	400 Acrylic ²
Adhesive Thickness		Faceside	0.025 mm (1 mil) ¹
Adhesive Thickness		Backside	0.05 mm (2 mil) ²
Total Tape Thickness	ASTM D3652		0.267 mm (10.5 mil)
Primary Liner Type			Release Coated Paper Liner ³
Secondary Liner Type			Polypropylene Film Liner ³
Primary Liner Thickness			0.1 mm (4 mil)
Secondary Liner Thickness			0.089 mm (3.5 mil)

¹ Faceside adhesive is on the interior of the roll, exposed when unwound and liner removed.

² Backside adhesive is on the exterior of the roll, exposed when liner is removed.

³ Outer liner (paper) is the primary liner, Inner liner (Polypropylene) is secondary liner.

Typical Performance Characteristics

Attribute Name	Value
Short Term Temperature Resistance	82 °C (180 °F) ¹
Long Term Temperature Resistance	66 °C (150 °F) ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Characteristics

Humidity Resistance

High humidity has a minimal effect on adhesive performance. Bond strengths are generally unchanged after exposure to 7 days at 100°F (38°C) /100% R.H

Industry Specifications

FDA Statement

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

Storage and Shelf Life

HUMIDITY CONTROLLED STORAGE (16°C/60°F TO 27°C/80°F & 40-60% RH). Storage in a plastic bag is recommended. Product retains its performance and properties for 24 months from date of manufacture.

Automotive Disclaimer

Select Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

3M is a trademark of 3M Company.
©3M 2023 (9/23)