



# Technical Data Sheet

## 3M™ Extended Liner Tape 9925XL



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

3M™ Extended Liner Tapes have a liner that extends beyond the width of the adhesive to provide easy liner starting and removal. The liner is printed with the message, “Remove to Expose Adhesive”.

### Product Features

- The extended liner provides a dry edge on both edges of the tape for easy liner removal. Stated product widths include the dry edge of the liner.
- 3M™ Extended Liner Tape 9925XL is ideal for adhesion to paper materials but also work well on many other surfaces. Some application ideas are:
  - Pressure-sensitive edges for posters and point of purchase sales advertising.
  - Permanent mounting of novelty items, note pads, literature, posters and labels.
  - Pressure-sensitive edging on business forms.
- 3M™ Extended Liner Tape 9925XL is a double coated tape with a thin tissue carrier for permanent paper to paper bonding.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Physical Properties

Attribute Name	Test Method	Value
Color		Off-White Translucent
Adhesive Type		770 Rubber
Adhesive Carrier		Tissue
Total Tape Thickness	ASTM D3652	0.065 mm (2.5 mil)
Liner Print		Remove to Expose Adhesive
Liner		43# Densified Kraft White Paper Black Printing
Liner Thickness		0.05 mm (2 mil)

Attribute Name	Value
*Note	3M™ Adhesive 770 is a soft rubber-resin pressure sensitive adhesive system. It features high initial adhesion to a wide variety of materials.

### Typical Performance Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	6.6 N/cm (60 oz/in) <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

Attribute Name	Value
Short Term Temperature Resistance	65 °C (150 °F) <sup>1</sup>
Long Term Temperature Resistance	38 °C (100 °F) <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## **Typical Environmental Performance**

<b>Attribute Name</b>	<b>Value</b>
Solvent Resistance	Low
UV Resistance	Not recommended for direct exposure to sunlight or other sources of ultra violet light.

## **Special Considerations**

The extended liner provides a dry edge on both edges of the tape for easy liner removal. Stated product widths include the dry edge of the liner.

- Liner side adhesive: The width of the adhesive on the liner side is narrower than the liner by the amount of the cumulative dry edges.

- Exposed side adhesive: The adhesive on the exposed side is the full width of the product and liner. This helps to establish increased differential in adhesion of the exposed side vs the liner side to further aid in easy removal of the liner.

## **Handling/Application Information**

### **Application Techniques**

- Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
- To obtain optimum adhesion, the bonding surfaces must be clean, dry, and well unified. Some typical surface cleaning solvents are isopropyl alcohol and heptane.\*
- Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

\*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

## **Industry Specifications**

### **FDA Statement**

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

## **Available Sizes**

<b>Attribute Name</b>	<b>Value</b>
Available Width	12.7, 19.1, 25.4 mm (1/2, 3/4, 1 in)
Core Size (ID)	76.2 mm (3 in)
Liner Extension Width (each side)	1.6 mm (1/16 in)
Maximum Length	685 m (750 yd)
Minimum Length	685 m (750 yd)
Normal Slitting Tolerance	± 0.8 mm (± 1/32 in)

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M is a trademark of 3M Company.  
©3M 2024 (9/24)