



Technical Data Sheet

3M™ High Strength Double Coated Tape
93010LE



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

Finite Element Analysis (FEA) data is available for this product at: 3m.com/FEA

3M™ Double Coated Tapes with 3M™ High Strength Acrylic Adhesive 300LSE provides a high bond strength to most surfaces, including many low surface energy plastics such as polypropylene and powder coated paints. The acrylic adhesive also provides excellent adhesion to surfaces contaminated with oil typically used with machine parts.

Product Features

- This tape has a film carrier which can add dimensional stability to foams and other substrates and also makes it easier to handle the tape during slitting and die-cutting.
- The bond strength of 3M™ Acrylic Adhesive 300LSE increases as a function of time and temperature, and has very high initial adhesion.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

| Attribute Name | Test Method | Test Condition | Value |
|----------------------|-------------|----------------|----------------------------------|
| Adhesive Type | | | 300LSE Acrylic |
| Adhesive Carrier | | | Clear Polyester |
| Adhesive Thickness | | Faceside | 0.044 mm (1.7 mil) ¹ |
| Carrier Thickness | | | 0.012 mm (0.5 mil) |
| Adhesive Thickness | | Backside | 0.044 mm (1.7 mil) ² |
| Total Tape Thickness | ASTM D3652 | | 0.1 mm (3.9 mil) |
| Liner | | | 58# Polycoated Kraft Paper (PCK) |
| Liner Print | | | 300LSE |
| Liner Thickness | | | 0.1 mm (4 mil) |
| Primary Liner Color | | | Tan |

¹ Faceside adhesive is on the interior of the roll, exposed when unwound and liner removed.

² Backside adhesive is on the exterior of the roll, exposed when liner is removed.

Typical Performance Characteristics

180° Peel Adhesion

Temperature: 22 °C (72 °F)

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

| Dwell Time | Substrate | Value |
|------------|--------------------|------------------------------------|
| 15 min | ABS | 8.8 N/cm (80 oz/in) ¹ |
| 15 min | Polycarbonate (PC) | 12.3 N/cm (110 oz/in) ¹ |
| 15 min | Polypropylene (PP) | 10.4 N/cm (95 oz/in) ¹ |
| 15 min | Stainless Steel | 9.3 N/cm (85 oz/in) ¹ |

| Dwell Time | Substrate | Value |
|------------|--------------------|------------------------------------|
| 72 h | ABS | 12 N/cm (110 oz/in) ¹ |
| 72 h | Polycarbonate (PC) | 15.3 N/cm (140 oz/in) ¹ |
| 72 h | Polypropylene (PP) | 12 N/cm (110 oz/in) ¹ |
| 72 h | Stainless Steel | 12 N/cm (110 oz/in) ¹ |

¹ 12 in/min (300 mm/min)

Static Shear

Substrate: Stainless Steel
Dwell Time: 72 h
Backing: 2 mil Aluminum Foil
Test Method: ASTM D3654

| Temperature | Test Condition | Value |
|----------------|----------------|-------------------------|
| 22 °C (72 °F) | 1000g | >10000 min ¹ |
| 70 °C (158 °F) | 500g | 99,999 ¹ |

¹ 1 in x 1 in sample area, test terminated after 10,000 minutes

| Attribute Name | Value |
|-----------------------------------|------------------------------|
| Short Term Temperature Resistance | 149 °C (300 °F) ¹ |
| Long Term Temperature Resistance | 93 °C (200 °F) ² |

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Characteristics

Environmental Resistance

Humidity Resistance: High humidity has minimal effect on adhesive performance. No significant reduction in bond strength is observed after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

UV Resistance: When properly applied, nameplates and decorative trim parts are not adversely affected by exposure.

Water Resistance: Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

Temperature Cycling Resistance: High bond strength is maintained after cycling four times through:
4 hours at 158°F (70°C)
4 hours at -20°F (-29°C)
4 hours at 73°F (22°C)

Chemical Resistance: When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids, and alkalis.

Electrical and Thermal Properties

| Attribute Name | Value |
|-------------------|---------|
| Breakdown Voltage | 5,600 V |

Handling/Application Information

Application Examples

- Foam to powder coated painted surfaces.
- Low surface energy plastic adhesion.

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength. To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.*

*Note: Carefully read and follow the manufacturer's precautions and directions for use when using solvents. Ideal tape

application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Industry Specifications

FDA Statement

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

Storage and Shelf Life

Store in original cartons at 70°F (21°C) and 50% relative humidity. If stored under proper conditions, these products retain their performance and properties for 24 months from date of manufacture.

Available Sizes

| Attribute Name | Width | Value |
|---------------------------|--------------------|---------------------------------------|
| Core Size (ID) | | 76.2 mm (3 in) |
| Maximum Length | 1 in to 3 in | 329 m (360 yd) |
| Maximum Length | 1/2 in to 63/64 in | 164 m (180 yd) |
| Maximum Length | 3 in to 48 in | 329 m (360 yd) |
| Maximum Length | 48 in to 54 in | 329 m (360 yd) |
| Normal Slitting Tolerance | | ± 0.8 mm (± 1/32 in) |
| Note | | Subject to Minimum Order Requirements |

Automotive Disclaimer

Select Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

3M is a trademark of 3M Company.
©3M 2022 (5/22)