



Technical Data Sheet

3M™ Adhesive Transfer Tape with Plasticizer Resistant Adhesive F9465PC



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Adhesive Transfer Tape F9465PC is an acrylic pressure sensitive adhesive which has been formulated for bonding to many flexible vinyls and provide outstanding resistance to the effects of plasticizer migration from flexible vinyls.

General Information

Note: Vinyl formulations differ and plasticizer types and amounts can vary. The most common types of Plasticized Vinyl contain low molecular weight materials (plasticizers) which tend to migrate out of the vinyl. In the case of adhesive bonding, these plasticizers migrate into the adhesive which can cause softening of the adhesive and loss of bond strength over time.

• The possible effect of plasticizer migration on an adhesive bond can be predicted by accelerated aging for 5 days at elevated temperature (150°F [65°C]).

Note: Due to the variability of vinyl formulations, we strongly recommend that the user test each vinyl substrate to determine suitability of the tape for the particular application.

• Natural and synthetic rubber materials such as neoprene and EPDM are also formulated with fillers and plasticizers.

Note: 3M™ Adhesive Transfer Tape F-9465PC does not resist the effects of these particular fillers and plasticizers and is not recommended for use in bonding these materials.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		Acrylic
Total Tape Thickness	ASTM D3652	0.13 mm (5 mil)
Liner		Polycoated Paper
Liner Thickness		0.1 mm (4.2 mil)
Primary Liner Color		Tan, printed

Typical Performance Characteristics

Substrate: Stainless Steel
Temperature: 22 °C (72 °F)
Dwell Time: 72 h

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	8.1 N/cm (74 oz/in) ¹

¹ 12 in/min (300 mm/min)

Temperature: 22 °C (72 °F)
Test Condition: 500g

Attribute Name	Value
Static Shear	10,000 min ¹

¹ 1/2 in x 1 in sample area, test terminated at 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	149 °C (300 °F) ¹
Long Term Temperature Resistance	93 °C (200 °F) ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Characteristics

Environmental Resistance

Bond Build-up: The bond strength of 3M™ Plasticizer Resistant Adhesive increases as a function of time and temperature

Temperature/Heat Resistance: 3M™ Plasticizer Resistant Adhesive is usable for short periods (minutes, hours) at temperatures up to 200°F (94°C) and for intermittent longer periods (days, weeks) up to 160°F (71°C).

Lower Temperature Service Limit: -40°F (-40°C).

UV Resistance: When properly applied, parts are not adversely affected by outdoor exposure.

Handling/Application Information

Application Examples

- Attaching flexible vinyl graphics to sporting helmets
- Attaching flexible vinyl films and graphics to signs
- Attaching flexible vinyl graphics to vehicles
- Attaching flexible vinyl graphics to collectibles
- Attaching flexible vinyl tubing

Storage and Shelf Life

Store in original cartons at 70°F (21°C) and 50% relative humidity.

When stored under proper conditions, product retains its performance and properties for 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Master Width	1371.6 mm (54 in) ¹

¹ More sizes may be available. Please talk to your local 3M representative for more information.

Recognition/Certification

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements

MSDS: 3M has not prepared a MSDS for this product which is not subjected to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R.1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, this product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

Note: One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information including that for OSHA, USCPSP, FDA, California Proposition 65, READY and RoHS, can be found at 3M.com/regs.

Automotive Disclaimer

Select Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/adhesives. Address correspondence to: 3M Industrial Adhesives and Tapes Division, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-35-06
St. Paul, MN 55144-1000
800-362-3550

3M is a trademark of 3M Company.
© 3M 2015 (2/14)