



# Technical Data Sheet

## 3M™ Adhesive Transfer Tape 8132LE



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

Finite Element Analysis (FEA) data is available for this product at: [3m.com/FEA](https://3m.com/FEA)

3M™ Adhesive Transfer Tapes with 3M™ Low Surface Energy Acrylic Adhesive 300LSE provides high bond strength to most surfaces, including many low surface energy plastics such as polypropylene and powder coated paints. The acrylic adhesive also provides excellent adhesion to surfaces contaminated lightly with oil typically used with machine parts.

### Product Features

- 3M™ Adhesive 300LSE is a hi-strength acrylic adhesive that provides a very high bond strength to most surfaces.
- Excellent bond to low surface energy plastics such as polypropylene and powder coatings.
- Excellent adhesion to lightly oiled surfaces typical of machine parts.
- Thickness range of 2.3 and 3.6 mils for use on smooth, or rough surfaces.
- Extremely smooth adhesive for excellent graphics appearance.
- Polycoated kraft liner for die-cutting end tabs and waste removed nameplates on a common carrier.
- 3M™ Adhesive Transfer Tape 8132LE is double lined for selective die-cutting.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		3M High Strength Acrylic Adhesive 300LSE
Total Tape Thickness	ASTM D3652	0.058 mm (2.3 mil)
Liner Print		300LSE
Primary Liner Type		83# Polycoated Kraft <sup>1</sup>
Secondary Liner Type		58# Polycoated Kraft <sup>1</sup>
Primary Liner Thickness		0.102 mm (4 mil)
Secondary Liner Thickness		0.157 mm (6.2 mil)

<sup>1</sup> Inner liner is primary (stays with die-cut part); Outer liner is secondary (removed first)

### Typical Performance Characteristics

#### 90° Peel Adhesion

Temperature: 23 °C (73 °F)

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Substrate	Value
15 min	ABS	7.7 N/cm (70 oz/in) <sup>1</sup>
15 min	Polypropylene (PP)	7.5 N/cm (69 oz/in) <sup>1</sup>
15 min	Stainless Steel	7.8 N/cm (71 oz/in) <sup>1</sup>
72 h	ABS	8.6 N/cm (79 oz/in) <sup>1</sup>
72 h	Polypropylene (PP)	8.1 N/cm (74 oz/in) <sup>1</sup>
72 h	Stainless Steel	8.2 N/cm (75 oz/in) <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

Attribute Name	Value
Short Term Temperature Resistance	149 °C (300 °F) <sup>1</sup>
Long Term Temperature Resistance	93 °C (200 °F) <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## **Typical Environmental Characteristics**

### **Environmental Resistance**

The properties defined are based on the attachment of impervious faceplate materials (such as aluminum) to a stainless steel test surface.

**Bond Build-up:** The bond strength of 3M™ Adhesive 300LSE increased as a function of time and temperature, and has very high initial adhesion.

**Humidity Resistance:** High humidity has a minimal effect on adhesive performance. No significant reduction in bond strength is observed after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

**U.V. Resistance:** When properly applied, nameplates and decorative trim parts are not adversely affected by exposure.

**Water Resistance:** Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

**Temperature Cycling Resistance:** High bond strength is maintained after cycling four times through:  
4 hours at 158°F (70°C)  
4 hours at -20°F (-29°C)  
4 hours at 73°F (22°C)

**Chemical Resistance:** When properly applied, nameplates and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids and alkalis.

**Temperature Resistance:** 3M™ Adhesive 300LSE is usable for short periods (minutes, hours) at temperatures up to 300°F (148°C) and for intermittent longer periods of time (days, weeks) up to 200°F (93°C).

**Lower Service Temperature:** -40°F (-40°C).

## **Processing**

**Slitting and die-cutting:** This adhesive is very aggressive and may be difficult to convert depending on your application requirements. Chilling the adhesive between 35°F and 50°F will improve the processability. In addition, dies can be lubricated with evaporative stamping oil. You may also refer to our Technical Bulletin on 3M™ Adhesive 300LSE converting. (70-0707-6205-2)

**Roll Laminating:** A combination of metal and rubber rollers with moderate pressure is recommended. Note: Please refer to the Technical Bulletin on slitting. (70-0709-3905-6)

## **Handling/Application Information**

### **Application Examples**

- Plastic nameplates or graphic overlays for use on low surface energy plastics.
- Waste removed nameplates on a common sheet for ease of application.
- Attaching membrane switch assemblies to powder coated surfaces and low surface energy plastics.
- Graphic overlays with end tabs for easy liner removal.
- Graphic application to surfaces such as wood, fabric, plastic, where very high bond strength is required.
- Attaching identification material to lightly oily surfaces typical of machine parts.

### **Application Techniques**

For maximum bond strength, the surface should be thoroughly cleaned and dried. Typical cleaning solvents are methyl ethyl ketone for metals or isopropyl alcohol for plastics. Carefully read and follow manufacturer's precautions and directions for use when using cleaning solvents.

Bond strength can also be improved with firm application pressure and moderate heat, from 100°F (38°C) to 130°F (54°C), causing the adhesive to develop intimate contact with the bonding surface.

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended for most pressure-sensitive adhesives because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

## **Industry Specifications**

### **FDA Statement**

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes**

<b>Attribute Name</b>	<b>Value</b>
Core Size (ID)	152.4 mm (6 in)
Limitations	Maximum 360 yd (329 m)
Maximum Slit Width	1219 mm (48 in)
Minimum Slit Width	305 mm (12 in)
Normal Slitting Tolerance	±0.8 mm (±1/32 in)
Standard Sheet Size	24in x 36in in <sup>1</sup>

<sup>1</sup> Custom sheets are available for 3M™ Adhesive Transfer Tapes 8132LE, 8153LE

## **Recognition/Certification**

**TSCA:** These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

**MSDS:** These products are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

**Note:** One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information including that for OSHA, USCPSCI, FDA, California Proposition 65, READY and RoHS, can be found at 3M.com/regs.

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M is a trademark of 3M Company.  
©3M 2024 (9/24)