



# Technical Data Sheet

3M™ Adhesive Transfer Tape 9471FL



[Product Details](#)



[Regulatory Info/SDS](#)

## Product Description

**Finite Element Analysis (FEA)** data is available for this product at: [3m.com/FEA](https://www.3m.com/FEA)

- 3M™ High-Strength Acrylic Adhesive 300LSE provides very high bond strength to most surfaces
- Excellent bond to low surface energy plastics such as polypropylene and powder coatings.
- Excellent adhesion to lightly oiled surfaces typical of machine parts.
- Thickness of 2 mils, 3.5 mils, and 5 mils for use on smooth and textured surfaces.
- Extremely smooth adhesive for excellent graphic appearances.
- Polyester film liner is ideal for rotary die-cutting, high speed processing, automatic dispensing, and clean room environments.
- Polyester film liner resists breakage for one piece liner removal.
- Polyester film liner resists curling or wrinkling in high humidity.

## General Information

### Processing:

Slitting and die-cutting: This adhesive is very aggressive and may be difficult to convert depending on your application requirements. Chilling the adhesive between 35 and 50°F will improve the processability. In addition, dies can be lubricated with Laminoleum evaporative stamping oil, which is available from Metal Lubricants Company (708-333-8900) or with Lubri-Blade 907 from Ceramic Technologies Inc. (800-258-8495). You may also refer to our Guide to Converting 3M Laminating Adhesive 300LSE Technical Bulletin

**Roll Laminating:** A combination of metal and rubber rollers with moderate pressure (approx. 14 psi) is recommended.

**Note:** Please refer to the 3M Slitting/Die-cutting Technical Bulletin for further details.

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		3M 300LSE High Strength Acrylic Adhesive
Total Tape Thickness	ASTM D3652	0.05 mm (2 mil)
Liner		Polyester Film
Liner Thickness		0.05 mm (2 mil)

## Typical Performance Characteristics

### 90° Peel Adhesion

Temperature: 22 °C (72 °F)

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Substrate	Value
15 min	ABS	7.7 N/cm (70 oz/in) <sup>1</sup>
15 min	Polypropylene (PP)	7.5 N/cm (69 oz/in) <sup>1</sup>
15 min	Stainless Steel	7.8 N/cm (71 oz/in) <sup>1</sup>
72 h	ABS	8.6 N/cm (79 oz/in) <sup>1</sup>
72 h	Polypropylene (PP)	8.1 N/cm (74 oz/in) <sup>1</sup>
72 h	Stainless Steel	8.2 N/cm (75 oz/in) <sup>1</sup>

<sup>1</sup> 12 in/min (300 mm/min)

Attribute Name	Value
Short Term Temperature Resistance	149 °C (300 °F) <sup>1</sup>
Long Term Temperature Resistance	93 °C (200 °F) <sup>2</sup>
Minimum Long Term Temperature Resistance	-40 °C (-40 °F) <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## **Typical Environmental Characteristics**

### **Environmental Resistance**

**Bond Build-up:** The bond strength of 3MTM High-Strength Acrylic Adhesive 300LSE increases as a function of time and temperature, and has very high initial adhesion.

**Humidity Resistance** - High humidity has a minimal effect on adhesive performance. No significant reduction in bond strength is observed after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

**UV Resistance** - When properly applied, adhesive bond is not adversely affected by exposure.

**Water Resistance** - Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

**Temperature Cycling Resistance** - High bond strength is maintained after cycling four times through the following conditions:

4 hours at 158°F (70°C)

4 hours at -20°F (-29°C)

4 hours at 73°F (22°C)

**Chemical Resistance** - When properly applied, adhesive bond will hold securely after exposure to numerous chemicals including oil, mild acids and alkalis.

## **Handling/Application Information**

### **Application Examples**

- Nameplates and graphic overlays printed and die-cut by rotary processing techniques.
- Labels engineers for performance with protected graphics for environmental durability (e.g., automotive under hood labels).
- Gaskets and other die-cut parts for use on difficult to bond to surfaces.
- Graphics and die-cut parts for application to oily metals, powder coatings or low surface energy plastics.

### **Application Techniques**

For maximum bond strength the surface should be thoroughly cleaned and dried. Typical cleaning solvents are heptane or isopropyl alcohol. Carefully read and follow manufacturer's precautions and directions for use when using cleaning solvents. This cleaning recommendation may not be compliant with the rules for certain Air Quality Management Districts in California; consult applicable rules before use.

Bond strength can also be improved with firm application pressure and moderate heat, from 100°F (38°C) to 130°F (54°C) which causes the adhesive to develop improved contact with the bonding surface.

The ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended for most pressure-sensitive adhesives because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

## **Industry Specifications**

### **FDA Statement**

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

## **Storage and Shelf Life**

Product retains its performance and properties for 24 months from date of manufacture if properly stored at room temperature conditions of 72°F (22°C) and 50% relative humidity. Storage in plastic bag is recommended.

## **Available Sizes**

<b>Attribute Name</b>	<b>Width</b>	<b>Value</b>
Core Size (ID)		76.2 mm (3 in)
Maximum Length	1/2 in to 63/64 in	165 m (180 yd)
Maximum Length	1 in to 54 in	329 m (360 yd)
Maximum Slit Width		1372 mm (54 in)
Minimum Slit Width		12.7 mm (1/2 in)
Normal Slitting Tolerance		± 0.8 mm (± 1/32 in)
Note		Subject to Minimum Order Requirements

## **Recognition/Certification**

**MSDS:** 3M has not prepared an MSDS for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, these products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

**TSCA:** These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

## **Automotive Disclaimer**

**Select Automotive Applications:** This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

## **For Additional Information**

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit [www.3M.com/bonding](http://www.3M.com/bonding). Address correspondence to: 3M Engineered Adhesives Division, 3M Center, Building 220-7E-01, St. Paul, MN 55144-1000. Our fax number is 651-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

3M  
Industrial Adhesives and Tapes Division  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550

©3M 2022 (5/22)