



Technical Data Sheet

3M™ Adhesive Transfer Tape 9372W



[Regulatory Info/SDS](#)

Product Description

3M™ Adhesive Transfer Tapes are acrylic based and specially formulated to provide a permanent bond between substrates in environments requiring regulatory compliance with flame retardant standards such as Federal Aviation Regulation 25.853.

Product Features

Flame Retardant

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Off White (opaque)
Adhesive Type		Tackified Acrylic, 300FR Series
Areal Density		75 g/m ²
Net Weight		83 lb/Ream
Total Tape Thickness	ASTM D3652	0.051 mm (0.002 in) (2 mil)
Thickness Tolerance		±15 %
Liner		PCK
Liner Thickness		0.17 mm (6.5 mil)
Primary Liner Color		Tan, unprinted

Typical Performance Characteristics

Substrate: Stainless Steel
Temperature: 23 °C (73 °F)
Dwell Time: 72 h

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	12.8 N/cm (115 oz/in) ¹

¹ 304 mm/min (12 in/min)

90° Peel Adhesion

Dwell Time: 72 h
Backing: 2 mil PET
Test Method: ASTM D3330

Temperature	Substrate	Value
23 °C (73 °F)	ABS	6.8 N/cm (62 oz/in) ¹
23 °C (73 °F)	High Density Polyethylene (HDPE)	5.6 N/cm (51 oz/in) ¹
23 °C (73 °F)	Polycarbonate (PC)	6.9 N/cm (63 oz/in) ¹
23 °C (73 °F)	Polypropylene (PP)	5.3 N/cm (48 oz/in) ¹
23 °C (73 °F)	Stainless Steel	7.9 N/cm (72 oz/in) ¹

Temperature	Substrate	Value
70 °C (158 °F)	Stainless Steel	11 N/cm (98 oz/in) ¹

¹ 304 mm/min (12 in/min)

Static Shear

Test Method: ASTM D3654

Temperature	Test Condition	Value
23 °C (73 °F)	1000 g	>10,000 min ¹
70 °C (158 °F)	500 g	>10,000 min ¹

¹ 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	121 °C (250 °F) ¹
Long Term Temperature Resistance	82 °C (180 °F) ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Performance

Attribute Name	Value
Solvent Resistance	Very Good
UV Resistance	Very Good

Handling/Application Information

Application Examples

This family of products has been formulated for applications requiring flame retardancy and high bond strength to a wide variety of substrates.

These attributes and choice of three product thicknesses make the products ideally suited to applications in aerospace, maritime, electronic, automotive and building construction applications on both smooth and textured substrates.

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength. 15 psi momentary pressure is typical.

Ideal tape application temperature range is 70°F to 100°F (21°C to 37°C). Initial tape application to surface at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once applied, low temperature holding is generally satisfactory.

Surfaces should be clean and dry prior to bonding. We recommend a final surface cleaning with a mixture of 50% isopropyl alcohol* and water.

Two liner options facilitate wide array of application techniques. Densified kraft liner ideal for roll to roll lamination and subsequent rotary die cutting. Heavy caliper, layflat, polycoated kraft liner, minimizes surface asperities, minimizes distortion of pre-laminated substrates in variable humidity conditions and provide convenient backing for kiss cutting operations.

*Carefully read and follow the manufacturer's precautions and directions for use when using cleaning solvents.

Application Equipment

To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality.

To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, Lamination Techniques for Converters of Laminating Adhesives (70-0704-1430-8).

For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

Certifications/Standards

Federal Aviation Regulations, FAR 25.853

Yes

Underwriter Laboratories 94, UL-94 (V-2)

No

Industry Specifications

FAR 25.853

[EN 45545 test report details \(ISO 5659-2, ISO 9239-1, ISO 5660-1, ISO 5658-2\)](#)

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

Available Sizes

Attribute Name	Value
Core Size (ID)	76.2 mm (3 in)
Maximum Available Width	60 in
Normal Slitting Tolerance	±0.8 mm (±1/32 in)
Precision Slitting Tolerance	±0.1 mm (±0.004 in) ¹
Standard Roll Length	180 m

¹ Precision slitting is available on select products with minimum order of full web increments.

Available Sizes - Detailed

Minimum Slit Width:		1" up to 3"	1/2" up to 3"	2" up to 3"
	minimum length	60 yards	60 yards	60 yards
	maximum length	180 yards	180 yards	180 yards
3" to 30"	minimum length	60 yards	60 yards	60 yards
	maximum length	720 yards	720 yards	720 yards
31" to 48"	minimum length	—	—	60 yards
	maximum length	—	—	500 yards
31" to 60"	minimum length	60 yards	60 yards	—
	maximum length	500 yards	500 yards	—

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company.
©3M 2024 (9/24)