



# Technical Data Sheet

3M™ Adhesive Transfer Tape 9461P



[Product Details](#)

## Product Description

The 3M™ Adhesive Transfer Tapes with 3M™ High Temperature Acrylic Adhesive 100 are designed for temperature exposure to 450°F (232°C) for short periods of time and/or solvent resistance. They have exceptional shear values even at elevated temperatures. They also offer low “outgassing” properties, which is an important consideration for the aerospace, automotive and electronic industries.

## Product Features

3M™ Adhesive Transfer Tapes 941, 966, 9461P, 9461PC and 9462P use the same 3M™ High Temperature Acrylic Adhesive 100 and come with different liners for a variety of die cutting applications. 3M™ Adhesive Transfer Tape 965 uses a slightly modified 3M™ High Temperature Acrylic Adhesive 100 to provide excellent resistance to jet fuel and other chemicals for identification labels on aircraft.

- Excellent bond to metal and high surface energy plastics.
- Outstanding temperature and chemical resistance.
- Two adhesive thicknesses: 1 mil for thin profile labels and 2 mil for rougher surfaces.
- Low outgassing and low leachable chloride, important considerations for electronic and aerospace industries.
- Available on various liners for specialized processing:
  - 62# Densified Kraft for die-cutting metal nameplates
  - 55# Densified Kraft for rotary die-cutting specialty labels
  - 58# Polycoated Kraft for moisture stability

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Attribute Name	Value
Dispenser Selection	For assistance in helping you determine the best dispenser for your application, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

Attribute Name	Test Method	Value
Adhesive Type		Acrylic
Total Tape Thickness	ASTM D3652	0.03 mm (1.16 mil)
Liner		55# Densified Kraft with “3M” printed in green
Liner Thickness		0.08 mm (3.2 mil)

## Typical Performance Characteristics

## 90° Peel Adhesion

Temperature: 23 °C (73 °F)

Dwell Time: 72 h

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Substrate	Value
ABS	3.9 N/cm (36 oz/in) <sup>1</sup>
Stainless Steel	9.3 N/cm (85 oz/in) <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

Temperature: 23 °C (73 °F)

Attribute Name	Value
Liner Release	29 g/in

## Static Shear

Test Method: ASTM D3654

Temperature	Test Condition	Value
23 °C (73 °F)	2000 g	10,000 min <sup>1</sup>
70 °C (158 °F)	1000 g	10,000 min <sup>1</sup>
93 °C (200 °F)	1000 g	10,000 min <sup>1</sup>
177 °C (350 °F)	500 g	10,000 min <sup>1</sup>
232 °C (450 °F)	400 g	10,000 min <sup>1</sup>

<sup>1</sup> 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	232 °C (450 °F) <sup>1</sup>
Long Term Temperature Resistance	204 °C (400 °F) <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)


Attribute Name	Value
Additional Test notes	Use on “Low Surface Energy Plastics” such as Polypropylene is not recommended. Consider other 3M™ Adhesive Transfer Tapes with 3M™ Adhesive 300, 300MP, 350 or 300LSE.

Typical Environmental Characteristics

Chemical and Environmental Exposure

The 3M™ High Temperature Acrylic Adhesive 100 is well known in industry for environmental and chemical resistance. For many applications, any one of the products in this grouping will perform satisfactorily when exposed to different chemicals or temperatures. Jet fuels, however, are a challenge for pressure sensitive products. More specifically, the Aviation Turbine Fuel, Grade JP-4 (MIL H-T-5624), will attack many of the best adhesives within 72 hours. In response to the demands of this market and the corresponding military specification MIL-T- 9906C, 3M™ Adhesive Transfer Tape 965 was developed as it differs slightly in chemistry from the rest of the 3M adhesive 100 family to provide the extra chemical resistance.

In addition to the added fuel resistance, 3M tape 965 retains all of the notable features of the adhesive 100: excellent adhesion to metals, good adhesion to high surface energy plastics, low outgassing, and excellent static shear values for room temperature and heated conditions. The chart below shows adhesion values (to stainless steel) of 3M™ Adhesive Transfer Tapes 965 and 966, with an emphasis on fuel and oil exposure. The data represents representative or typical values and should not be used for specification purposes.



## Environmental Resistance

### Bond Build-up:

The bond strength of 3M™ Adhesive 100 increases as a function of time and temperature.

### Humidity Resistance:

High humidity has a minimal effect on adhesive performance. Bond strengths are generally higher after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

### U.V. Resistance:

When properly applied, nameplates and decorative trim parts are not adversely affected by outdoor exposure.

### Water Resistance:

Immersion in water has no appreciable effect on the bond strength. After 100 hours in room temperature, the bond actually shows an increase in strength.

### Temperature Cycling Resistance:

**Bond strength generally increases after cycling four times through:**

4 hours at 158°F (70°C)

4 hours at -20°F (-29°C)

16 hours at room temperature

### Chemical Resistance:

When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including gasoline, oil, Freon™ TF, sodium chloride solution, mild acids and alkalis.

### Heat Resistance:

The 3M adhesive 100 is usable for short periods (minutes, hours) at temperatures up to 450°F (232°C) and for longer periods (days, weeks) up to 300°F (149°C).

**Low Temperature Service:** -40°F (-40°C). Parts should be tested for low temperature shock service.

## Electrical and Thermal Properties

Attribute Name	Test Method	Temperature	Test Condition	Value
Coefficient of Thermal Expansion	ASTM D696		First Heat (125 ~ 175 °C)	19.9 x 10 <sup>-5</sup> m/m/°C
Coefficient of Thermal Expansion	ASTM D696		Second Heat (25 ~ 175 °C)	58.4 x 10 <sup>-5</sup> m/m/°C
Thermal Conductivity	ASTM C518	41 °C (107 °F)		0.178 W/m/K (0.103 (btu-ft)/(h-ft <sup>2</sup> -°F))
Thermal Conductivity	ASTM C518	71 °C (160 °F)		0.183 W/m/K (0.106 (btu-ft)/(h-ft <sup>2</sup> -°F))
Thermal Conductivity	ASTM C518	101 °C (214 °F)		0.187 W/m/K (0.108 (btu-ft)/(h-ft <sup>2</sup> -°F))

Attribute Name	Test Method	Temperature	Test Condition	Value
Dielectric Constant	ASTM D150	23 °C (73 °F)	1 KHz	2.92
Dissipation Factor	ASTM D150	23 °C (73 °F)	1 KHz	0.025
Dielectric Strength	ASTM D149		500 vac, rms[60 hz/sec]	1,100 V/mil
Insulation Resistance	Mil-I-46058C		24 hr after moisture resistance	9.7 x 10 <sup>12</sup> Ω <sup>-1</sup>
Insulation Resistance	Mil-I-46058C		Cycle #10	9.4 x 10 <sup>10</sup> Ω <sup>-1</sup>
Insulation Resistance	Mil-I-46058C		Cycle #4	1.5 x 10 <sup>11</sup> Ω <sup>-1</sup>
Insulation Resistance	Mil-I-46058C		Before moisture resistance	>1 x 10 <sup>15</sup> Ω <sup>-1</sup>
Surface Resistivity				>1 x 10 <sup>15</sup> Ω
Volume Resistivity	ASTM D257	23 °C (73 °F)		4 x 10 <sup>15</sup> Ω-cm

<sup>1</sup> test voltage = 100 VDC

## **Handling/Application Information**

### **Application Examples**

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C) and application to surfaces at temperatures below 50°F (10°C) is not recommended for most pressure sensitive adhesives because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is satisfactory. For more specific information, contact Customer Service at 1-800-223-7427.

The liner used for 3M™ Adhesive Transfer Tapes 9461P, 9461PC and 9462P is not intended to provide premium release characteristics. Testing is urged for applications where liner release is critical. These products are not recommended for use with non-transferable facestocks such as 3M™ Label Material 8070, 8071 or 8074 because of the potential for liner caused pre-destruct.

3M™ Adhesive Transfer Tape 965 has been specially modified to provide outstanding performance for fuel line identification labels, bar code labels for harsh environments and specially performance-engineered labels for automotive, aerospace and industrial markets. It also meets MIL-T-9906C specification requirements.

### **Application Techniques**

For maximum bond strength the surface should be thoroughly cleaned and dried. Typical cleaning solvents are heptane or isopropyl alcohol.\*

Bond strength can also be improved with firm application pressure and moderate heat, from 100°F (38°C) to 130°F (54°C), causing the adhesive to develop intimate contact with the bonding surface.

\*Note: Carefully read and follow the manufacturer's precautions and directions for use when working with solvents. These cleaning recommendations may not be compliant with the rules of certain Air Quality Management Districts in California; consult applicable rules before use.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in a sealed plastic bag, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes**

Attribute Name	Value
Core Size (ID)	76.2 mm (3 in)
Maximum Available Width	48 in
Minimum Available Width	1 in
Standard Roll Length	180 yd

## **Recognition/Certification**

**TSCA:** These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements. Additional regulatory information for IATD products is available on the regs website: [www.3m.com/regs](http://www.3m.com/regs).

**MSDS:** 3M has not prepared a MSDS for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

**UL:** 3M™ Adhesive Transfer Tapes 941, 966 and 9462P have been recognized by Underwriters Laboratories Inc. under Standard UL 969 Marking and Labeling in File MH26206. For more information on the UL Certification, please visit the website at <http://www.3m.com/converter>, select UL Recognized Materials, and then select the specific product area.

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M is a trademark of 3M Company.  
©3M 2024 (9/24)