



Technical Data Sheet

3M™ Lead Foil Tape 420 (Linered)



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Lead Foil Tape 420 is backed with a rubber adhesive, offering excellent conformability in a variety of application conditions.

Product Features

- Very good conformability.
- Good thermal properties and will perform over a wide variety of temperature conditions (-60° to 225°F or -54° to 106°C). It has been used at higher temperatures for shorter duration.
- Electrically and thermally conductive.
- Can be die-cut into specific shapes.
- This material when disposed of separately is classified as RCRA hazardous waste. Please consult applicable Federal, State and local regulations for proper disposal.
- Elevated lead levels in water may result from long term submersion of this product.
- Best results are obtained when applied to a clean dry surface above 32°F (0°C). Also, by “feathering” the edges - rubbing the tape down with a smooth-edged plastic piece (or similar object) - the tape can be made to better conform to the substrate. This is especially important if the tape is to be used as a “thief” in electroplating where the edges must fully contact the metal base.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Dark Silver
Adhesive Type		Rubber (green)
Approximate Weight		35.2 g/m/24 mm (0.075 lb/yd/in)
Backing		Lead Foil
Water Vapor Transmission	ASTM D3833	1.55 g/m ² /24 h (0.1 g/100 in ² /24 h)
Backing Thickness	ASTM D3652	0.13 mm (5 mil)
Total Tape Thickness	ASTM D3652	0.19 mm (7.6 mil)
Liner		White, easy-release film
Liner Thickness		0.09 mm (3.7 mil)

Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Value
180° Peel Adhesion	ASTM D3330	23 °C (73 °F)	4.9 N/cm (45 oz/in) ¹
Elongation at Break	ASTM D3759		12 %
Tensile Strength	ASTM D3759		35 N/cm (20 lb/in)
Long Term Temperature Resistance			107 °C (225 °F) ²
Minimum Long Term Temperature Resistance			-51 °C (-60 °F) ²

¹ 304 mm/min (12 in/min)

² Long Term (day, weeks)

Handling/Application Information

Application Examples

- Electroplating
- Radiation barrier
- Moisture barrier
- Chemical milling
- X-ray plate masking

Disposal and Safety Considerations

- Wear protective gloves when handling the tape as transfer of lead to the hands is possible. To ensure removal of any lead residue after use, wash hands with a soap specifically formulated to remove lead from the surface of the skin. This will minimize additional transfer of lead to other surfaces. • Lead will slowly leach into water when submerged. Leaching will accelerate as acidity increases. • This material when disposed of separately is classified as RCRA hazardous waste. Please consult applicable Federal, State and local regulations for proper disposal.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

Available Sizes

Attribute Name	Value
Standard Roll Length	33 m (36 yd)

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company.
©3M 2024 (9/24)