



Technical Data Sheet

3M™ Super Duty Duct Tape DT17



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Super Duty Duct Tape DT17 is a 17 mil duct tape with a natural rubber adhesive and water resistant polyethylene backing. It provides easy hand tear and good conformability. The thick construction makes it a great choice for seaming applications, and protecting various surfaces.

Product Features

- Aggressive natural rubber adhesive provides instant adhesion to a wide variety of surfaces including metal, glass, plastic, and sealed concrete.
- Woven cloth scrim allows the tape to tear easily by hand and provides ease of application and handling.
- Tightly woven scrim provides high tensile strength which is ideal for bundling applications.
- Thick backing offers the highest level of durability and strength. Offers abrasion resistance for the most demanding duct tape applications.
- Conformable Backing.
- Roll sides are not tacky, keeping roll cleaner on the job site.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Black
Adhesive Type		Synthetic/Natural Rubber blend
Backing		Polyethylene film over cloth scrim
Total Tape Thickness	ASTM D3652	0.42 mm (17 mil)

Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Substrate	Value
180° Peel Adhesion	ASTM D3330	23 °C (73 °F)	Stainless Steel	9.2 N/cm (85 oz/in) ¹
Elongation at Break	ASTM D3759			18 %
Tensile Strength	ASTM D3759			66 N/cm (38 lb/in)

¹ 304 mm/min (12 in/min)

Handling/Application Information

Application Examples

- Seaming and extra strength Bundling applications
- Abrasion protection
- Protection of metal parts and various surfaces against media blasting overspray

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 12 months from date of manufacture.

Available Sizes

Attribute Name	Value
Standard Roll Length	32 m (35 yd)

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iat

3M is a trademark of 3M Company.
©3M 2024 (9/24)