



Technical Data Sheet

3M™ Outdoor Masking and Stucco Tape 5959



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Outdoor Masking and Stucco Tape 5959 is designed for construction, marine and maintenance applications. It is a robust tape made with polyethylene film over a dense cloth scrim and a blend of natural and synthetic rubber adhesive. With its 90 day UV resistant waterproof backing and high shear resistant adhesive, it is an excellent choice for outdoor holding and masking applications. The unique adhesive removes cleanly from most opaque surfaces up to 90 days after application. The strong backing makes it ideal for pulling through spatter from stucco and EIFS applications.

Product Features

- Red color for good visibility. Color insures that the tape is not accidentally left on.
- High shear adhesive for reliable holding of polyethylene sheeting.
- UV resistant backing does not fade or break down outdoors for up to 90 days.
- Clean removal from most opaque surfaces up to 90 days.
- High tensile backing for pulling through tough coatings.
- Aggressive rubber adhesive grabs and adheres well to many surfaces.
- Roll sides are not tacky so the roll stays cleaner on the job site.
- Abrasion resistant backing keeps surface from being marred.
- Tested according to UL 723 / ASTM E84

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Substrate	Value
Color			Red
Adhesive Type			Natural and Synthetic rubber
Backing			Polyethylene film over cloth scrim
Total Tape Thickness	ASTM D3652		0.28 mm (11 mil)
Clean Removal and Weathering	G90 Cycle 3	Stainless Steel	90 d

Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Value
180° Peel Adhesion	ASTM D3330	23 °C (73 °F)	6.2 N/cm (57 oz/in) ¹
Elongation at Break	ASTM D3759		16 %
Tensile Strength	ASTM D3759		63 N/cm (36 lb/in)
Minimum Application Temperature			4 °C (40 °F)
Long Term Temperature Resistance			93 °C (200 °F) ²
Flame Spread Index	ASTM E84		5 ³
Smoke Developed Index	ASTM E84		0 ³

¹ 304 mm/min (12 in/min)

² Long Term (day, weeks)

³ UL-723, NFPA 255, and UBC 8-1 are publications of the same test method.

Handling/Application Information

Application Examples

- Ideal for overspray protection when masking substrates from coatings such as stucco, EIFS, gel coat, and construction coatings.
- Effective in marine applications where temporary tents are made to contain coating that is being removed or to protect coating being applied from dust and debris.
- The tough polyethylene outer layer and strong scrim backing make one piece removal of the tape possible when pulling through heavy or extra strong coating.
- Can be used on surfaces such as window and door frames to protect them from damage during construction.
- Ideal for critical abatement applications where the surface must not be damaged or marred during the removal process.
- Thick adhesive layer holds well to irregular surfaces such as sealed masonry or brick.
- Excellent for temporary repairs and holding on the job.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

Available Sizes

Attribute Name	Value
Standard Roll Length	41.1 m (45 yd)

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company.
©3M 2024 (9/24)