



Technical Data Sheet

3M™ Single-Coated Urethane Foam Tape
4104



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Single-Coated Foam Tapes will adhere to a variety of substrates, including latex-painted wood, lacquered wood, enameled steel, glass, aluminum, stainless steel, acrylic, ABS, and PVC (non-plasticized) as tape adhesion is typically satisfactory within 20 minutes and continues to build with additional time.

Product Features

3M™ Urethane Foam Tapes Series 4100 are a natural-white, firm, high-density, open-cell foam with pressure-sensitive adhesive on one side. The acrylic adhesive offers high initial quick stick to many types of surfaces along with excellent shear strength and high temperature performance. The adhesive is protected by a 0.003 inch (0.08 mm) thick white, silicone treated paper liner and has a firm rigid open cell urethane that offers excellent cushioning characteristics while allowing air or gas vapors to pass through the open cells. This product is placed on a 1.5 in. wide common core when the tape is 3/4 in. or less in width. Skip slitting is also used for roll stability on these narrow sizes. Note: 3M urethane foam tape series 4100 may turn yellow when exposed to light. Such yellowing affects only the appearance and not the physical performance of the tapes.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Natural-white
Adhesive Type		350*
Density	ASTM D3574	192 kg/m ³ (12 lb/ft ³) ¹
Shore 00 Hardness	ASTM D2240	75 ¹
Mold and Mildew Resistance	ASTM G21	No growth after 28 days ²
Compression Deflection: 25% Compression	ASTM D3574	27.6 kPa (4 lb/in ²)

¹ Foam with adhesive

² Foam with Adhesive

Attribute Name	Value
Thickness	6.4 mm (250 mil)
Liner Thickness	0.08 mm (3 mil)
Primary Liner Color	White
Thickness Tolerance	15 %

Attribute Name	Value
*Note	* 3M™ Adhesive 350 is a medium-firm acrylic adhesive that provides a continuation of high wet grab and initial adhesion.

Typical Performance Characteristics

Attribute Name	Value
Short Term Temperature Resistance	177 °C (350 °F) ¹
Long Term Temperature Resistance	93 °C (200 °F) ²
Temperature Resistance	Cold flex at -18 °C (Cold flex at 0 °F) ³
Temperature Use Range note	For Short term

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

³ No cracks. Tape slowly bent around a 1/4 in. diameter mandrel.

Attribute Name	Test Method	Value
Elongation	ASTM D3574	100 % ¹
Tensile Strength	ASTM D3574	795 kPa (115 lb/in ²) ¹
Compression Set	ASTM D1667	8 %

¹ Die "A"

Typical Environmental Characteristics

Solvent Resistance

Solvent/Fuel	3M urethane foam tape series 4100	
	Adhesive	Foam
Acetone	Softens	Softens
Ammonia Cleaner	No effect	No effect
Engine Oil	No effect	No effect
Gasoline	Softens	Swells
JP-4 (jet fuel)	Softens	Swells
MEK	Softens	Softens
Mineral Spirits	No effect	Swells
Soapy Water	No effect	No effect

*Visual observations of tape bonded to steel panels and immersed totally in solvent/fuel for 24 hours.

Electrical and Thermal Properties

Attribute Name	Test Method	Value
Thermal Conductivity	ASTM C518	0.066 W/m/K (0.5 (btu-in)/(h-ft ² -°F))
Surface Resistivity (Adhesive)	ASTM D257	1 x 10 ¹⁵ Ω ¹
Surface Resistivity (Non-Adhesive)	ASTM D257	1 x 10 ¹⁵ Ω ²
Water Absorption: 30% Compression	ASTM D1056	open cell - NA % by Volume

¹ Adhesive Side

² Non-Adhesive Side

Handling/Application Information

Application Techniques

- Bond strength is dependent upon the amount of adhesive-to-surface contact. Firm application pressure develops better adhesive contact and helps improve bond strength.
- To obtain optimum adhesion, the bonding surface must be clean, dry, and well unified. Some typical surface cleaning solvents are isopropyl alcohol and heptane.*

*Be sure to follow the solvent manufacturer's precautions and directions for use when handling solvents.

- Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Industry Specifications

UL 94HBF (File #E76581)

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Maximum Available Width	914 mm (36 in)
Maximum Length	22.9 m (25 yd)
Minimum Available Width	6 mm (0.25 in)
Normal Slitting Tolerance	± 0.8 mm (± 1/32 in)
Roll Diameter	380 mm (15 in)
Standard Roll Length	16.5 m (18 yd)

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of the 3M Company.
©3M 2024 (6/24)