



Technical Data Sheet

3M™ Silane Glass Treatment AP115



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Silane Glass Treatment AP115 is used to promote adhesion of 3M™ VHB™ Tapes to uncoated glass surfaces. Glass is hydrophilic (water loving) in nature and may lead to performance issues over time in humid or wet environments due to water vapor undercutting the bondline and interfering with normal adhesion forces. 3M silane glass treatment AP115 treats the glass surface creating a hydrophobic surface that will act to protect the 3M™ VHB™ Tape bondline.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Temperature	Value
Color		Clear
Liquid Density	16 °C (60 °F)	0.789 kg/L (6.58 lb/gal)
Solvent Resistance		Isopropyl alcohol and water
Flash Point		18 °C (64 °F) ¹
VOC		728 g/L (6.08 lb/gal)
Active Ingredient		<1 % by weight

¹ Closed Cup

Typical Performance Characteristics

Attribute Name	Value
Application Temperature	10 — 38 °C (50 — 100 °F) ¹

¹ It is best to apply the solution at or above the minimum application temperature of the selected 3M™ VHB™ Tape since the tape will be applied shortly after the application of the silane solution.

Handling/Application Information

Application Techniques

The glass surface must be relatively clean and dry. Contaminated glass surfaces (excessively dirty or oily) should be cleaned first with a 50/50 isopropyl alcohol and water mixture.* A clean lint-free cloth should be used. The following surface preparation method should be followed when using 3M™ Silane Glass Treatment AP115 to treat an uncoated glass surface. This procedure is commonly known as the “two cloth” cleaning method.

1. Moisten a clean, soft absorbent, lint-free cloth with the silane solution and vigorously wipe over the area to be bonded in one direction. Do not dip the cloth into the silane solution as this will contaminate it. Alternatively, the silane solution may be sprayed onto the surface and vigorously wiped with the clean cloth around the perimeter of the glass or wherever the tape will be applied. Experience has shown that only a very thin layer (monolayer) of the silane solution gives the best and most consistent results.

2. In an effort to achieve a monolayer, the primed area should be re-wiped (in one direction) with a fresh, clean, lint-free, dry cloth immediately after initial application. The glass should be completely dry with no film residue visible.* Under normal room temperature conditions it is best to wait 1 to 2 minutes before applying the tape so that any residual moisture can evaporate. Apply 3M™ VHB™ Tape within 15 minutes after treating the surface to minimize the risk of recontamination of the surface.

*3M™ Silane Glass Treatment AP115 is clear and should not cloud or discolor glass. If clouding occurs, excess solution has been applied. This must be removed immediately with a dry and clean, lint-free cloth prior to bonding with 3M™ VHB™ Tape. If excess solution has been allowed to dry it must be removed with a 50/50 isopropyl alcohol and water mixture.*The two cloth cleaning method can then be followed again prior to tape application.

*Note: When using solvents, extinguish all ignitions sources, including pilot lights, and follow the manufacturer's precautions and directions for use. Please refer to the MSDS for further precautions and safe handling information for this product.

Storage and Shelf Life

Flammable Liquid and Vapor. Keep away from sources of ignition and avoid static discharge. Conductive clothing and shoes are recommended while dispensing or handling this product. • Keep 3M silane glass treatment AP115 in the original container unless transferring from the one gallon container to a smaller vessel such as a 4 oz. spray bottle. • Keep original container tightly sealed to avoid solvent evaporation. • Store in an environment between 10°C to 35°C (50°F to 95°F). Allow the solution to acclimate to application room temperature condition before using to treat glass. When stored under proper conditions, product retains its performance and properties for 12 months from date of manufacture. See the date of manufacture listed on the bottle label.

Available Sizes - Detailed

4 fl. oz. (118 ml) spray bottle or 1 gallon (3.78 L) bulk bottle

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M and VHB are trademarks of 3M.
©3M 2024 (6/24)