



Technical Data Sheet

3M™ Scotch® Filament Tape 880



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

Scotch® Filament Tape 880 is a high performance tape reinforced with continuous, polyester yarn filaments that give the tape high tensile strength, high impact resistance and high cut resistance. The polypropylene film backing provides excellent abrasion and moisture resistance. The aggressive packaging grade adhesive is specifically formulated to provide an excellent balance of high initial adhesion and long term holding power to fiberboard, “non-oily” metals, printed and painted surfaces.

Product Features

- Good handling.
- Printable (clear only).
- Cut and impact resistant.
- High shear adhesion.
- Excellent aging.
- Tough film backing protects the filaments and adhesive to provide longer functional tape performance.
- Good handling characteristics saves time through ease of dispensing and tape application.
- When printed, the tape provides advertising, warning, and labeling capability.
- The polyester filaments resist cutting when tabbing the end lap of metal coils.
- The polyester filaments absorb the shock of rough, high impact handling to keep package secure during shipping.
- High tensile strength allows the use of less tape in many applications and lowers the cost per application.
- Translucency of the clear version allows good clarity of artwork and important messages, even when covered by the tape.
- Adhesive provides good holding under wide range of application conditions with minimum amount of tape.
- Holds instantly with minimum rubdown.
- Boxes remain securely closed through normal warehouse time cycles

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		Pressure sensitive synthetic rubber resin
Backing		Biaxial Oriented Polypropylene(BOPP)
Backing Color		Transparent
Fiber Reinforcement		Polyester Yarn
Total Tape Thickness	ASTM D3652	0.196 mm (7.7 mil)

Typical Performance Characteristics

Attribute Name	Test Method	Dwell Time	Temperature	Substrate	Value
180° Peel Adhesion	ASTM D3330	72 h	23 °C (73 °F)	Stainless Steel	88 N/100mm (80 oz/in) ¹
Elongation at Break	ASTM D3759				19 %
Tensile Strength	ASTM D3759				4725 N/100mm (472.5 N/cm) (270 lb/in)

¹ 304 mm/min (12 in/min)

Storage and Shelf Life

Store under normal conditions of 4° to 27°C (40° to 80°F) and 40 to 50% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 18 months from date of manufacture.

Information

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

Technical Information

The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

Scotch is a registered trademark of 3M.
©3M 2024 (9/24)