



Technical Data Sheet

3M™ Self-Extinguishing Hot Melt Adhesive
3748 VO



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Hot Melt Adhesive 3748 VO is a tough, flexible, thermoplastic hot melt, 100% solids adhesive which exhibits good peel adhesion and thermal shock properties along with higher heat resistance. It features excellent electrical properties which make it ideal for use on printed wiring board and other electronic bonding applications. Hot Melt Adhesive 3748 VO is self-extinguishing and has a UL 94 VO rating. In addition to electronic applications, it is also useful in many general industrial bonding and sealing applications where a self-extinguishing characteristic is required.

Product Features

- Excellent Adhesion
- Good Electrical Properties
- Non Corrosive to Metal

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Uncured Physical Properties

Attribute Name	Value
Color	Light Yellow ¹
Base Resin	Polyolefin

¹ Colors may vary from nearly white to yellow/amber. Adhesive performance is not affected by color variation.

Typical Physical Properties

Attribute Name	Temperature	Value
Specific Gravity		1.09
Ball & Ring Softening Point		152 °C (305 °F)
Weight Loss by TMA (In Air)	237 °C (459 °F)	1 % ¹
Weight Loss by TMA (In Air)	327 °C (621 °F)	5 % ¹
Weight Loss by TMA (In Air)	356 °C (672 °F)	10 % ¹
Viscosity	180 °C (356 °F)	8,500 cP
Viscosity	200 °C (392 °F)	5,000 cP
Viscosity	23 °C (73 °F)	3,300 cP

¹ Temperature of weight loss at 5 °C/min

Typical Cured Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Shore D Hardness	ASTM D2240	26

Typical Performance Characteristics

180° Peel Adhesion

Temperature: 23 °C (73 °F)

Test Method: 3M C3168

Substrate	Value
Wire Mesh to Fir	416 oz/in ¹
Wire Mesh to FR-4	608 oz/in ¹
Wire Mesh to Polyethylene	432 oz/in ¹
Wire Mesh to Polypropylene	560 oz/in ¹

¹ Test involves bonding 0.5 mm (0.02 in) wire mesh (galvanized window screen type) to substrate using hot melt adhesive. Wire mesh is encapsulated with adhesive. After conditioning, bond is tested by 180° peel back method using Instron at 254 mm/min (10 in/min).

Overlap Shear Strength

Temperature: 23 °C (73 °F)

Test Method: 3M C3096

Substrate	Value
FR-4	215 lb/in ² ¹
Fir	275 lb/in ² ¹
Polypropylene (PP)	250 lb/in ² ¹
Polyethylene (PE)	220 lb/in ² ¹

¹ 25 x 102 mm (1 x 4 in) Douglas Fir specimens bonded with hot melt adhesive, 25 mm (1 in) overlap and 0.3 mm (13 mil) wire spacer to set bond line thickness. 24 hours at 22 °C (70 °F), 50% relative humidity dwell. Shear separation at 51 mm/min (2 in/min) recording strength at failure.

Attribute Name	Test Method	Test Condition	Value
Two Pound Dead Load Heat Resistance	3M C3093		79 °C (175 °F) ¹
Thermal Shock Resistance	3M C3167	100 °C (air) ~ -40 °C (liquid)	Passes 5 cycles w/o cracking ²

¹ 25 x 102 mm (1 x 4 in) Douglas Fir specimens, 25 mm (1 in) overlap shear. 24hr @ 22 °C (70 °F), 50%RH dwell. 14 kPa (2psi) load at 49 °C (100 °F) for 30 min. Bond line temp is raised every 30 minutes until failure. Heat resistance recorded is the last temp prior to bond failure.

² Potted Washer Olyphant test

Typical Environmental Performance

Solvent Resistance

Environmental Condition	Value
Immersed in Isopropyl Alcohol one hour	A ¹
Immersed in Acetone one hour	A ¹
Immersed In 1, 1, 1 - Trichloroethane one hour	B ¹
Immersed in Freon TF one hour	B ¹
Immersed in Freon TMC one hour	B ¹
Immersed in RMA Flux one hour	A ¹
Immersed in Isopropyl Alcohol 30 days	B ¹
Immersed in Acetone 30 days	B ¹
Immersed In 1, 1, 1 - Trichloroethane 30 days	C ¹
Immersed in Freon TF 30 days	C ¹
Immersed in Freon TMC 30 days	C ¹

Environmental Condition	Value
Immersed in RMA Flux 30 days	B ¹

- ¹ A = No attack
B = Slight Surface Attack/Softness
C = Severe Attack/Breakup

Electrical and Thermal Properties

Attribute Name	Temperature	Test Condition	Value
Coefficient of Thermal Expansion		-100 ~ -40 °C	-34 x 10 ⁻⁶ m/m/°C ¹
Coefficient of Thermal Expansion		-20 ~ 25 °C	154.5 x 10 ⁻⁶ m/m/°C ¹
Thermal Conductivity	41 °C (107 °F)		4.58 x 10 ⁻⁴ Cal/s/cm/°C (1.1 x 10 ⁻¹ (btu-ft)/(h-ft ² -°F)) (1.92 x 10 ⁻³ J/cm · s · °C) (19.2 W/m/K) ²
Thermal Conductivity			6 x 10 ¹⁷ W/m/K

¹ CTE determined using TMA Analyzer using a heating rate of 10 °C per minute. Second heat values given.

² On 0.5 mm (0.02 in) samples

Attribute Name	Test Method	Temperature	Test Condition	Value
Dielectric Constant	ASTM D150	23 °C (73 °F)	100 Hz	2.3
Dielectric Constant	ASTM D150	23 °C (73 °F)	1 KHz	2.3
Dielectric Constant	ASTM D150	23 °C (73 °F)	10 KHz	2.3
Dielectric Constant	ASTM D150	23 °C (73 °F)	100 KHz	2.3
Dielectric Constant	ASTM D150	23 °C (73 °F)	1 MHz	0.001
Dielectric Constant	ASTM D150	23 °C (73 °F)	100 MHz	2.3
Dissipation Factor	ASTM D150	23 °C (73 °F)	100 Hz	0.002
Dissipation Factor	ASTM D150	23 °C (73 °F)	1 KHz	0.001
Dissipation Factor	ASTM D150	23 °C (73 °F)	10 KHz	0.001
Dissipation Factor	ASTM D150	23 °C (73 °F)	100 KHz	0.001
Dissipation Factor	ASTM D150	23 °C (73 °F)	100 MHz	0.001
Dielectric Strength	ASTM D149			2.3 V/μm
Dielectric Strength	ASTM D149			1,400 V/mil ¹
Volume Resistivity	ASTM D257	23 °C (73 °F)		4.5 x 10 ¹⁷ Ω-cm

¹ 11 mil (0.27 mm) sample

Handling/Application Information

Application Equipment

- 3M™ Hot Melt Applicator TC or TCQ
- 3M™ Hot Melt Applicator EC - Temperature Module #4
- 3M™ Hot Melt Applicator PG II

Industry Specifications

UL 94 - V0

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M.
Freon is a registered trademark of E.I. DuPont de Nemours Co.
©3M 2024 (9/24)