



## Technical Data Sheet

3M™ Fastbond™ Foam Adhesive 100NF  
Neutral



[Product Details](#)



[Regulatory Info/SDS](#)

### **Product Description**

3M™ Fastbond™ Foam Adhesive 100 is a one-part, water-dispersed, fast setting adhesive. This neoprene-based product bonds many porous substrates to porous or non-porous substrates with minimal dry time. Adheres to many types of flexible polyurethane foam, latex foam fabric, polyester fiberfill, wood, plywood, particleboard and many plastic and metal surfaces.

### **Product Features**

- Water-dispersed so is non-flammable in the wet state.
- High solids for high coverage.
- One component to simplify dispensing.
- Neoprene-based for high heat resistance.
- Low pressure sprayable to reduce misting and overspray.
- Non-dimpling for soft bondlines.
- Designed to be applied between two substrates. Application to substrates that results in direct exposure of the adhesive to light may result in eventual discoloration of the exposed adhesive. Direct exposure can be controlled by proper spray application. Adhesive may soak through very thin fabrics.
- Not recommended for exterior bare metal surfaces unless metal surfaces are completely dried by force drying and protected from moisture.
- Certified to GREENGUARD® Product Emission Standard For Children and Schools(SM) for low emitting interior building materials:



° Addresses or Contributes to LEED® EQ Credit 4.1: Low Emitting Materials: Adhesive and Sealants

### **Technical Information Note**

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### **Typical Uncured Physical Properties**

Attribute Name	Value
Density	9 to 9.4 lb/gal

## Typical Mixed Physical Properties

Attribute Name	Value
Time to Handling Strength	15 s <sup>1</sup>

<sup>1</sup> Min time between bond creation and ability to support a 5 psi tensile load. Open and set times determined by RT environment. Higher temps will lengthen open and set times, while lower temperatures will shorten open time and set time.

## Typical Physical Properties

Attribute Name	Value
Color	White (semi-transparent when dry)
Solids Content by Weight	45 to 49 %
Base Polymer	Polychloroprene (neoprene)
pH	8.4 to 9
Coverage	1,000 ft <sup>2</sup> /gal <sup>1</sup>
Bonding Range	20 min
Viscosity	10 to 40 cP <sup>2</sup>

<sup>1</sup> 2 grms/sq ft dry wt

<sup>2</sup> Brookfield RVF #1 sp @ 20 rpm

## Typical Performance Characteristics

### 180° Peel Adhesion

Temperature: 25 °C (77 °F)

Substrate	Value
ABS	32 oz/in <sup>1</sup>
Aluminum	18 oz/in <sup>1</sup>
Cold Rolled Steel	18 oz/in <sup>1</sup>
Galvanized Steel	18 oz/in <sup>1</sup>
High Density Polyethylene (HDPE)	24 oz/in <sup>1</sup>
Polypropylene (PP)	14 oz/in <sup>1</sup>
Polyvinyl chloride (PVC)	30 oz/in <sup>1</sup>

<sup>1</sup> Peel bonds of cotton duck were tested at a peel angle of 180° @ 2in/min separation rate @RT. The value listed is the average force required to peel the canvas from the substrates in pounds per inch of bond width (PIW).

## Typical Environmental Characteristics

### Temperature Resistance

After air drying 24 hours, 4-inch cube knife edge foam bonds made with 3M™ Fastbond™ Foam Adhesive 100 on 1.2 lb./cu. ft. density urethane foam specimens withstood operating temperatures at 230°F (110°C) for 24 hours without showing any signs of failure along the bonded seams. The adhesive exhibited no indication of attacking or deteriorating the foam and the bondlines remained strong and flexible.

## Handling/Application Information

### Directions for Use

**Note:** When using 3M™ Fastbond™ Foam Adhesive 100, it is required that at least one of each pair of substrates to be bonded be porous or water permeable.

1. Surface Preparation: Use only on clean, dry surfaces. Contamination of surfaces with oil, grease or release agents will prevent good, strong bonds.

2. Application: Adhesive does not require agitation before use. Adjust the spray equipment to give a fine, mist-like spray pattern. Spray a uniform, light coat of adhesive to both surfaces holding spray applicator 10-15 inches from surface.

3. Coverage: Coverage will depend on foam density, surface porosity of substrates, and strength of adhesive bond required. Typically one gallon of adhesive will cover up to 1000 square feet of substrate surface at a coating weight of approximately 2 dry grams of adhesive/sqft. In all cases, user evaluation will be required to determine the optimum coverage levels.

**Note:** Application of adhesive at coating weights above 2 dry grams/sqft or using a coarse spray pattern may result in

longer activation times.

4. Activation Time: The adhesive activates sufficiently to permit making foam/foam bonds within 15 seconds after application. Bonds of foam or fabric to smooth, nonporous surfaces such as plastic or metal will require longer activation times. Bonds may be made up to 20 minutes after application depending on ambient temperature and humidity conditions. See Note above.

5. Assembly and bonding: For foam bonding and foam fabrication, pressure sufficient to compress the foam should be applied to the bond line by manual or mechanical methods. Bond the adhesive coated surfaces with sufficient pressure to ensure good contact across the entire adhesive bond line.

6. Cleanup: Wet adhesive may be removed with water containing a small amount of detergent.\* Dry adhesive may be removed with a combination of 3M™ Citrus Base Cleaner or equivalent and mechanical systems such as wire brushing. Dry adhesive cannot be removed from porous surfaces such as foams or fabrics. Flush the adhesive wetted surfaces of spray equipment with water containing a small amount of detergent.\* Follow with a flush of clean water.

\*Cleaning Solution: One pint of detergent to five gallons of water.

\*\***Note:** When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer’s precautions and directions for use.

**Application Equipment**

**Note:** Appropriate application equipment can enhance adhesive performance. We suggest the following application equipment for the user’s evaluation in light of the user’s particular purpose and method of application.

Low to Medium Volume Applications				
Equipment Type	Equipment Example*	Air Cap	Fluid Tip	Atomizing Air Pressure**
Siphon Gun	Critter Siphon Gun #118	N/A	N/A	10 psi
Gravity Feed Gun	Binks Model 95G	66SD	65 SS (.059")	6 psi
	Binks M1-G	93P	94 (.055")	10 psi

Medium to High Volume Applications				
Equipment Type	Equipment Example*	Air Cap	Fluid Tip***	Atomizing Air Pressure**
Pressure Fed Hand Held Spray Guns	Binks 2001 SS	63P	63 SS (.028")	10 psi
	Binks 95	63P	63 SS (.028")	10 psi
	Binks Cub SL	25	25 T (.025")	10 psi

\*Systems other than those listed can be used with 3M™ Fastbond™ Foam Adhesive 100. Existing spray equipment can also be adapted. Fluid hoses used previously with solvent-based adhesive or cleaning compounds must be replaced with new hose. Be sure to follow the equipment manufacturer’s precautions, directions for use, and recommendations for such equipment. For additional information, contact your local representative.

\*\*Starting air pressure on regulator. Adjust up or down based on application requirements.

\*\*\* Also available are 2 piece fluid tips as replacements fluid tips. These 2 piece tips allow for easier cleaning with less chance of adhesive contamination of the air passages in the spray gun.

**Pressure Pots**

Stainless steel pressure pots recommended. Non-stainless may be used with plastic liners if dip tube and fittings are changed to plastic or stainless steel.

**Pumping Equipment**

1 inch plastic diaphragm pump with PTFE checks and diaphragms. All pumps should be short stroked for pump longevity. For additional information, contact your local representative.

**Filter (pump output)**

Graco model 12 (stainless steel) with filter bag #521-264 or equivalent.

**Hoses**

All fluid hoses should be nylon or polyester lined. Hose fittings should be stainless steel or plastic. The typical fluid hose length @ 1/4 inch i.d. should be 15 to 25 ft. Use of larger fluid hose i.d. or lengths less than 15 ft. will result in loss of fluid pressure control. Use of smaller fluid hose I.D. lengths greater than 25 ft. can result in product coagulation in the line.

**Note:** Do not use fluid lines that have been previously used with solvent. Do not use air operated piston pumps with these products.

## **Storage and Shelf Life**

Best storage temperature is 40-90°F (5-32°C). Higher temperatures reduce normal storage life. Lower temperatures cause increased viscosity of a temporary nature. This water-dispersed adhesive will become unusable with prolonged storage below 40°F (4°C). Rotate stock on a “first in, first out” basis. Protect from freezing. When stored at the recommended temperature in the original, unopened container, this product has a shelf life of 18 months from date of manufacture.

## **Precautionary Information**

Refer to Product Label and Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

## **Automotive Disclaimer**

**Select Automotive Applications:** This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M  
Industrial Adhesives and Tapes Division  
3M Center, Building 225-35-06  
St. Paul, MN 55144-1000  
800-362-3550

3M and Fastbond are trademarks of 3M Company.  
LEED is a registered trademark of the United States Green Building Council (USGBC).  
©3M 2022 (5/22)