



Technical Data Sheet

3M™ Scotch® Filament Tape 890RCT



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

Scotch® Filament Tape 890RCT is a high-performance transparent filament tape reinforced along its length with continuous fiberglass-yarn filaments, which gives the tape a very high tensile strength. The clear polyester backing provides excellent abrasion, moisture and scuff resistance. The adhesive is a very aggressive packaging adhesive specifically formulated to meet the high demands of sealing corrugated cartons, including those with high recycled content as used in today's packaging materials.

Product Features

- High tensile strength.
- High shear strength.
- Good initial adhesion to enhance bond strength to recycled board.
- Excellent aging before and after application.
- Excellent long-term holding power.
- Good protection of filaments and adhesive to provide longer package life.
- Assures maximum package performance for limited outdoor use.
- Saves time through ease of dispensing and handling versus glue and strapping.
- Advertising, and warnings are printable by the print seal process.
- Good holding under a wide range of application conditions with minimum amount of tape.
- Boxes remain securely closed through normal warehouse time cycles.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		Pressure sensitive synthetic rubber-resin
Backing		Polyester(PET)
Backing Color		Clear
Fiber Reinforcement		Glass Yarn
Total Tape Thickness	ASTM D3652	0.203 mm (8 mil)

Typical Performance Characteristics

Attribute Name	Test Method	Dwell Time	Temperature	Substrate	Value
180° Peel Adhesion	ASTM D3330	72 h	22 °C (72 °F)	Stainless Steel	88 N/100mm (80 oz/in) ¹
Elongation at Break	ASTM D3759				5 %
Tensile Strength	ASTM D3759				1190.9 N/cm (11909 N/100mm) (680 lb/in)

¹ 12 in/min (300 mm/min)

Handling/Application Information

Application Techniques

An extensive line of application equipment including hand-held dispensers and an automatic L-Clip applicator is available. Application is most easily accomplished at room temperature. At lower temperatures, approaching 32°F (0°C), the adhesive becomes firm. Once applied, Scotch® Filament Tape 890RCT performs well through- out the normal temperature ranges encountered by packaged products in shipping and storage environments

Storage and Shelf Life

Store behind present stock. Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40-50% relative humidity are recommended. Rotate your stock.
To obtain best performance, use this product within 18 months from date of manufacture.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

Scotch is a registered trademark of 3M.
©3M 2016 (1/16)