



Technical Data Sheet

3M™ Fastbond™ Contact Adhesive 2000-NF



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Fastbond™ Contact Adhesive 2000-NF with Spray Activator #1 is a waterdispersed, high solid, activated adhesive which provides immediate bonding capabilities and handling strength without forced drying equipment for most applications.

Product Features

- Immediate bonding without heat.
- Immediate handling strength.
- Bonds flexible polyurethane and latex foams, plastic laminate, wood, plywood, particle board, fabrics, fiber, aluminum, galvanized steel and many plastics.
- Post-formable and heat resistant.
- Co-sprayed with plural component, external mix spray systems - no premixing, no limited pot life.
- Available in blue, light orange or neutral color.
- Not recommended for bonding bare steel surfaces (unless force dried and protected from moisture). Primed or painted steel surfaces must be thoroughly tested for corrosion and compatibility with Fastbond contact adhesive 2000-NF with spray activator #1 before use.
- Designed to be applied between two substrates. Application to substrates that results in direct exposure of the adhesive to light may result in eventual discoloration of the exposed adhesive. Direct exposure can be controlled by proper spray application. Adhesive may soak through very thin fabrics.
- Certified to GREENGUARD® Product Emission Standard For Children and Schools(SM) for low emitting interior building materials:



- Addresses or Contributes to LEED® EQ Credit 4.1: Low Emitting Materials: Adhesive and Sealants
- Addresses or Contributes to LEED® EQ Credit 4.3: Low Emitting Materials: Flooring Materials
- Addresses or Contributes to LEED® EQ Credit 4.4: Low Emitting Materials: Composite Wood and Agrifiber Products
- Addresses or Contributes to LEED® EQ Credit 4.5: Low Emitting Materials: Furniture and Furnishings
- Addresses or Contributes to LEED® EQ Credit 4.6: Low Emitting Materials: Ceiling and Wall Systems

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Uncured Physical Properties

Attribute Name	Value
Base	Polychloroprene
Net Weight	8.9 to 9.3 lb/gal

Typical Physical Properties

Attribute Name	Temperature	Value
Color		Blue, Light Orange or Neutral
Solids Content by Weight		47 to 51 %
pH		10 to 11
Coverage		(including activator) 690 ft ² /gal ¹
Viscosity	27 °C (80 °F)	200 to 750 cP ²

¹ @ 3 g/ft² dry

² Brookfield Viscometer RVF #2 spindle @ 20 rpm

Attribute Name	Value
*Note	When bonding wood veneers, success is dependent on many variables such as environmental conditions, bonding process, type of base material, type of veneer, adhesive type and top coat finishing systems to name a few. For unbacked wood veneers, water based contact adhesives are not recommended. It is the user's responsibility to thoroughly test any adhesive for its suitability in bonding wood veneers. It is also recommended to follow the veneer manufacturers recommendation and industry guidelines.

Typical Performance Characteristics

Overlap Shear Strength

Substrate: Birch to Birch
 Temperature: 22 °C (72 °F)
 Dwell Time: 3 week
 Test Method: ASTM D1002

Test Condition	Value
-30°F(-34°C)	1,000 lb/in ² ¹
	350 lb/in ² ¹
180°F(82°C)	50 lb/in ² ¹
200°F(93°C)	40 lb/in ² ¹
225°F(107°C)	30 lb/in ² ¹

¹ Adhesive co-spray applied and bonded immediately with nip roll pressure. Bonds tested at a separation rate of 0.2 in./min. 1/8 in substrates

Flatwise Tensile Strength

Dwell Time: 3 week
 Test Method: C297

Temperature	Value
22 °C (72 °F)	84 lb/in ² ¹
82 °C (108 °F)	25 lb/in ² ¹
93 °C (200 °F)	25 lb/in ² ¹

Temperature	Value
107 °C (225 °F)	25 lb/in ² ¹

¹ High pressure laminate/particle board. Test speed = 0.05 in./min.

Handling/Application Information

Directions for Use

When using 3MTM Fastbond™ Contact Adhesive 2000-NF with Spray Activator #1, it is required that at least one of each pair of substrates to be bonded be porous or water permeable.

Surface Preparation

Surfaces must be clean, dry and dust free.

Spray Mix Ratio of Activator to Adhesive

It is recommended that Fastbond contact adhesive 2000-NF be spray mixed with spray activator #1 at a ratio of 15 parts adhesive to 1 part activator (by weight or volume). When activated, slight adhesive transfer should occur when adhesive film is

touched immediately after spraying.

Application

Use a plural nozzle, external mix spray applicator to mix adhesive with activator to achieve proper mix of Fastbond contact adhesive 2000-NF with spray activator #1. (Refer to Application Equipment Suggestions above for additional information about spray equipment.) Spray apply a uniform coat of mixed adhesive to both surfaces. (See coverage section.) One coat should usually be sufficient for both surfaces. Be sure to overlap the spray pattern slightly with each pass of the spray applicator to ensure complete activation of adhesive and uniform coverage.

A uniform dull film indicates sufficient mixture of Fastbond contact adhesive 2000-NF with spray activator #1.

Coverage

Approximately 690 sqft/gal. sufficient to apply 345 sqft of bonded surface on most substrates such as decorative laminate and particle board. Optimum performance is obtained using 2.5-3.5 grams/sqft dry adhesive on each surface.

Note: Coverage will vary depending on the porosity of substrates and strength of adhesive bond desired. For decorative laminate to particle board, optimum performance is obtained at 2.5-3.5 grams of dry adhesive per square foot applied to each surface. Depending on the user's performance requirements, less adhesive is suggested if fabrics, foams, etc. are to be bonded. In all cases, user's evaluation will be required to determine the optimum coverage levels.

Activation Time

With proper mixing of adhesive and activator and depending on ambient conditions, adhesive activates sufficiently to make bonds within 5-15 seconds after application. Depending on ambient conditions and substrates, bonds should be made within (2) hours. While bonds may be made immediately, the optimum initial strength will be obtained by allowing the adhesive to dry the same amount of time as the previous adhesive (solvent) type.

Assembly

For foam bonding and foam fabrication, pressure may be applied to the bond by manual or mechanical methods. Bond adhesive coated surfaces with sufficient pressure to assure good contact across adhesive bond line. For decorative laminates, spacers such as dowels or strips of laminate may be used to help prevent premature adhesive/adhesive contact and bonding prior to positioning. Slide out the spacers and apply uniform pressure working toward the edges. A 3 inch roller used with maximum body pressure should be used to help ensure adequate contact and bonding especially on the edges. Bonded assemblies may be machined, trimmed, etc. immediately after bonding. The use of a pinch roll is preferred for optimum performance.

Cleanup

Work Surface: If adhesive has not activated, clean surfaces with water or with a small amount of liquid detergent followed with a cleaner such as 3M™ Citrus Base Cleaner or equivalent. Dried, activated adhesive may be cleaned with a combination

of cleaner and mechanical systems such as wire brushing.

Spray Equipment: Flush adhesive portion of spray equipment with cold water containing a small amount of detergent* followed by a flush with clean water. The activator portion of spray equipment should be flushed with clean water (no detergent).

*Cleaning Solution: One pint of detergent to five gallons of water.

Application Techniques

Co-Spray (Adhesive to Activator ratio of 15:1)

Application Equipment

Note: Appropriate application equipment can enhance adhesive performance. We suggest the following application equipment for the user's evaluation in light of the user's particular purpose and method of application.

Air Atomizing Spray Equipment:

When hand spraying, plural component (co-spray) applicators are used. These applicators spray activator and adhesive through separate fluid nozzles with mixing occurring outside the spray applicator.

For automatic spray systems, separate spray applicators are used for the activator and adhesive, with the applicators aimed so the spray patterns converge and mix together before reaching the substrate.

Note: Premixing of the adhesive and activator prior to spraying is NOT possible and makes the adhesive unusable.

Hand Held Spray Applicators	Air Cap	Fluid Nozzle	Atomizing Air Pressure	Approximate Air Requirement
Binks Mach 1PC H.V.L.P.	91 PC	94F (.055")	15-30 psi	6 scfm @ 15 psi
Graco Optimizer 2K H.V.L.P.	188-754	185-702 (.055")	25-35 psi	6 scfm @ 15 psi
Mattson Cross-Fire H.V.L.P.	81270	82017 (.050")	15-30 psi	6 scfm @ 15 psi
DeVilbiss Pro Bond 2K	28L	FF (.055")	25-35 psi	6 scfm @ 15 psi

Automatic Spray Applicators	Air Cap	Fluid Nozzle	Atomizing Air Pressure	Approximate Air Requirement
Binks Mach 1PC H.V.L.P.	91 PC	94F (.055")	15-30 psi	6 scfm @ 15 psi
Binks Mach 1A H.V.L.P. (Adhesive)	91 P	94F (.055")	15-30 psi	11 scfm @ 30 psi
Binks Mach 1A H.V.L.P. (Activator)	91 P	90F (.030")	15-30 psi	11 scfm @ 30 psi
Binks 21, 61, 95A (Adhesive)	66SD-3	65SS (.059")	15-30 psi	6 scfm @ 15 psi
Binks 21, 61, 95A (Activator)	66S	63SS (.028")	10-15 psi	3.4 scfm @ 30 psi
DeVilbiss AGX (Adhesive)	30	FF (.055")	15-30 psi	6 scfm @ 20 psi
DeVilbiss AGX (Activator)	30	G (.028")	10-15 psi	6 scfm @ 20 psi
DeVilbiss AGXV H.V.L.P. (Adhesive)	33A	FF (.055")	15-30 psi	12 scfm @ 30 psi
DeVilbiss AGXV H.V.L.P. (Activator)	33A	G (.028")	10-15 psi	6 scfm @ 20 psi

TO MEASURE FLUID FLOW

Hand Held Applicators: Pressurize adhesive source only. Direct adhesive fluid nozzle into a measuring device. Pull trigger and flow material into measuring device for 60 seconds. Increase or decrease fluid source pressure to obtain desired fluid flow. The fluid flow of the activator should be adjusted to 15 to 1 ratio when co-sprayed. The measurement can be done by either weight or volume.

Automatic Applicators: Pressurize adhesive fluid source only. Activate trigger and flow adhesive into measuring device for 60 seconds. Increase or decrease fluid pressure to obtain desired fluid flow. When adhesive fluid flow is correctly adjusted repeat the process with the activator spray applicator, setting fluid flow to one-fifteenth of the adhesive fluid flow. The measurement can be done by either weight or volume.

Material Supply:

Pressure Pots

Adhesive and Activator: For best results, use stainless steel pressure pots. Nonstainless pressure pots may be used if used with plastic liner and the dip tube and fittings are changed to plastic or stainless steel.

Pumps

Adhesive: Use a 1 inch plastic bodied, double diaphragm pump with PTFE diaphragms and ball checks. It is suggested that all diaphragm pumps are short stroked by the manufacturer before use. Do not use piston type reciprocating pumps, or diaphragm pumps smaller than 1 inch. When using diaphragm pumps the use of a bag type fluid filter is recommended on the output of the pump. A filter such as the Graco Model 12 part number 915-518 with a 300 micron filter bag part number 521-264 or equivalent is suggested.

Fluid regulators cannot be used with this adhesive. Fluid pressure is controlled by the pump pressure.

Activator: A 1:1 or 2:1 pogo or piston type reciprocating pump is suggested. All pump parts in contact with activator must be plastic or stainless steel. Diaphragm pumps and fluid regulators can be used (stainless steel or plastic on all wetted components).

Hoses

All fluid hoses should be nylon or polyethylene lined. Hose fittings should be stainless steel or plastic.

Note: Do not use fluid lines that have previously been used with solvent whether flammable or nonflammable.

Industry Specifications

Certified to GREENGUARD® Product Emission Standard For Children and Schools(SM) for low emitting interior building materials:

- ° Addresses or Contributes to LEED® EQ Credit 4.1: Low Emitting Materials: Adhesive and Sealants
- ° Addresses or Contributes to LEED® EQ Credit 4.3: Low Emitting Materials: Flooring Materials
- ° Addresses or Contributes to LEED® EQ Credit 4.4: Low Emitting Materials: Composite Wood and Agrifiber Products
- ° Addresses or Contributes to LEED® EQ Credit 4.5: Low Emitting Materials: Furniture and Furnishings

° Addresses or Contributes to LEED® EQ Credit 4.6: Low Emitting Materials: Ceiling and Wall Systems

Storage and Shelf Life

Best storage temperature is 60-80°F (16-27°C). Higher temperatures reduce normal storage life. Lower temperatures cause increased viscosity of a temporary nature. This water-dispersed adhesive will become unusable with prolonged storage below 40°F (4°C). Rotate stock on a “first in, first out” basis. Protect from freezing. When stored at the recommended temperature in the original, unopened container, these products have a shelf life of 21 months from date of manufacture.

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

Automotive Disclaimer

Select Automotive Applications: This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M’s control and uniquely within user’s knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer’s application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M’s option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

3M and Fastbond are trademarks of 3M.
Setaflash is a registered trademark of Erdco Engineering Corp.
©3M 2022 (5/22)