



# Technical Data Sheet

3M™ Conformable Double Coated Tape  
93420



[Product Details](#)



[Regulatory Info/SDS](#)

## Product Description

Finite Element Analysis (FEA) data is available for this product at: [3m.com/FEA](https://3m.com/FEA)

3M™ Conformable Double Coated Tape 93420 is a high-performance double coated tape specifically designed for the bonding of touch panel modules to device housings ("Lens" or "Window" Bonding). This product incorporates a unique energy absorbing carrier film and pressure sensitive adhesive that provides an exceptional balance of properties required for demanding applications. 3M™ acrylic adhesive provides good bond strength to most surfaces, including printed inks.

## Product Features

- Excellent anti-lifting properties
- Great drop performance is obtained from the energy absorbing core
- Chemical Resistant to a variety of household chemicals
- Great peel adhesion to both Low Surface Energy (LSE) and High Surface Energy (HSE) surfaces

## Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

## Typical Physical Properties

Attribute Name	Test Method	Test Condition	Value
Adhesive Type		Faceside	Acrylic Adhesive <sup>1</sup>
Adhesive Type		Backside	Acrylic Adhesive <sup>2</sup>
Adhesive Carrier			Energy Absorbing Core, Black
Total Tape Thickness	ASTM D3652		0.2 mm (8 mil)
Adhesive Thickness		Faceside	0.0375 mm (1.5 mil) <sup>1</sup>
Adhesive Thickness		Backside	0.0375 mm (1.5 mil) <sup>2</sup>
Carrier Thickness			0.125 mm (5 mil)
Liner			PCK
Liner Thickness			0.106 mm (4.2 mil)

<sup>1</sup> Faceside adhesive is on the interior of the roll, exposed when unwound and liner removed.

<sup>2</sup> Backside adhesive is on the exterior of the roll, exposed when liner is removed.

## Typical Performance Characteristics

### 180° Peel Adhesion

Test Method: ASTM D3330

Dwell Time	Temperature	Substrate	Backing	Value
15 min	23 °C (73 °F)	ABS	2 mil PET	10.4 N/cm (95 oz/in) <sup>1</sup>
15 min	23 °C (73 °F)	Polycarbonate (PC)	2 mil PET	11.5 N/cm (105 oz/in) <sup>1</sup>
15 min	23 °C (73 °F)	Polypropylene (PP)	2 mil PET	9.3 N/cm (85 oz/in) <sup>1</sup>
15 min	23 °C (73 °F)	Stainless Steel	2 mil PET	9.3 N/cm (85 oz/in) <sup>1</sup>

Dwell Time	Temperature	Substrate	Backing	Value
72 h	23 °C (73 °F)	ABS	2 mil PET	10.9 N/cm (100 oz/in) <sup>1</sup>
72 h	23 °C (73 °F)	Glass	2 mil PET	10.9 N/cm (100 oz/in) <sup>1</sup>
72 h	23 °C (73 °F)	Polycarbonate (PC)	2 mil PET	11.5 N/cm (105 oz/in) <sup>1</sup>
72 h	23 °C (73 °F)	Polypropylene (PP)	2 mil PET	12 N/cm (110 oz/in) <sup>1</sup>
72 h	23 °C (73 °F)	Stainless Steel	2 mil PET	10.9 N/cm (100 oz/in) <sup>1</sup>
72 h	70 °C (158 °F)	Glass		7.7 N/cm (70 oz/in) <sup>1</sup>
72 h	70 °C (158 °F)	Polycarbonate (PC)		8.2 N/cm (75 oz/in) <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

### Static Shear

Test Method: ASTM D3654

Temperature	Test Condition	Value
23 °C (73 °F)	1000 g	>10,000 min <sup>1</sup>
70 °C (158 °F)		>10,000 min <sup>1</sup>

<sup>1</sup> 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	149 °C (300 °F) <sup>1</sup>
Long Term Temperature Resistance	93 °C (200 °F) <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## Handling/Application Information

### Application Examples

- Lens Bonding Applications
- Electronic Device Bonding

## Application Techniques

For maximum bond strength the surfaces should be thoroughly cleaned with a 50:50 mixture of isopropyl alcohol and water. Consult manufacturer's directions for use and precautions when using cleaning solvents. Ideal tape application is accomplished when temperature is between 21° and 38°C (between 70° and 100°F) and the bond is allowed to dwell 72 hours. Initial tape application to surfaces at temperatures below 10°C (50°F) is not recommended.

## Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## Automotive Disclaimer

### Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M is a trademark of 3M Company.  
©3M 2024 (9/24)