



## Technical Data Sheet

### 3M™ Impact Resistant Adhesive Transfer Tape 95010



[Product Details](#)



[Regulatory Info/SDS](#)

#### Product Description

3M™ Impact Resistant Adhesive Transfer Tape 95010 is a black pressure sensitive adhesive used for bonding a wide range of materials in the electronics industry. This 100 um tapes provide superior impact resistance to meet industry drop test requirements and have high bond strength while providing good conformability and removability.

#### Product Features

- Engineered for impact resistance and vibration damping
- 100 micron (4 mil) tape helps consumer electronics keep a thin profile
- Black modified acrylic adhesive provides conformability and removability
- Double liner provides stability for die cutting

#### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Typical Physical Properties

Attribute Name	Value
Adhesive Thickness	0.1 mm (4 mil)
Primary Liner Type	Clear PET <sup>1</sup>
Liner Thickness	0.05 mm (1.97 mil)
Secondary Liner Type	Clear PET <sup>1</sup>
Primary Liner Thickness	0.05 mm (1.97 mil)
Secondary Liner Thickness	0.03 mm (1.18 mil)
Primary Liner Color	Clear

<sup>1</sup> Outer liner (paper) is the primary liner, Inner liner (Polypropylene) is secondary liner.

#### Typical Performance Characteristics

##### 180° Peel Adhesion

Temperature: 23 °C (73 °F)

Test Method: ASTM D3330

Dwell Time	Substrate	Backing	Value
20 min	Stainless Steel	2 mil Aluminum Foil	7 N/cm (64 oz/in) <sup>1</sup>
72 h	Polycarbonate (PC)		9.5 N/cm (86.4 oz/in) <sup>1</sup>
72 h	Stainless Steel	2 mil Aluminum Foil	10.5 N/cm (96 oz/in) <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

## **Handling/Application Information**

### **Application Examples**

Bonding various electronic components (e.g., display, battery, speaker, keyboard, trackpad, camera lens, antenna, FPC, etc.)

### **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

### **Recognition/Certification**

**TSCA:** This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements

**MSDS:** 3M has not prepared a MSDS for this product which is not subjected to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R.1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, this product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

**UL:** These products have been recognized by Underwriters Laboratories, Inc. under UI 746C and UL 969. For more information on the UL Certification, please visit the website at <http://www.3M.com/converter>, select UL Recognized Materials, then select the specific product area.

**Note:** One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information including that for OSHA, USCPSP, California Proposition 65, REACH and RoHS, can be found at [3M.com/regs](http://3M.com/regs).

### **Automotive Disclaimer**

#### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
3M.com/iatd

3M is a trademark of 3M Company  
© 3M 201 (12/16)