

## 3M™ PELTOR™ Electronic Earplug, EEP-100 EU OR

### Product Description

The 3M™ PELTOR™ Electronic Earplug, EEP-100 helps protect your hearing, and can help improve situational awareness and communications in challenging environments.

Integrated with level-dependent technology, the EEP-100 helps provide hearing protection in noise and enhanced situational awareness in quiet environments.

The small and lightweight design helps improve the overall comfort and user experience.

### Key Features

- Helps provide hearing protection
- Level-dependent function (for enhanced situational awareness)
- Intuitive one-button operation
- Durable storage and charging case (IP54)
- Small and lightweight design
- Replaceable eartips
- Cord and Windscreen included

### Common Applications

Forestry, Agriculture, Hunting and Shooting

### Standards and Approvals

Hereby, 3M Svenska AB declares that the product is in compliance with appropriate directives or regulations to fulfill the requirements for the CE marking.

The full text of the EU declaration of conformity is available at the following internet address: [www.3M.com/PELTOR/DOC](http://www.3M.com/PELTOR/DOC).

A copy of the declaration of conformity and additional information required in the directives or regulations can also be obtained by contacting 3M in the country of purchase.



### Models:

Article number	Description	3M ID number
EEP-100 EU OR	3M™ PELTOR™ Electronic Earplug, EEP-100 EU OR Kit, Cord and Windscreen incl.	7100232825

### Accessories and Spare parts

370-TEPL-25	3M™ UltraFit™ Communication Tips Replacement, Large, 25 pairs	7100066388
370-TEPM-25	3M™ UltraFit™ Communication Tips Replacement, Medium, 25 pairs	7100066387
370-TEPS-25	3M™ UltraFit™ Communication Tips Replacement, Small, 25 pairs	7100066371
PELTIP5-01	3M™ Torque™ Eartips, 50 pairs	7000108492
CCC-GRM-25	3M™ PELTOR™ Communication Tip, Triple C, 25 pairs	7100103087
TEP-WINDSCREEN	3M™ PELTOR™ TEP/LEP WINDSCREEN FOAM	7100113748
TEP-CORD	3M™ PELTOR™ Tactical Earplug Replacement Cord	7100074090

# Technical data specifications

## 3M™ PELTOR™ Electronic Earplug, EEP-100 EU

### Technical data specifications

#### Model

Microphone Type: Omni-directional

#### Earplug Power / Electrical Characteristics

Earplug Battery Type: Lithium Ion  
 Earplug Battery Life: Approximately: 16 hours  
 Earplug Battery Charge Time: Approximately: 180 minutes  
 Earplug Volume Steps: 3 steps, (-6dB, +0dB, +6dB)  
 Case USB Type: Micro B

Waterproof Rating: Complies with IP54 with cover and USB port closed.

SNR: PPE regulation 2016/425

#### Physical Characteristics

Case Size (L x W x H): 89.6mm x 61.6mm x 27.3mm

Case Material: ABS

Earplug Keypad: One button operation (On / Off / Volume / Comms)

RoHS Compliance: RoHS II

Weight Box containing charger, 2 Earplugs, 5 pair communications Eartips, USB cable, Cord, Windscreen: Approximately: 240 g

Weight: Charger: Approximately: 57 g

Weight: 1 earpiece: Approximately: 4 g

#### Environmental Characteristics

Storage temp (complete kit): -20 to +50°C

Earpiece Operating temp: -20 to +50°C

Charger Operating temp: 0 to +45°C

Shelf time (battery): Max 12 Months


### Laboratory Attenuation

#### Ultrafit™ Eartips




Frequency (Hz)	125	250	500	1000	2000	4000	8000	H	M	L	SNR
MV (dB)	34.5	31.5	36.2	33.4	34.8	34.9	38.8	34.5	33.6	33.0	35.2
SD (dB)	6.0	5.4	5.6	4.3	3.8	5.0	4.0	3.7	4.0	4.6	3.8
APV = MV - SD (dB)	28.5	26.1	30.6	29.1	31.0	29.9	34.8	31	30	28	31

#### PELTIP5-01/Torque™ Eartips (not incl.)



Frequency (Hz)	125	250	500	1000	2000	4000	8000	H	M	L	SNR
MV (dB)	37.8	36.0	40.5	41.2	41.3	39.6	46.1	40.3	39.9	38.2	41.0
SD (dB)	4.3	5.5	4.2	4.7	3.2	4.3	3.6	3.0	3.4	4.1	3.1
APV = MV - SD (dB)	33.5	30.5	36.3	36.5	38.0	35.3	42.5	37	37	34	38

#### CCC-GRM-25 Eartips



Frequency (Hz)	125	250	500	1000	2000	4000	8000	H	M	L	SNR
MV (dB)	35.5	32.5	37.1	38.0	37.6	39.5	45.5	38.0	37.1	35.2	38.7
SD (dB)	4.5	4.0	4.4	3.7	2.9	4.6	4.2	2.6	3.1	3.6	2.8
APV = MV - SD (dB)	30.9	28.4	32.7	34.3	34.6	34.9	41.3	35	34	32	36

**WARNING!** 3M strongly recommends personal fit testing of hearing protectors. Research suggests that users may receive less noise reduction than indicated by the attenuation label value(s) on the packaging due to variation in fit, fitting skill, and motivation of the user. Refer to applicable regulations for guidance on how to adjust attenuation label values. In the absence of applicable regulations, it is recommended that the SNR be reduced to better estimate typical workplace protection.

**CAUTION!** When worn according to the User Instructions, this hearing protector helps reduce exposure to both continuous noises, such as industrial noises and noises from vehicles and aircraft, as well as very loud impulse noises, such as gunfire. It is difficult to predict the required and/or actual hearing protection obtained during exposure to impulse noises. For gunfire, the weapon type, number of rounds fired, proper selection, fit and use of hearing protection, proper care of hearing protection, and other variables will impact performance. If your hearing seems dulled or you hear a ringing or buzzing during or after any noise exposure (including gunfire), or for any other reason you suspect a hearing problem, your hearing may be at risk. To learn more about hearing protection for impulse noise, please visit [www.3M.com/hearing](http://www.3M.com/hearing).



#### Warranty:

The warranty does not cover any damage caused by neglected maintenance or careless handling. For more information on maintenance, please see the user instruction. For complete warranty condition, contact your dealer or local 3M office

#### Important Notice

3M does not accept liability of any kind, be it direct or consequential (including, but not limited to, loss of profits, business and/or goodwill) arising from reliance upon any information herein provided by 3M. The user is responsible for determining the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. Always read and follow User Instructions.



**3M Personal Safety Division**  
 3M Svenska AB, Box 2341  
 SE-331 02 Värnamo  
 Sweden  
 Internet: [www.3M.com/PELTOR](http://www.3M.com/PELTOR)

3M Personal Safety Division products are for occupational use only. Please recycle. Printed in Sweden. © 3M 2023. All rights reserved. 3M, PELTOR, UltraFit, and Torque are trademarks of 3M Company, and its affiliates.