

|                  |                                                                                     | 3M Code     | Model #     | Item Description                                               | Qty/NZ UOM                     | SLC <sub>80</sub> dB | Class |
|------------------|-------------------------------------------------------------------------------------|-------------|-------------|----------------------------------------------------------------|--------------------------------|----------------------|-------|
| Disposable       |    | 70071514932 | 312-1201    | 3M™ E-A-R™ Classic™ Polybag, Uncorded                          | 2000 pairs                     | 23                   | 4     |
|                  |                                                                                     | 70071562774 | 393-2003-50 | 3M™ E-A-R™ Classic™ EARfit Probed Test Plug                    | 50 pairs                       |                      |       |
|                  |    | HC000664637 | 1100        | 3M™ 1100 & 1110 Uncorded                                       | 200 pairs                      | 21                   | 3     |
|                  |                                                                                     | HC000664934 | 1110        | 3M™ 1100 & 1110 Corded                                         | 500 pairs                      |                      |       |
|                  |                                                                                     | 70071577772 | 393-2010-50 | 3M™ 1100 EARfit Probed Test Plug                               | 50 pairs                       |                      |       |
|                  |    | 70071515848 | 310-4002    | 3M™ E-A-R™ Classic™ Platinum (small) Pillow Pack, Uncorded     | 2000 pairs                     | 23                   | 4     |
|                  |                                                                                     | 70071562816 | 393-2003-50 | 3M™ E-A-R™ Classic™ Platinum (Small) EARFit Probed Test Plug   | 50 pairs                       |                      |       |
|                  |    | 70071515020 | 312-1250    | 3M™ E-A-Rsoft™ Yellow Neons™ Regular Uncorded                  | 2000 pairs                     | 23                   | 4     |
|                  |                                                                                     | 70071515152 | 311-1251    | 3M™ E-A-Rsoft™ Yellow Neons™ Large Corded                      | 2000 pairs                     |                      |       |
|                  |                                                                                     | 70071515053 | 312-1251    | 3M™ E-A-Rsoft™ Yellow Neons™ Large Uncorded                    | 2000 pairs                     |                      |       |
|                  |                                                                                     | 70071562741 | 393-2000-50 | 3M™ E-A-Rsoft™ Yellow Neons™ EARfit Probed Test Plug - Regular | 50 pairs                       |                      |       |
|                  |                                                                                     | 70071650249 | 393-2014-50 | 3M™ E-A-Rsoft™ Yellow Neons™ EARfit Probed Test Plug - Large   | 50 pairs                       |                      |       |
|                  |    | 70071515137 | 312-1260    | 3M™ E-A-Rsoft™ FX™ Corded                                      | 2000 pairs                     | 26                   | 5     |
|                  |                                                                                     | 70071515046 | 312-1261    | 3M™ E-A-Rsoft™ FX™ Uncorded                                    | 2000 pairs                     |                      |       |
|                  |                                                                                     | 70071562782 | 393-2004-50 | 3M™ E-A-Rsoft™ FX™ EARfit Probed Test Plug                     | 50 pairs                       |                      |       |
|                  |    | 70071515228 | 312-1219    | 3M™ E-A-R™ Taperfit™ 2 Regular Uncorded                        | 2000 pairs                     | 26                   | 5     |
|                  |                                                                                     | 70071515236 | 312-1221    | 3M™ E-A-R™ Taperfit™ 2 Large Uncorded                          | 2000 pairs                     |                      |       |
|                  |                                                                                     | 70071562808 | 393-2006-50 | 3M™ E-A-R™ TaperFit™ 2 EARfit Probed Test Plug - Regular       | 50 pairs                       |                      |       |
|                  |                                                                                     | 70071733557 | 393-2027-50 | 3M™ E-A-R™ TaperFit™ 2 EARfit Probed Test Plug - Large         | 50 pairs                       |                      |       |
| Push-to-Fit      |  | 70071516002 | 321-2115    | 3M™ E-A-R™ Express™ PodPlugs™ Corded                           | 400 pairs                      | 19                   | 3     |
|                  |                                                                                     | 70071562725 | 393-2008-50 | 3M™ E-A-R™ Express™ PodPlugs™ EARfit Probed Test Plug          | 50 pairs                       |                      |       |
|                  |  | 70071515673 | 318-1002    | 3M™ E-A-R™ Push-Ins™ Uncorded                                  | 2000 pairs                     | 23                   | 4     |
|                  |                                                                                     | 70071515707 | 318-1003    | 3M™ E-A-R™ Push-Ins™ Corded                                    | 2000 pairs                     |                      |       |
|                  |                                                                                     | 70071562766 | 393-2002-50 | 3M™ E-A-R™ Push-Ins™ EARfit Probed Test Plug                   | 50 pairs                       |                      |       |
|                  |  | 70071515640 | P1300       | 3M™ Skull Screws™ Uncorded                                     | 480 pairs                      | 26                   | 5     |
|                  |                                                                                     | 70071515632 | P1301       | 3M™ Skull Screws™ Corded                                       | 480 pairs                      |                      |       |
|                  |                                                                                     | 70071647757 | 393-2012-50 | 3M™ Skull Screws™ EARfit Probed Test Plug                      | 50 pairs                       |                      |       |
|                  |  | 70071515657 | 318-1008    | 3M™ E-A-R™ Push-Ins™ w/ Grip Rings Uncorded                    | 2000 pairs                     | 24                   | 4     |
|                  |                                                                                     | 70071515681 | 318-1009    | 3M™ E-A-R™ Push-Ins™ w/ Grip Rings Corded                      | 2000 pairs                     |                      |       |
|                  |                                                                                     | 70071650298 | 393-2015-50 | 3M™ E-A-R™ Push-Ins™ w/Grip Rings EARfit Probed Test Plug      | 50 pairs                       |                      |       |
|                  |  | 70071515624 | P2000       | 3M™ No-Touch™ Uncorded                                         | 400 pairs                      | 25                   | 4     |
|                  |                                                                                     | 70071515616 | P2001       | 3M™ No-Touch™ Corded                                           | 400 pairs                      |                      |       |
|                  |                                                                                     | 70071650231 | 393-2013-50 | 3M™ No Touch™ EARfit Probed Test Plug                          | 50 pairs                       |                      |       |
| Reusable         |  | 70071515798 | 340-4002    | 3M™ E-A-R™ UltraFit™ Corded with Storage Case                  | 200 pairs                      | 18                   | 3     |
|                  |                                                                                     | 70071515772 | 340-4004    | 3M™ E-A-R™ UltraFit™ Polybag Corded                            | 400 pairs                      |                      |       |
|                  |                                                                                     | 70071562758 | 393-2001-50 | 3M™ E-A-R™ UltraFit™ EARfit Probed Test Plug                   | 50 pairs                       |                      |       |
|                  |  | HC000664777 | 1290        | 1290 Earplugs Corded                                           | 500 pairs                      | 21                   | 3     |
|                  |                                                                                     | HC000664785 | 1291        | 1291 Earplugs Cased Corded                                     | 250 pairs                      |                      |       |
|                  |                                                                                     | 70071675626 | 393-2024-50 | 1290 EARfit ProbedTest Plug                                    | 50 pairs                       |                      |       |
|                  |  | 70071515723 | P3000       | 3M™ Tri-Flange Earplugs Corded                                 | 400 pairs                      | 19                   | 3     |
|                  |                                                                                     | 70071647740 | 393-2011-50 | 3M™ Tri-Flange EARfit Probed Test Plug                         | 50 pairs                       |                      |       |
| Metal Detectable |  | 70071515749 | 340-4007    | 3M™ E-A-R™ UltraFit™ Metal Detectable Corded                   | 400 pairs                      | 18                   | 3     |
|                  |                                                                                     | 70071562758 | 393-2001-50 | 3M™ E-A-R™ UltraFit™ EARfit Probed Test Plug                   | 50 pairs                       |                      |       |
|                  |  | 70071515103 | 311-4106    | 3M™ E-A-Rsoft™ Yellow Neons™ Corded                            | 2000 pairs                     | 23                   | 4     |
|                  |                                                                                     | 70071562741 | 393-2000-50 | 3M™ E-A-Rsoft™ Yellow Neons™ EARfit Probed Test Plug - Regular | 50 pairs                       |                      |       |
| Banded           |  | UU004902688 | 1310        | 3M™ 1310 - When worn behind the neck                           | 10 pairs                       | 13                   | 1     |
|                  |                                                                                     |             |             | 3M™ 1310 - When worn under the chin                            |                                | 18                   | 3     |
|                  |                                                                                     | HC000664835 | 1311        | 3M™ 1311 Replacement Pod                                       | 100 pairs                      |                      |       |
| One Touch        |  | XA007701783 | 1100-BT     | 3M™ 1100 One Touch™ Refill                                     | Pairs/Bottle, 4 x Bottles/Case | 21                   | 3     |
|                  |                                                                                     | 70071515087 | 391-1004    | 3M™ E-A-Rsoft™ Yellow Neons™ One Touch™ Refill                 | Pairs/Bottle, 4 x Bottles/Case | 23                   | 4     |
|                  |                                                                                     | 70071674751 | 390-1012    | 3M™ E-A-Rsoft™ FX™ One Touch™ Refill                           | Pairs/Bottle, 4 x Bottles/Case | 26                   | 5     |
|                  |                                                                                     | 70071674207 | 391-0000    | 3M™ One Touch™ Pro - Earplug Dispenser                         | 1                              |                      |       |

All 3M earplugs are offered corded and most are also offered uncorded.

|                 |                                                                                     | 3M Code     | Model #    | Item Description                                                                            | Qty/Case | SLC <sub>80</sub> dB | Class |
|-----------------|-------------------------------------------------------------------------------------|-------------|------------|---------------------------------------------------------------------------------------------|----------|----------------------|-------|
| PELTOR Earmuffs |    | XA007707947 | X4A        | 3M™ PELTOR™ X Series Headband Earmuffs Light Green                                          | 10       | 31                   | 5     |
|                 |                                                                                     | UU008197848 | X4B        | 3M™ PELTOR™ X Series Neckband Earmuffs Light Green                                          | 10       | 29                   |       |
|                 |                                                                                     | UU010818886 | X4P3GS/E   | 3M™ PELTOR™ X Series Helmet Attach Earmuffs Light Green                                     | 10       | 26                   |       |
|                 |    | XA007707608 | HYX4       | Replacement Hygiene Kit for X4 Earmuff Models                                               | 10       |                      |       |
|                 |                                                                                     | 70071691136 | 393-3005-2 | 3M™ PELTOR™ Earmuff EARfit Probed Test Cushion D                                            | 2 pairs  |                      |       |
|                 |    | XA007707954 | X5A        | 3M™ PELTOR™ X Series Headband Earmuffs Black                                                | 10       | 35                   | 5     |
|                 |                                                                                     | UU010818878 | X5P3GS/E   | 3M™ PELTOR™ X Series Helmet Attach Earmuffs Black                                           | 10       | 31                   |       |
|                 |                                                                                     | XA007707616 | HYX5       | Replacement Hygiene Kit for X5 Earmuff Models                                               | 10       |                      |       |
|                 |                                                                                     | 70071691136 | 393-3005-2 | 3M™ PELTOR™ Earmuff EARfit Probed Test Cushion D                                            | 2 pairs  |                      |       |
|                 |    | 70071730454 | H510A      | 3M™ PELTOR™ Optime™ I Headband                                                              | 10       | 28                   | 5     |
|                 |                                                                                     | 70071730504 | H510F      | 3M™ PELTOR™ Optime™ I Foldable Earmuff                                                      | 10       | 28                   |       |
|                 |                                                                                     | 70071730421 | H510B      | 3M™ PELTOR™ Optime™ I                                                                       | 10       | 25                   | 4     |
|                 |                                                                                     | 70071730496 | H510P3GS/E | 3M™ PELTOR™ Optime™ I Helmet Attach Earmuff                                                 | 10       | 26                   | 5     |
|                 |                                                                                     | XA007707574 | HYX1       | Replacement Hygiene Kit for Optime™ I Series                                                | 10       |                      |       |
|                 |                                                                                     | 70071691110 | 393-3001-2 | 3M™ PELTOR™ Earmuff EARfit Probed Test Cushion B                                            | 2 pairs  |                      |       |
|                 |    | 70071730553 | H520A      | 3M™ PELTOR™ Optime™ II Headband Earmuff                                                     | 10       | 32                   | 5     |
|                 |                                                                                     | 70071730538 | H520F      | 3M™ PELTOR™ Optime™ II Foldable Headband Earmuff                                            | 10       | 32                   |       |
|                 |                                                                                     | 70071730579 | H520FHV    | 3M™ PELTOR™ Optime™ II High Visibility Foldable Headband                                    | 10       | 32                   |       |
|                 |                                                                                     | 70071730546 | H520B      | 3M™ PELTOR™ Optime™ II Neckband Earmuff                                                     | 10       | 27                   |       |
|                 |                                                                                     | 70071730520 | H520P3GS/E | 3M™ PELTOR™ Optime™ II Helmet Attach Earmuff                                                | 10       | 29                   |       |
|                 |    | XA007707582 | HYX2       | Replacement Hygiene Kit for Optime™ II Series                                               | 10       |                      |       |
|                 |                                                                                     | 70071691110 | 393-3001-2 | 3M™ PELTOR™ Earmuff EARfit Probed Test Cushion B                                            | 2 pairs  |                      |       |
|                 |   | 70071730603 | H540A      | 3M™ PELTOR™ Optime™ III Headband Earmuff                                                    | 10       | 33                   | 5     |
|                 |                                                                                     | 70071730629 | H540AHV    | 3M™ PELTOR™ Optime™ III High Visibility Headband                                            | 10       | 33                   |       |
|                 |                                                                                     | 70071730595 | H540B      | 3M™ PELTOR™ Optime™ III Neckband Earmuff                                                    | 10       | 34                   |       |
|                 |                                                                                     | 70071730587 | H540P3GS/E | 3M™ PELTOR™ Optime™ III Helmet Attach Earmuff                                               | 10       | 30                   |       |
|                 |  | XH001659362 | HY54       | Replacement Hygiene Kit for Optime™ III Series                                              | 20       |                      |       |
|                 |                                                                                     | 70071676285 | 393-3004-2 | 3M™ PELTOR™ Earmuff EARfit Probed Test Cushion A                                            | 2 pairs  |                      |       |
|                 |  | XA007703797 | H505B      | 3M™ H505B Welders Earmuff - Neckband                                                        | 10       | 22                   | 4     |
|                 |                                                                                     | UU008049353 | HY220      | 3M™ PELTOR™ Replacement Hygiene Kit                                                         | 20       |                      |       |
|                 |  | XA007702583 | H31P3AF    | 3M™ PELTOR™ H31 Low Profile Series Earmuff for M-100 Series Head Top (M-100 no longer sold) | 1        | 20                   | 3     |
|                 |                                                                                     |             |            | 3M™ PELTOR™ H31 Low Profile Series Earmuff for M-300 Series Head Top                        |          | 25                   | 4     |

E-A-Rfit™ Dual-Ear Validation System

| 3M Code     | Model #  | Item Description                            |
|-------------|----------|---------------------------------------------|
| 70071674116 | 393-1100 | 3M™ E-A-Rfit™ Dual-Ear Validation System    |
| 70071674694 | 073-781  | 3M™ E-A-Rfit™ Dual-Ear, Microphone Assembly |

In Ear Electronic Earplug EARfit Probed Test Plug Range

| 3M Code     | Model #     | Item Description     |
|-------------|-------------|----------------------|
| 70071734431 | 393-2030-50 | 3M™ Skull Screws     |
| 70071734449 | 393-2031-50 | CCCGRM-25            |
| 70071734456 | 393-2032-50 | 3M™ UltraFit™ Small  |
| 70071734464 | 393-2033-50 | 3M™ UltraFit™ Medium |
| 70071734472 | 393-2034-50 | 3M™ UltraFit™ Large  |

