



Automotive Aftermarket Division

3M™ 08984 Adhesive Cleaner

1) Part Numbers

08984 : 1 litre metallic can with pouring system

2) Description and end uses

- To remove adhesive, silicone polish, wax, tar, oil, etc.
- As thinner for some adhesives

Major product features:

- Can be used on all surfaces
- General purpose cleaner
- Will not harm dry paint
- Dry wiping not needed
- Slow drying properties allows efficient cleaning on all adhesives build up
- Clean work because of the plastic dispensing system, which avoids waste.

3) Physical Properties

Base	Mixture of petroleum distillates - Liquid
Colour	Transparent
Storage conditions	Cool dry place. Best results are obtained when material is stored and applied at room temperature, 15 to 30°C. Storage temperature must not exceed 50°C.
Shelf life	4 years from date of manufacture under normal storage conditions.

4) Directions for Use

- To open: Put finger through the ring and pull to remove.
- Apply the required quantity on a clean rag by using the special plastic pourer, and wipe off area.

Caution:

- Don't use any cleaner on fresh or uncured paint
- Flammable product



5) Storage

Store at room temperature in flammables storage area. Rotate stock on a “first-in-first-out” basis. When stored at the recommended conditions in original, unopened containers, this product has a shelf life see container for details. Use in a well-ventilated area.

6) Safety

Please refer to the Material Safety Data Sheet or contact your local 3M™ Toxicology Department.

3M™ 08984 Adhesive Cleaner is designed FOR PROFESSIONAL USE ONLY.

7) Disclaimer

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 21/02/2024 Supersedes: 18/08/2020

For Additional Health and Safety Information

<p>3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk</p>	<p>3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk</p>
<p>3M Finland, Suomen 3M Oy Autotuotteet Keilaniementie 1 02151 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet</p>	<p>3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad</p>	<p>3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto</p>
<p>3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv</p>	<p>3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee</p>	<p>3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt</p>

© 3M 2023. 3M is a trademark of the 3M company. All rights reserved