



Technical Data Sheet

3M™ Velvet Textured Polycarbonate Overlaminating Film 7737FL



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

3M™ Velvet Textured Polycarbonate Overlaminating Film 7737FL utilizes velvet textured polycarbonate film to achieve a decorative velvet appearance. 3M™ Adhesive 400 offers low temperature performance and long term aging for resistance to yellowing in outdoor applications.

Product Features

- Velvet textured polycarbonate overlaminate offers the opportunity to achieve the attractive appearance of a subsurface screen printed nameplate with an economical overlaminate construction which can create looks that are unique.
- Film liner offers graphic appearance when overlaminating metallized or darker surfaces.
- UL Recognized file MH11410

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Value
Adhesive Type	#400 Acrylic
Facestock	Velvet Clear Lexan
Adhesive Coat Weight	1.05 — 1.65 g/100 in ²

Attribute Name	Value
Adhesive Thickness	0.02 mm (0.8 mil)
Facestock Thickness	0.08 mm (3 mil)
Liner	Clear Polyester
Liner Thickness	0.038 mm (1.5 mil)

Attribute Name	Value
Convertability	Low temperature, high clarity 3M™ Acrylic Adhesive 400 is specifically designed to be compatible with a variety of print methods and overlaminate applications. When converting labels for thermal transfer applications, care should be taken with regard to proper roll tensions, handling and storage conditions.

Typical Performance Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Dwell Time	Substrate	Value
180° Peel Adhesion	ASTM D3330	10 min	Stainless Steel	4.2 N/cm (38 oz/in) ¹
Liner Release	TLMI			1 — 10.8 ²

¹ 300 mm/min (12 in/min)

² 180° removal, 300 in/min

Attribute Name	Value
Minimum Application Temperature	-12 °C (10 °F)
Long Term Temperature Resistance	121 °C (250 °F) ¹
Minimum Long Term Temperature Resistance	-40 °C (-40 °F) ¹

¹ Long Term (day, weeks)

Attribute Name	Value
Note	Calipers are nominal values

Typical Environmental Characteristics

Chemical and Environmental Exposure

Samples were applied to stainless steel panels and allowed to dwell for 24 hours prior to exposures.

Liquid Dwell Time/Exposure Condition Results

Isopropyl Alcohol @ Room Temperature 4 hours Good appearance - 1/16" edge penetration

5% Sulfuric Acid @ Room Temperature 4 hours Good appearance - no edge penetration

Engine Oil @ 250°F (121°C) 4 hours Good appearance - no edge penetration

Water @ Room Temperature 24 hours Good appearance - edge penetration

Humidity Resistance

1 day at 95°F (35°C) and 95% relative humidity: no change

Temperature Resistance

-40°F (-40°C) to 250°F (121°C) for 1 day: no change

Printing

This film is not treated for printability.

Handling/Application Information

Application Techniques

For maximum bond strength, the surface should be clean and dry. A typical cleaning solvent is heptane or isopropyl alcohol.*

For best bonding conditions, application surfaces should be at room temperature or slightly higher. Low temperature surfaces, below 50°F (10°C), cause the adhesive to become firm and will not allow the adhesive to flow and develop intimate contact with the substrate.

*Note: When using solvents, read and follow the manufacturer's precautions and directions for use.

Industry Specifications

UL Recognized, File PGGU2.MH11410, Marking & Labeling System Materials - Component, ANSI/UL 969

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 12 months from date of manufacture.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company.
©3M 2025 (4/25)