

Product Description

Product Features

- 3M™ Protection Wrap Film combines vehicle customization with durable protection against rock chips, scratches and stains
- Create full color change or personalize with accents or partial wraps with nearly 25 premium colors, including gloss and matte finishes, flips and textures
- At least 70% thicker than typical vinyl films, providing long-lasting protection
- Mirror-like finish that looks like paint
- Dry installation method that's two times faster end to end than wet-applied PPF*
- Wet installation method that allows for the repositioning, precise alignment, and workflow familiar to paint protection film installers
- Both the wet and dry method can be used in a single installation, allowing installers to customize their installation experience based on the material, surface, and installation environment
- Cold stretch capabilities make it highly conformable in deep recesses with minimal heat
- 3M™ Controltac™ Film Technology and 3M™ Comply™ Adhesive Technology
 - 3M™ Controltac™ Film Technology minimizes the adhesive's initial contact area for easy sliding, tacking, snap-up, and repositioning.
 - 3M™ Comply™ Adhesive Technology allows air to exit through air release channels to the edge of the film for fast, easy, bubble-free installations.
- Self-healing polymer technology allows minor scratches to disappear with heat applied to the film
- Approved for use with 3M™ Knifeless™ Tape Precision Line and Design Line (for dry installation method only)
- 10-year consumer warranty for vehicle applications†
- 3-year consumer warranty for watercraft applications†

* When compared to Scotchgard™ Paint Protection Film Pro Series 200.

† Ask a 3M authorized installer or see the warranty card for complete details.

NOTE

All installations should be conducted by a professional installer.

NOTE

Mist the liner and cap sheet with water to help reduce static.

Recommended Types of Films and End Uses

- Standard vehicle films, including solid color, detailing, decoration
- Personal watercraft (when applied above the static water line)

Coverage Options

Packages	Accents	Partial Coverage	Full Vehicle Coverage	Watercraft Coverage
Coverage	Gas cap, rocker panels, racing stripes, chrome delete, etc.	Hood or roof examples	Complete color change	Above the static water line
Coverage Illustration				

Characteristics

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Physical Characteristics

Characteristic	Value
Material	Polyurethane
Thickness	Film with adhesive: 7.5 mil to 9 mil (0.19 mm to 0.23 mm), depending on color Release liner: 6.4 mil (0.16 mm) Cap sheet: 2.0 mil (0.05 mm)
Adhesive	Pressure-sensitive adhesive, repositionable with air release channels
Adhesive Color	Clear
Typical Adhesion 20 Minutes After Application	Painted panel: 2.1 lbf/in. (3.7 N/cm)
Protective Cap Sheet	Clear polyester
Liner	Polyethylene-coated PET
Flammability	Flammability standards are different from country to country. Contact a local 3M representative for details.

Application Characteristics

Characteristic	Value
Substrate Type	Painted surfaces*
Application Temperature	60°F to 85°F However for optimal application, 3M recommends installing at 65°F to 75°F (18.3°C to 23.9°C).
Application Method	Wet or Dry (See the 3M™ Protection Wrap Film Installation Guide)

* Check the film's adhesion to powder-coated or water-based paints.

NOTE

This film is NOT recommended for use on stainless steel substrates, nor warranted for stainless steel applications. Contact a 3M sales representative for information about more appropriate products.

Factors Affecting Performance Life

The actual performance life of a protection wrap is affected by:

- Selection and preparation of the substrate
- Surface texture
- Application methods
- Angle and direction of sun exposure
- Environmental conditions
- Cleaning and maintenance methods

Installation Over Vehicle Sensors, Radar, and Autonomous Equipment

It is the vehicle owner's and/or vehicle manufacturer's responsibility to validate the compatibility of 3M™ Protection Wrap Film with any and all sensors or like equipment prior to installation. In order to ensure such equipment functions properly, 3M recommends users NEVER apply film over such equipment. Always test and confirm an installation does NOT create signal disruptions or loss of functionality prior to full adoption.

Application and Installation

In addition to other 3M bulletins specified in this document, the following bulletins provide details users may need to successfully apply a film.

- [3M™ Vehicle Prep for Success Guide](#)
- [3M™ Protection Wrap Film Installation Guide](#)
- [3M™ Protection Wrap Film Vehicle Maintenance FAQ](#)

Pressure-activated Adhesive

The pressure activated adhesive on this film offers:

- smooth sliding into position on a substrate;
- fast finger tacking to check positioning; and
- easy snap-up and repositioning when you need it.

The **snap-up and reposition feature is lost:**

- when firm pressure with a squeegee or other application tool is applied;
- at application temperatures above 100°F (38°C) even if only light finger pressure was used for tacking; or
- if any part of the film is removed from the original liner and reapplied to the same or another liner.

Working with Non-Visible Air Release Channels

Air release channels are a characteristic of films with 3M™ Comply™ Adhesive Technology, allowing trapped air to exit through the edges of the film.

- The channels will be damaged if installers remove and attempt to change liners or reapply the same liner.
- For the best results, always work from the center of a film out to the edges to allow trapped air to escape.

Maintenance and Cleaning

Detailed vehicle maintenance and cleaning instructions are specified in the [3M™ Protection Wrap Film Vehicle Maintenance FAQ](#).

- The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 6 and 8 (neither strongly acidic nor strongly alkaline).
- 3M™ Perfect-It™ Show Car Paste Wax (PN39526) can be applied after film installation. Users must then regularly wash and recoat the surface going forward.
- Alternatively, 3M™ Ceramic Coating (PN 39901) or 3M™ Ceramic Boost (PN39905) can be applied for additional hydrophobicity, stain resistance, and easy clean features.
- Do NOT use waxes containing dyes, abrasive polishes, and/or rubbing compounds. The abrasive particles will damage the film surface and result in a loss of surface quality.

Removal

3M recommends hiring an installation professional for the removal process. Use a heat gun or steamer to aid removal. Remove the film at a 30 to 60 degree angle relative to the surface of the paint.

Shelf Life and Storage

Shelf Life

The shelf life is an indicative and maximum data, subject to many external and non-controllable factors. It may NEVER be interpreted as a warranty. The shelf life is three years from the date of manufacture on the original box.

Storage Conditions

- 60°F to 85°F (16°C to 30°C)
- Out of sunlight
- Clean, dry area
- Original container
- Bring the film to room temperature before use
- Unused portions of a roll should be taped tightly and stored horizontally
- See FAQs for additional storage considerations

Health and Safety

Chemicals

When handling any chemical products, read the manufacturers' container labels and the safety data sheets (SDS) for important health, safety, and environmental information.

[Follow this link to obtain SDS sheets for 3M products.](#)

[Follow this link to obtain information about substances of very high concern \(SVHC\) for EU products.](#)

Tools and Equipment Usage

When using any equipment, always follow the manufacturer's instructions for safe operation.

Warranty Information

Technical Information

Technical information, guidance, and other statements provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license to any intellectual property rights is granted or implied with respect to this technical information.

Product Selection and Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment, reviewing all applicable regulations and standards, and reviewing the product label and use instructions. Failure to properly evaluate, select, and use a 3M product in accordance with instructions or to meet all applicable safety regulations may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer

Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Commercial Branding and Transportation

3M Center, Building 223-3N-30
St. Paul, MN 55144

1-800-328-1684
3M.com/protectionwrapfilm

© 3M 2026. All rights reserved.
3M, Comply, Controltac, Knifeless, and Perfect-It are trademarks of 3M.
Used under license in Canada.
All other trademarks are property of their respective owners.
Revision D, August 2026 Please recycle.

