



Technical Data Sheet

3M™ Screen Printable Sheet Polyester Label Material 7980



[Product Details](#)

Product Description

3M™ Screen Printable Sheet Polyester Label Material 7980 is a durable, high performance material that offers excellent thermal stability, moisture resistance and chemical resistance. This material utilizes 3M™ Adhesive 300, which has excellent quick tack and also bonds well to a variety of surfaces including LSE plastics.

Product Features

- Matte coating is compatible with screen printing and resists degradation from scuffing, chemicals, moisture, and wide temperature fluctuations. Variable information can be added by the end user, as the material is dot matrix printable and hand writable.
- 3M adhesive 300 bonds well to a wide variety of substrates including metals, high surface energy (HSE) plastics and low surface energy (LSE) plastics. It is ideal for applications requiring high initial adhesion especially to LSE plastic surfaces.
- Liner provides easy sheet processing and is designed for layflat. The backside of the liner is not printable.
- UL recognized (File MH11410) and CSA accepted (File 99316). See the UL and CSA listings for details.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Value
Adhesive Type	300 Acrylic
Facestock	White Polyester Matte TC
Adhesive Coat Weight	1.21 — 1.49 g/100 in ²

Attribute Name	Value
Adhesive Thickness	0.02 mm (0.8 mil)
Facestock Thickness	0.058 mm (2.3 mil)
Liner	90# Polycyd. bleached kraft sheet polyethylene coated on two sides
Liner Thickness	0.17 mm (6.7 mil)

Attribute Name	Value
Convertability	3M™ High Strength Acrylic Adhesive 300 is designed to be compatible with a variety of print methods and end use applications. Due to the quick flowing aggressive nature of this adhesive, care should be taken when converting labels for thermal transfer applications. Please refer to the die cutting/converting section of this data page or the “Guide to Converting and Handling Label Products” technical bulletin for additional information.

Typical Performance Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Liner Release	TLMI	10 — 60 g/2 in ¹

¹ 180° removal, 300 in/min

Attribute Name	Value
Minimum Application Temperature	10 °C (50 °F)
Long Term Temperature Resistance	149 °C (302 °F) ¹
Minimum Long Term Temperature Resistance	-40 °C (-40 °F) ¹

¹ Long Term (day, weeks)

180° Peel Adhesion

Temperature: 23 °C (73 °F)

Dwell Time: 72 h

Test Method: ASTM D3330

Substrate	Value
Polycarbonate (PC)	6.7 N/cm (61 oz/in) ¹
Polypropylene (PP)	6.1 N/cm (56 oz/in) ¹
Stainless Steel	7.3 N/cm (67 oz/in) ¹

¹ 304 mm/min (12 in/min)

Attribute Name	Value
Note	Calipers are nominal values

Typical Environmental Characteristics

Humidity Resistance

24 hours at 100°F (38°C) and 100% relative humidity: no significant change in appearance or adhesion

Temperature Resistance

300°F (149°C) for 24 hours: no significant visual change

-40°F (-40°C) for 10 days: no significant visual change

Printing

Material has a topcoating which is receptive to many inks including UV and conventional ink systems. The converter should verify that their ink systems are compatible with the topcoating on the polyester film by testing beforehand.

The topcoating is also receptive to other forms of printing including hot stamping and dot matrix printing. The converter should verify that the method of printing is compatible with the topcoating by testing beforehand.

The following dot matrix ribbons are recommended for use with this material:

- CGL-79 from Mid City Columbia, 800-462 or 800-996-4656
 - Ranger 288 from Herbert Dehinton & Co., 847-998-8150
- 3M does not recommend the Ranger 288 ribbon for bar code printing.

Converting

Die cut with steel rule or flatbed dies. The 90# lay-flat liner also allows kiss cutting and back splitting. The converter can cut through the polyester facestock without cutting through the liner. Sheet label materials are not recommended for rotary die cutting and stripping operations.

Handling/Application Information

Application Examples

- Barcode labels and rating plates.
- Property identification and asset labeling.
- Warning, instruction, and service labels for durable goods.
- Nameplates for durable goods.

Application Techniques

For maximum bond strength, the surface should be clean and dry. Typical cleaning solvents are heptane and isopropyl alcohol.*

For best bonding conditions, application surface should be at room temperature or higher. Low temperature surfaces, below 50°F (10°C), can cause the adhesive to become so firm that it will not develop maximum contact with the substrate. Higher initial bonds can be achieved through increased rubdown pressure.

*When using solvents, read and follow the manufacturer's precautions and directions for use.

Industry Specifications

UL Recognized (File MH11410)
CSA Accepted (File 99316)

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Packaging	Finished labels should be stored in plastic bags.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company.
Alconox is a registered trademark of Alconox, Inc.
409 is a registered trademark of Clorox.
©3M 2024 (9/24)