



# Technical Data Sheet

## 3M™ Thermal Transfer Polyester Label Material 7831



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

3M™ Thermal Transfer Polyester Label Materials are thin profile, gloss polyester label stocks that offer excellent durability and moisture resistance. These label materials utilize 3M™ Adhesive 400 which is designed to offer good peel strength to a variety of surfaces, as well as, excellent clarity and UV resistance.

### Product Features

- Facestock is topcoated for thermal transfer printing. Resin ribbons are recommended for optimum durability. The topcoat also provides improved ink anchorage for traditional forms of press printing.
- 3M adhesive 400 offers excellent low temperature performance and peel adhesion to a wide variety of substrates. It has excellent long term aging that resists yellowing.
- 55# densified kraft liner assures consistent die cutting.
- UL recognized (File MH11410) and CSA accepted (File 99316). See the UL and CSA listings for details.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Physical Properties

Attribute Name	Value
Adhesive Type	400 Acrylic
Facestock	Clear Polyester Gloss TC
Adhesive Coat Weight	1.08 — 1.62 g/100 in <sup>2</sup>

Attribute Name	Value
Adhesive Thickness	0.02 mm (0.8 mil)
Facestock Thickness	0.025 mm (1 mil)
Liner	55# Densified kraft
Liner Thickness	0.081 mm (3.2 mil)

Attribute Name	Value
Convertability	Low temperature, high clarity 3M™ Acrylic Adhesive 400 is specifically designed to be compatible with a variety of print methods and overlaminate applications. When converting labels for thermal transfer applications, care should be taken with regard to proper roll tensions, handling and storage conditions. Please refer to the die cutting/converting section of this data page or the “Guide to Converting and Handling Label Products” technical bulletin for additional information.

## Typical Performance Characteristics

### 180° Peel Adhesion

Temperature: 23 °C (73 °F)

Dwell Time: 72 h

Test Method: ASTM D3330

Substrate	Value
Polycarbonate (PC)	4.3 N/cm (39 oz/in) <sup>1</sup>
Polypropylene (PP)	3.2 N/cm (29 oz/in) <sup>1</sup>
Stainless Steel	4.5 N/cm (41 oz/in) <sup>1</sup>

<sup>1</sup> 300 mm/min (12 in/min)

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Liner Release	TLMI	2 – 13.7 <sup>1</sup>

<sup>1</sup> 180° removal, 300 in/min

Attribute Name	Value
Minimum Application Temperature	-12 °C (10 °F)
Long Term Temperature Resistance	121 °C (250 °F) <sup>1</sup>
Minimum Long Term Temperature Resistance	-51 °C (-60 °F) <sup>1</sup>

<sup>1</sup> Long Term (day, weeks)

Attribute Name	Value
Note	Calipers are nominal values

## Typical Environmental Characteristics

### Humidity Resistance

24 hours at 100°F (38°C) and 100% relative humidity: no significant change in appearance or adhesion

### Temperature Resistance

300°F (149°C) for 24 hours: no significant visual change

-40°F (-40°C) for 10 days: no significant visual change

## Printing

Facestock is topcoated for improved ink receptivity and is designed for thermal transfer printing. It is printable by standard roll processing methods including flexography, hot stamp, letterpress, and screen printing.

UL Recognized thermal transfer ribbons

**Advent:**301 Black; 303 Black; 501 Black; 501 Red; 501 Blue; 501 Green

**Armor:**AXR-7; AXR-7+; AXR-600

**Astromed:**R5

**CP:**5440 Red; 5640 Blue; 5940 Black

**Dasco:**DR-74; DR-84

**Great Ribbon:**SDR

**ICS:**ICS-CC-4099.1

**limak:**SH-36; SP-330; PrimeMark

**Intermec:**053258-2; 054048-4

**Japan Pulp and Paper:**JP Resin 1; JP Resin 2 Blue; JP Resin 2 Red (suitable for indoor use only); JP Resin 2 Green (suitable for indoor use only)

**Kurz:**K500; K501

**Markem:**716 (suitable for indoor use only)

**Mid City Columbia:**CGL-80; CGL-80HE

**NCR:**Matrix Resin; Matrix; PaceSetter; Promark II; Ultra V

**Pelikan:**T016

**Ricoh:**B110A; B110C; B110CX

**Sato:**Premier 1

**Sony:**4070; 4072; 4075; 4085; 5070; Signature Series Resin; Signature Series Wax

UBI:HR03; HR04  
Zebra:5095; 5099; 5100; 5175

## Converting

Rotary die cutting is recommended. Fanfolding of labels is not recommended. Small labels should be evaluated carefully. Winding tensions should be kept at a minimum to help prevent the adhesive from oozing.

## Handling/Application Information

### Application Examples

- Barcode labels and rating plates.
- Property identification and asset labeling.
- Warning, instruction, and service labels for durable goods.
- Nameplates and durable goods.

### Application Techniques

For maximum bond strength, the surface should be clean and dry. Typical cleaning solvents are heptane and isopropyl alcohol.\*

For best bonding conditions, application surface should be at room temperature or higher. Low temperature surfaces, below 50°F (10°C), can cause the adhesive to become so firm that it will not develop maximum contact with the substrate. Higher initial bonds can be achieved through increased rubdown pressure.

\*When using solvents, read and follow the manufacturer's precautions and directions for use.

## Industry Specifications

UL Recognized (File MH11410)  
CSA Accepted (File 099316)

## Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## Available Sizes

Attribute Name	Value
Packaging	Finished labels should be stored in plastic bags.

## Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
3M.com/iatd

3M is a trademark of 3M Company.  
Alconox is a registered trademark of Alconox, Inc.  
409 is a registered trademark of Clorox.  
©3M 2025 (4/25)