



# Technical Data Sheet

## 3M™ Performance Paper Label Material 7000



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

3M™ Performance Paper Label Material provides resistance to flapping on small diameter vials. These label materials utilize 3M™ High Precision Acrylic Adhesive 320, which provides firmness and strength on a variety of surfaces including high surface energy (HSE) and low surface energy (LSE) plastics, as well as, metals.

### Product Features

- Facestock is designed for traditional forms of press printing and write-on variable information.
- Designed to survive autoclaving, ETO and gamma sterilization while adhered to most surfaces.
- Meets many pharmaceutical industry or manufacturer specifications.
- 3M™ Performance Paper Label Material 7000 utilizes a 43# Densified Kraft liner that help improve application accuracy due to liner release consistency.
- Application rates up to 250 containers per minute.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Physical Properties

Attribute Name	Value
Adhesive Type	320 Acrylic
Adhesive Coat Weight	1.24 — 1.65 g/in <sup>2</sup>
Facestock	60# High Gloss Kromekote™

Attribute Name	Value
Adhesive Thickness	0.023 mm (0.9 mil)
Facestock Thickness	0.102 mm (4 mil)
Liner	43# Densified Kraft
Liner Thickness	0.064 mm (2.5 mil)

Attribute Name	Value
Convertability	The high tenacity of 3M™ Specialty Acrylic Adhesive 320 is specifically designed to be compatible with flexographic and thermal transfer technologies. Its aggressive tack properties, while desirable for the end use application, may require extra care during processing. Please refer to the die cutting/converting section of this data page or the “Guide to Converting and Handling Label Products” technical bulletin for additional information.

## Typical Performance Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Liner Release	TLMI	5 — 55 g/2 in <sup>1</sup>

<sup>1</sup> 180° removal, 300 in/min

Attribute Name	Value
Minimum Application Temperature	10 °C (50 °F)
Long Term Temperature Resistance	121 °C (250 °F) <sup>1</sup>
Minimum Long Term Temperature Resistance	-40 °C (-40 °F) <sup>1</sup>

<sup>1</sup> Long Term (day, weeks)

### 180° Peel Adhesion

Temperature: 23 °C (73 °F)

Dwell Time: 72 h

Test Method: ASTM D3330

Substrate	Value
Polypropylene (PP)	*Delaminated N/cm <sup>1</sup>
Stainless Steel	*Delaminated N/cm <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

Attribute Name	Value
Note	Calipers are nominal values (*The adhesion to the substrate is higher than the internal strength of the paper resulting in delamination or paper tear upon removal. )

## Typical Environmental Characteristics

### Temperature Resistance

250°F (121°C) for 24 hours: slight yellowing

-40°F (-40°C) for 24 hours: no significant visual change

### Sterilization Process

Specifically designed for excellent flagging resistance on small diameter glass vials following steam autoclave, gamma or ethylene oxide sterilization.

## Printing

Facestock is press printable with traditional flexographic process and thermal transfer printable with high-quality thermal transfer ribbons. Whenever printing for the first time, with a different ink system or on a new machine, we strongly recommend carrying out proofing trials to validate ink adhesion and durability prior to a full production run.

## Converting

Rotary die cutting is recommended. Fanfolding labels is not recommended. Small labels should be evaluated carefully. Winding tensions should be kept at a minimum to prevent the adhesive from oozing.

## **Handling/Application Information**

### **Application Examples**

- Pharmaceutical labeling.
- Barcode labels and rating plates.
- Property identification and asset labeling.

### **Application Techniques**

- For maximum bond strength, surface should be thoroughly cleaned and dried. A typical cleaning solvent is heptane or isopropyl alcohol. Note: Follow the manufacturer's precautions and directions for use when using solvents.
  - For best bonding conditions, application surface should be at room temperature or higher. Low temperature surfaces, below 40°F (5°C), cause the adhesive to become firm and will not allow the adhesive to flow and develop intimate contact with the substrate.
  - Higher initial bonds can be achieved through increased rubdown pressure. Use a rubber roller with maximum hand pressure for best results.
- \*Note: When using solvents, read and follow the manufacturer's precautions and directions for use.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes**

<b>Attribute Name</b>	<b>Value</b>
Packaging	To minimize the effects of humidity, the product should be stored in plastic bags. Low density polyethylene (2 - 4 mils) can help prevent humidity penetration and stabilize the moisture content.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3m.com](http://www.3m.com).

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division  
3M Center, St. Paul, MN 55144-1000  
[3M.com/iatd](http://3M.com/iatd)

3M is a trademark of 3M Company.  
Kromekote is a trademark of SMART Papers.  
ALCONOX is a registered trademark of Alconox, Inc.  
©3M 2024 (9/24)