










# Seam Sealing – the Choice is Yours



## Replication of OEM Seams Made Easy



2K Tips for 2K Cartridges and 1K Flex Packs					1K Tips for 1K Cartridges									
Nozzle	Product Recommendations			Applicator		Nozzle	Product Recommendations			Applicator				
<b>3M™ OEM Match Sprayable 2K Tip</b>					<b>3M™ OEM Match Sprayable 1K Tip</b>									
	○ 08524	3M™ OEM Match Epoxy Seam Sealer, 200 ml Cartridge		33999	3M™ OEM Match Air Supply Kit		● 08374	3M™ MSP Sprayable Seam Sealer, 310 ml Cartridge		33999	3M™ OEM Match Air Supply Kit			
	● 08526			3M™ NVH Dampening Material, 200 ml Cartridge								09930	3M™ Performance Pneumatic Applicator	
	● 08522											3M™ Flexible Package Applicator - Pneumatic	08193	3M™ Static Mixing Nozzle
	● 08528													
	● 04274	3M™ MSP Seam Sealer, 310 ml Flexpack		08399	3M™ Flexible Package Applicator - Pneumatic							39000	3M™ Single Cartridge Applicator	
	○ 08369			3M™ OEM Match Air Supply Kit	33999									3M™ OEM Match Air Supply Kit
	● 08370													

3M™ OEM Match Adjustable Ripple Tip 2K					3M™ OEM Match Ripple 1K Tip									
	○ 08524	3M™ OEM Match Epoxy Seam Sealer, 200 ml Cartridge		09930	3M™ Performance Pneumatic Applicator		● 08362	3M™ Urethane Seam Sealer, 310 ml Cartridge		39000	3M™ Single Cartridge Applicator			
	● 08526			3M™ Urethane Seam Sealer, 310 ml Flexpack								08193	3M™ Static Mixing Nozzle	
	● 08522											3M™ Flexible Package Applicator - Pneumatic	08194	3M™ MSP Sprayable Seam Sealer, 310 ml Cartridge
	● 08528													
	○ 08360	3M™ MSP Seam Sealer, 310 ml Flexpack		08206	3M™ OEM Seam Sealer Tip Adapter		08374	3M™ MSP Sprayable Seam Sealer, 310 ml Cartridge						
	● 08361			3M™ OEM Match Air Supply Kit	08399				3M™ OEM Match Air Supply Kit					
	● 08364									08206	3M™ OEM Seam Sealer Tip Adapter			

3M™ OEM Match Wing Nozzle 2K Tip					3M™ OEM Match Wing Nozzle 1K Tip									
	○ 08524	3M™ OEM Match Epoxy Seam Sealer, 200 ml Cartridge		09930	3M™ Performance Pneumatic Applicator		● 08362	3M™ Urethane Seam Sealer, 310 ml Cartridge		39000	3M™ Single Cartridge Applicator			
	● 08526			3M™ Factory-Match Seam Sealer, 200 ml Cartridge								08193	3M™ Static Mixing Nozzle	
	● 08522											3M™ EZ Sand Multi Purpose Repair Material, 200 ml Cartridge	08194	3M™ Flexible Package Applicator - Pneumatic
	● 08528													
	● 08323	3M™ Urethane Seam Sealer, 310 ml Flexpack		08206	3M™ OEM Seam Sealer Tip Adapter		08374	3M™ MSP Sprayable Seam Sealer, 310 ml Cartridge						
	● 05887			3M™ OEM Match Air Supply Kit	08399				3M™ OEM Match Air Supply Kit					
	○ 08360									08206	3M™ OEM Seam Sealer Tip Adapter			

3M™ OEM Match Wide Stream 2K Tip					3M™ OEM Match Wide Stream 1K Tip									
	○ 08524	3M™ OEM Match Epoxy Seam Sealer, 200 ml Cartridge		09930	3M™ Performance Pneumatic Applicator		● 08362	3M™ Urethane Seam Sealer, 310 ml Cartridge		39000	3M™ Single Cartridge Applicator			
	● 08526			3M™ Factory-Match Seam Sealer, 200 ml Cartridge								08193	3M™ Static Mixing Nozzle	
	● 08522											3M™ EZ Sand Multi Purpose Repair Material, 200 ml Cartridge	08194	3M™ Flexible Package Applicator - Pneumatic
	● 08528													
	● 08323	3M™ Self Leveling Seam Sealer, 200 ml Cartridge		08206	3M™ OEM Seam Sealer Tip Adapter		08374	3M™ MSP Sprayable Seam Sealer, 310 ml Cartridge						
	● 05887			3M™ OEM Match Air Supply Kit	08399				3M™ OEM Match Air Supply Kit					
	○ 08307									08206	3M™ OEM Seam Sealer Tip Adapter			

\*Pressure, speed, and angle of application will cause bead texture to vary.

