

3M DI-NOC™ Architectural Finishes

Standard Products

Oxidized Metal	Black Iron	Premium Metal	Metallic Palette	Metal
Stone	Concrete	Mortar	Fresco	Stucco
Terracotta	Ceramic	Brick	Tiled Design	Leather
Suède	Textile	Abstract	Carbon	Premium Wood
Dry Wood	Plank Design	Chipboard	Metallic Wood	Fine Wood
Wood Grain Palette	Wood Grain	Wood Grain Gloss	Solid Color	

Functional Products

Abasion Resistant	Exterior	Tile	Whiteboard Film	Glass Finishes
-------------------	----------	------	-----------------	----------------

E-Series

RC Recycled Content* Film	PO Polyolefin Film
---------------------------	--------------------

Ready to create
your masterpiece?

See and feel our surface finishes.
Request for your free sample.

[Request a Sample ▶](#)

Have questions or need help in
choosing the right surface finishes?

[Contact a 3M Expert ▶](#)

2024

* E-Series Recycled Content Film has a base film layer made with 80% post-consumer recycled polyester and a colored layer made with 20% scallop shell powder as a bio-based filler.



3M™ DI-NOC™

Architectural Finishes

2024

Design Description Guide



- ① — WG-960
- ② —  — ②
- ③ —  — WG-960EX




WG-960EX

Series | Number | Suffix for product types






- ① Standard series description
- ② Supplementary information icon
- ③ Functional / other series icon and design description

Standard and Functional / other series have a similar appearance but are not identical.

Supplementary Information Icon List

- A/NZ** Curated for Australia and New Zealand environments. Readily available from your local stockist.
- NEW** New design
- H** Horizontal woodgrain
- MT** Matte design
-  DO NOT apply to 3D compound curved surfaces
-  Use caution when applying to 3D compound curved surfaces to prevent damage to product
-  Manufactured to order item
- W** Wiping Woodgrain : Film surface has a special treatment. DO NOT use double-cut seams

Functional / other Series Icon List

-  **EX Series :** for exterior applications
-  **AR Series :** for high traffic applications
-  **DG Series :** for applications behind glass
-  **TIL Series:** for application to tile
-  **E-Series PO Polyolefin Film**

WHAT IS A MASTERPIECE?

A masterpiece improves the lives of all who experience it.

They are the objects of beauty inspired by nature and materials at hand — wood, textile, stone, leather, metal — and are limited only by the imagination of the master. 3M™ DI-NOC™ Architectural Finishes bring you the beauty of hundreds of natural elements with additional designs to inspire your masterpiece. We use advancements in science, so you can capture the world's natural beauty without sacrificing your creative ideals.

We're not only inspired by nature, but we strive to protect it by challenging ourselves to develop more sustainable solutions without sacrificing on beauty. Our latest innovations contain select designs with a release liner made from 40% recycled paper content and new earth tone designs made in part from crushed seashells and post-consumer recycled polyester. With 3M™ DI-NOC™ Architectural Finishes, you can create a stunning new space quickly and easily, extending the life of fixtures or breathe new life into an existing space almost overnight. The non-porous surface of DI-NOC™ Architectural Finishes is not just beautiful, but easy to maintain, clean and disinfect. There are no boundaries. No limits. Only your imagination. Create your masterpiece.





Contents

Functional Products :

- 6 Abrasion Resistant
- 8 Exterior
- 10 Tile
- 12 Whiteboard Film
- 13 Glass Finishes

E-Series :

- 15 PO Polyolefin Film
- 18 RC Recycled Content* Film

Standard Products :

- 20 Oxidized Metal
- 24 Black Iron
- 26 Premium Metal
- 28 Metallic Palette
- 30 Metal
- 32 Stone
- 36 Concrete / Mortar
- 40 Fresco / Stucco
- 42 Terracotta / Ceramic
- 44 Brick / Tiled Design
- 46 Leather / Suède
- 48 Textile
- 50 Abstract / Carbon
- 54 Premium Wood
- 56 Dry Wood
- 60 Plank Design / Chipboard
- Metallic Wood
- 62 Fine Wood
- 71 Wood Grain Palette
- 72 Wood Grain
- 74 Wood Grain Gloss
- 76 Solid Color

*E-Series Recycled Content Film has a base film layer made with 80% post-consumer recycled polyester and a colored layer made with 20% scallop shell powder as a bio-based filler.





Do more with your designs

- 1 PW-2305MT
- 2 DW-1883MT
- 3 AE-2154
- 4 SU-2234MT
- 5 ME-388
- 6 ME-2025 / AE-2162MT /
ME-1225
- 7 VM-1694
- 8 Special design
- 9 ME-2558






AR Series Abrasion Resistant


Excellent Abrasion Resistance

Standard 3M™ DI-NOC™ Architectural Finishes provide good abrasion resistance in most applications. For areas that experience heavier wear and tear, we recommend our AR Series Abrasion Resistant, which is a great solution with excellent surface abrasion resistance and scratch resistance. This allows the finish to maintain its aesthetic appearance, ultimately extending the lifespan of the space.























































ME-2297AR **NEW**

◀ Try scratching the surface with a coin.



Even after scratching, AR Series remains intact and maintains its aesthetic appearance.

 FW-1138AR A/NZ	 FW-1129AR A/NZ	 FW-1293AR	 FW-236AR (AR-1119) A/NZ	 FW-1280AR A/NZ	 FW-233AR	 FW-625AR (AR-1120)		
 FW-7017AR (AR-1664)	 FW-1122AR A/NZ	 FW-337AR A/NZ	 FW-7011AR	 FW-1294AR A/NZ	 FW-1022AR A/NZ	 FW-338AR		
 BW-1310AR NEW	 ME-1467AR	 ME-433AR	 ME-432AR A/NZ	 PA-045AR (AR-1117) A/NZ	 PA-180AR	 PA-183AR (AR-1246) A/NZ		
 ME-1466AR (AR-1725)	 ME-904AR	 ME-2381AR NEW A/NZ	 ME-2383AR NEW	 ME-396AR	 PA-187AR	 PA-181AR (AR-1663) A/NZ	 PA-389AR (AR-1118)	
 ME-1781AR (AR-1726)	 ME-1629AR (AR-1723)	 ME-2384AR NEW	 ME-2386AR NEW	 ME-1684AR A/NZ	 CH-1628AR A/NZ	 ME-009AR (AR-1724) A/NZ	 CH-1630AR A/NZ	 CH-1631AR
 ME-2291AR	 ME-2292AR	 ME-2293AR A/NZ	 ME-2295AR A/NZ	 ME-2294AR A/NZ	 ME-2297AR NEW	 ME-2296AR NEW		
 ME-2281AR A/NZ	 ME-2282AR	 ME-2283AR A/NZ	 ME-2285AR A/NZ	 ME-2284AR A/NZ	 ME-2287AR NEW	 ME-2286AR NEW		

A

B

C

D

E

F

G

H

I

J


K



ME-433AR



AE-1632AR



ST-1914AR

NEW



AE-2163AR

NEW



ST-736AR
(AR-1116)

A/NZ



PT-345AR
(AR-1250)

A/NZ




SE-567AR
(AR-1248)

A/NZ



FA-1526AR

A/NZ



SE-568AR
(AR-1249)

A/NZ



SE-010AR
(AR-1251)

A/NZ



ST-1919AR

NEW



ST-2171AR

NEW




AE-2153AR

NEW




AE-2167AR

NEW




AE-1632AR

A/NZ




AE-1634AR

NEW




FA-1678AR

A/NZ




FA-1527AR

A/NZ




PS-051AR

NEW



PS-055AR

NEW




PS-057AR

NEW




PS-058AR

NEW




PS-001AR

A/NZ



PS-002AR

A/NZ




PS-005AR



PS-006AR


B



PS-007AR
(AR-1662)

B


A/NZ



PS-008AR


B

A/NZ



PS-003AR
(AR-1115)

A/NZ



PS-004AR
(AR-1661)

A/NZ

B Can be used with chalk for blackboard application.



3M™ DI-NOC™ Architectural Finishes

EX Series for Exterior

Enable an entirely new appearance to existing exterior elements

The 3M™ DI-NOC™ Architectural Finishes EX Series for exterior applications are durable, dimensionally stable, and weather resistant surface finishes. They can be applied directly on smooth, non-porous application surfaces and are designed to maintain a consistent finish and color, despite the UV exposure and other weather conditions.

Extensive palette of patterns


Choose from 58 different designs, available mostly in wood grain and metallic patterns or make to order the DI-NOC™ Architectural Finishes EX Series in more than 100 different 3M™ DI-NOC™ Architectural Finishes Standard Series.

Excellent weather resistance

Exterior warranty ranges from 3 to 14 years, depending on the climate and installation location. Contact 3M Technical Support for detailed warranty information.

Easy to Install

The EX Series is an adhesive-backed film with a thickness of approximately 0.2 mm. It is easy to cut with a cutter knife, making it suitable for on-site work.



Combine exterior and interior designs

Create a sense of unity between interior and exterior surfaces by using DI-NOC™ Architectural Finishes Standard Series and DI-NOC™ Architectural Finishes EX Series with the same design.



Exterior / AE-1635EX, AE-1634EX, ME-007EX, PS-976EX, ST-442EX

Design Description Guide



FW-1214EX

Series	Suffix for product types
	Number
























































FW-1214EX

FW-1214

Standard and functional series have a similar appearance but are not identical.



Interior / PS-885, PS-949, PS-952, PS-1441

 WG-657EX ⊗	 FW-1129EX ⊗ A/NZ	 FW-1214EX ⊗ A/NZ	 WG-1144EX ⊗ A/NZ	 FW-1122EX ⊗ A/NZ	 FW-7011EX ⊗ A/NZ
 WG-960EX ⊗	 FW-1143EX ⊗ A/NZ	 FW-236EX ⊗ A/NZ	 FW-1023EX ⊗	 FW-1123EX ⊗ A/NZ	 FW-1805EX ⊗
 FW-233EX ⊗ A/NZ	 FW-1124EX ⊗	 FW-887EX ⊗	 WG-7024EX ⊗	 FW-1022EX ⊗ A/NZ	 FW-7008EX ⊗
 WG-695EX ⊗	 FW-1113EX ⊗	 FW-609HEX ⊗	 FW-1801EX ⊗	 FW-625EX ⊗	 FW-651EX ⊗
 WG-1044EX ⊗	 FW-640EX ⊗	 FW-324EX ⊗	 FW-330EX ⊗ A/NZ	 FW-627EX ⊗	 FW-522EX ⊗
 ME-004EX ⊗ A/NZ	 PA-038EX ⊗	 PA-039EX ⊗	 PA-390EX ⊗ A/NZ	 ME-002EX ⊗	 FW-643EX ⊗
 ME-001EX ⊗	 PA-187EX ⊗	 ME-003EX ⊗	 PA-181EX ⊗ A/NZ	 FA-1530EX ⊗	 FW-618EX ⊗
 PA-1854EX ⊗	 PS-959EX ⊗	 PS-957EX ⊗	 AE-1634EX ⊗	 ST-442EX ⊗	 PA-389EX ⊗ A/NZ
 PS-976EX ⊗	 PS-090EX ⊗	 AE-1632EX ⊗	 ST-736EX ⊗	 AE-1635EX ⊗	 LE-703EX ⊗ A/NZ
					 ME-007EX ⊗ A/NZ

A

B

C

D

E

F

G

H

I

J

K



3M™ DI-NOC™ Architectural Finishes

TIL Series for Application to Tile

Quickly bring new life and design to your tiled walls without demolition

3M™ DI-NOC™ Architectural Finishes TIL Series is designed for application to tiled wall surfaces. Composite film is made with a conformable metal foil designed for the refurbishment of damaged tiled wall surfaces or tiles displaying cracks, dirt, or mold.




Restroom refurbishment / ST-024TIL

Suitable for tiled walls with grout between tiles.

You can update the look of existing tile surfaces with minimal disruption.

- 3M™ Comply™ adhesive for fast, easy, air bubble-free installations
- High adhesion to tiled surfaces.



Quick Installation

This product gives a gamechanging, rejuvenated look just by applying film over a tiled surface, substantially lowering work time and costs, when compared to conventional replacement of an entire tiled surface.





Easy to Clean and Maintain

Film is easy to apply over existing tile and conforms into grout areas. It's easy to clean the entire surface including the covered grout. Fast and inexpensive to repair, when compared to expensive tile replacement.




Quality and Durability

Excellent design, water resistance, and durability properties.



⊠ This product is manufactured to order. Contact your local 3M sales rep to learn more on its lead time and minimum order quantity
 ⊗ Product conforms into grout between tiles. DO NOT apply to 3D compound curved surfaces.



A

B

C

D

E

F

G

H





3M™ DI-NOC™ Architectural Finishes

Whiteboard Film

Transform Surfaces into Communication Spaces

3M™ DI-NOC™ Whiteboard Film is a unique architectural finish that can convert interior surfaces into creative and collaborative environments. Compatible with most dry erase markers.

Writing




WH-111 offers excellent writing and erasing performance with a glossy surface.




WH-111

⊗ A/NZ

Writing and Projection



PWF-500 provides both whiteboard and projection capabilities, with the matte surface providing minimal glare from a projector.



PWF-500

⊗ A/NZ



PWF-500

3M™ DI-NOC™ Architectural Finishes Glass Finishes DG Series

Make your glass surface unique

3M™ DI-NOC™ Glass Finishes DG Series can be used behind many glass surfaces to provide a unique opaque dimensional look when viewed from the front glass surface.



FA-1161DG



ST-1831DG (DG-1831) ⊗



ME-1716DG (DG-1716) ⊗



ME-432DG (DG-432) ⊗



ME-1434DG ⊗



PA-180DG ⊗




ST-1587DG (DG-1587) ⊗




FA-1161DG (DG-1161) ⊗




FA-1156DG (DG-1156) ⊗



ME-379DG (DG-379) ⊗



RT-1827DG ⊗



PS-504DG (DG-504) ⊗

A

B

C

D

E

F

G

H

Sustainable Framework



Enabling a more Circular Economy with material, science and design.

1. Remodel and reuse

- Versatile application and conformability - Can be applied to most interior surfaces, from flat to curved, to enhance or refresh the design.
- Allows reuse / resurfacing / remodeling of existing structures
- Contribute to extending building life cycle
- Obtain LEEDv4 building credits - Building owners can use 3M™ DI-NOC™ Architectural Finishes to acquire LEEDv4 building credits for:
 1. Interior Life Cycle Impact Reduction
 2. Construction and Demolition Waste Management
 3. Low Emitting Materials
 4. Building Life Cycle Impact Reduction
 5. Furniture & Medical Furnishings
 6. Facility Maintenance and Renovation





3. Embodying the beautiful quality of natural resources through superior texturing technology and design variety

- Avoids cost of purchasing new construction materials
- Simulate the appearance of natural materials
- Creativity is never compromised with a selection from 900+ designs



2. Reduction of construction waste and shipping volume

- The film is thin, light, rollable, and flexible, making it more compact to transport than traditional construction material
- Reduces the need for demolition/ rebuilding of fixtures
- Helps reduce landfill/incineration of existing building fixtures



4. Excellent durability and maintainability

- The product has been tested for flammability per regional requirements and can be used in a wide range of interior architectural applications.
- Resistant to abrasion, impact, stains, chemicals, and UV light
- Easily cleaned as a non-porous surface with typical cleaners and disinfectants. *Please consult the Technical Data Sheet for additional technical information




📦 This product is manufactured to order. Contact your local 3M sales rep to learn more on its lead time and minimum order quantity
 ⊗ Application to simple curves and around straight edges is possible. DO NOT apply to 3D compound curved surfaces.
















3M™ DI-NOC™ Architectural Finishes E-Series PO Polyolefin Film

Help you meet your goals without sacrificing your vision.

The New E-Series PO collection offers an alternative for those that seek to go further. Find your own way and make a statement through our variety of patterns and textures. This product is made with approximately 99.5% non-PVC (non-vinyl) materials.



Available as make to order. *Standard Series and E-Series PO Polyolefin Film have a similar appearance but are not identical.

				
DW-1875PO Wood	FW-1256PO Wood	DW-2207PO Wood	DW-2212PO Wood	WG-1140PO Wood
				
DW-2218PO Wood	DW-2219PO Wood	FW-1755PO Wood	DW-2213PO Wood	FW-1801PO Wood
				
CN-1958PO Concrete	AE-2162PO Concrete	CN-1621PO Concrete	AE-2153PO Mortar	DW-2229PO Wood
1	2	3	4	5

A

B

C

Design Towards Sustainability



Recycled content liner


3M™ DI-NOC™ Architectural Finishes E-Series RC Recycled Content*** Film, E-Series PO Polyolefin Film and select designs* have a poly coated paper release liner made with 40% recycled pulp as base paper. Liner printed with ink containing 10% biomass derived material.

*Contact 3M for a list of designs.



Sample book

Cover made from 100% recycled paper and pages made from 70% recycled paper, all printed with vegetable oil based ink.



Options without phthalate plasticizer

3M™ DI-NOC™ Architectural Finishes Metallic Palette Series products manufactured after 2024 do not contain intentionally added phthalate plasticizer. P28

**Samples on this book are for visual assessment only.



E-Series RC Recycled Content*** Film

3M™ DI-NOC™ Architectural Finishes E-Series RC Recycled Content*** Film products are made in part with recycled polyester and bio-based material. P18~19

***E-Series Recycled Content Film has a base film layer made with 80% post-consumer recycled polyester and a colored layer made with 20% scallop shell powder as a bio-based filler.



DI-NOC™

Architectural Finishes



- 1 PW-2327MT
- 2 ME-2353
- 3 ST-2532MT
- 4 PW-2325MT
- 5 PS-2401MTRC
- 6 ME-2564
- 7 ME-2551
- 8 AE-2508
- 9 ST-2536MT
- 10 VM-2364
- 11 PS-2402MTRC
- 12 ME-2296AR

2024 New Products : Explore our most recent collections



E-Series RC P.18~
Recycled Content* Film

The E-Series RC offers clients more options as they pursue their sustainability goals. This is achieved by incorporating beautiful earth tones created in part from seashells and recycled polyester, bringing a bit of the sea to your walls.



E-Series PO P.15~
Polyolefin Film

The New E-Series PO collection offers an alternative for those that seek to go further. Find your own way and make a statement through our variety of patterns and textures. This product is made with approximately 99.5% non-PVC (non-vinyl) materials.



AR Series P.6~
Abrasion Resistant

Extend the life of your designs in heavy traffic areas with this revolutionary series, a solution tailor-made for spaces affected by the burdens of wear and tear.



TIL Series P.10~
for Tile Application

Bring new life and color quickly to your tiled walls. TIL Series is designed for tiled wall applications surfaces, such as bathrooms. You can update the look of existing tile surfaces with minimal facility disruption.

*E-Series Recycled Content Film has a base film layer made with 80% post-consumer recycled polyester and a colored layer made with 20% scallop shell powder as a bio-based filler.



8

9

10

11

12



Wood

P.52~

Step into a world of creative possibility, where nostalgia, resilience, and comfort converge to inspire your visionary designs. Our collection includes a range of looks from common to rare woods species, inviting guests into an atmosphere of warm comfort.



Metal

P.20~

Attain your design vision with our 'Metal Series'. Create more sophisticated spaces with process driven metal surfaces that achieve authentic expressions without the extra cost and maintenance. It's your choice. It has been expanded to include the latest trends via vibrational texture, optical mesh, oxidized metals.



Stone

P.32~

Make your luxurious design vision come true and within budget with our latest Stone Collection. We seamlessly blended captivating details that feel like they were extracted directly from nature.



Concrete, Stucco

P.36~

Bring out the artist inside you and make your vision come true with our Concrete & Stucco collection, where we seamlessly blend captivating natural elements. Our designs include multiple handcrafted finishes, inviting guests into an atmosphere rich in the traditions of craftsmanship.

3M™ DI-NOC™ Architectural Finishes

E-Series RC Recycled Content* Film

1

2

3

4

5

4

6

1 PS-2400MTRC

2 PS-2401MTRC

3 PS-2402MTRC

4 PS-2405MTRC


5 PS-2403MTRC

6 DW-2473MT

Unearth more sustainable decorative finish options with our new 3M™ DI-NOC™ Architectural Finishes E-Series RC Recycled Content* Film.

The E-Series RC Recycled Content* Film palette incorporates beautiful earth tones created in part from seashells and recycled polyester, bringing a bit of the sea to your walls.

Film construction :



Recycled PET resin

80%

Base film layer made with 80% post-consumer recycled polyester

Scallop shell powder


20%

Colored layer made with 20% scallop shell powder as a bio-based filler


Recycled paper with bio-mass ink

40%


Poly coated paper release liner made with 40% recycled pulp and printed with ink containing 10% biomass derived material




PS-2401MTRC ⊗ A/NZ NEW
Terracotta Brown




PS-2402MTRC ⊗ A/NZ NEW
Sage Green




PS-2400MTRC ⊗ A/NZ NEW
Desert Sand




PS-2404MTRC ⊗ A/NZ NEW
Timeless Grey



PS-2403MTRC ⊗ A/NZ NEW
Air Blue



PS-2405MTRC ⊗ A/NZ NEW
Classic Navy



PS-2406MTRC ⊗ A/NZ NEW
Midnight Black

*E-Series Recycled Content Film has a base film layer made with 80% post-consumer recycled polyester and a colored layer made with 20% scallop shell powder as a bio-based filler.

⚠ Texture of Application Surface:
The application surface texture may be visible through the film. Apply the film to very smooth and clean applications surfaces.
⊗ Application to simple curves is possible. DO NOT apply to 3D compound curved surfaces.

A

B

C

D

E

F

G

E-Series RC



1 ME-2554 2 ME-2556 3 ME-2559 4 WG-2450 5 ST-2541MT 6 ST-1914AR 7 DW-2473MT 8 ST-2171AR

Oxidized Metal



ME-2026



ME-1961



ME-2554

A/NZ NEW



ME-2172

A/NZ



ME-2024

A/NZ




AE-1643



ME-2025

A/NZ




ME-2556

NEW




ME-2559

A/NZ NEW




ME-2555

NEW



LE-1109



LE-1108

A

B

Metal

C

D

E

F

G

1

2

3

4

5

6

6

Oxidized Metal



ME-2564

A/NZ NEW




ME-2565

NEW



ME-2560

NEW



ME-2562

A/NZ NEW




ME-2022

A/NZ




ME-2173


A/NZ



RT-1112




ME-2020



ME-2023

A/NZ



1 ME-2560 2 ME-2562 3 ME-2565 4 ME-2564

A

B

C

D

E

F

G

Metal



1

2

2

3

4

5

6

1 AE-2500MT 2 VM-2363 3 PS-2406MTRC 4 ME-2552 5 ME-2551 6 ME-2556

Black Iron




ME-2561

NEW




ME-2563

NEW




ME-2553

NEW



ME-2551

A/NZ NEW



ME-2552

A/NZ NEW




ME-2550

NEW




ME-2174

A/NZ




RT-1827

A/NZ




ME-2027

A/NZ



RT-1111



ME-1469

A

B

C

D

E

F

G

Metal

1

2

3

4

4

1 VM-2364 2 ST-2540MT 3 PW-2322MT 4 ME-2384AR

Premium Metal



VM-2360

⊗ A/NZ NEW



VM-2361

⊗ A/NZ NEW



VM-2362

⊗ A/NZ NEW



VM-2363

⊗ A/NZ NEW



VM-2364

⊗ A/NZ NEW




VM-2365

⊗ A/NZ NEW



VM-2366

⊗ A/NZ NEW




VM-1691

⊗




VM-1695

⊗




VM-1487

⊗ A/NZ




VM-1692

⊗ A/NZ



VM-1695

⊗



VM-305

⊗ A/NZ



VM-1694

⊗ A/NZ




VM-1488

⊗




VM-1693

⊗ A/NZ



VM-2035

⊗



VM-2037

⊗



VM-2090

⊗



AM-1700

⊗ A/NZ



VM-2036

⊗



VM-1489

⊗

A

B

C

D

E

F

G

H
































Metal

Metallic Palette



3M™ DI-NOC™ Architectural Finishes Metallic Palette Series products manufactured after 2024 do not contain intentionally added phthalate plasticizer. Samples on this page are for visual assessment only.

Metal

A	 ME-2261	 ME-2262	 ME-2263	 ME-2264	
B	 ME-2271	 ME-2273	 ME-2274		
C	 ME-2381AR	 ME-2383AR	 ME-2384AR	 ME-2386AR	
D	 ME-2351	 ME-2353	 ME-2354	 ME-2356	
E	 ME-2341	 ME-2343	 ME-2344	 ME-2346	
F	 ME-2291AR	 ME-2292AR	 ME-2293AR	 ME-2294AR	 ME-2296AR
G	 ME-2281AR	 ME-2282AR	 ME-2283AR	 ME-2284AR	 ME-2286AR
H	 OM-2393			 OM-2394	 OM-2396



ME-2265

A/NZ



ME-2357

NEW



ME-2295AR

A/NZ



ME-2297AR

NEW



ME-2285AR

A/NZ



ME-2287AR

NEW



1 ME-2351 2 PS-2406MTRC 3 AE-2500MT 4 VM-2363 5 DA-PA Blaze



A

B

C

D

E
































F

G

H

Metal

Metal

A	 ME-1466 ☑ ME-1466AR	 ME-1467 ☑ ME-1467AR	 CH-2117	 CH-1627	
B	 ME-1716 ☑ ME-1716DG	 ME-433 ☑ ME-433AR	 ME-432 ☑ ME-432AR ☑ ME-432DG	 ME-904 ☑ ME-904AR	
C	 ME-1716 ☑ ME-1716DG	 CH-1677	 ME-1435	 PA-045 ☑ PA-045AR	 PA-184
D	 PA-178	 ME-377	 CH-1628 ☑ CH-1628AR	 ME-396 ☑ ME-396AR	
E	 ME-391	 LW-1085	 ME-388	 ME-1434 ☑ ME-1434DG	 CH-1630 ☑ CH-1630AR
F	 ME-1781 ☑ ME-1781AR	 ME-1781 ☑ ME-1781AR		 ME-431	 ME-1685
G	 ME-379 ☑ ME-379DG	 ME-1684 ☑ ME-1684AR	 ME-1175	 ME-1685	 CH-1631 ☑ CH-1631AR
H					

NEW New design

EX series: for exterior applications
AR series: for high traffic applications
DG series: for applications behind glass

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.



CH-1629
AR CH-1629AR

A/NZ



PA-180
AR PA-180AR **DG** PA-180DG

A/NZ



PA-046

A/NZ



PA-175



PA-036



ME-147



ME-1997

A/NZ



ME-1223

A/NZ



ET-1775

A/NZ



ET-1772




ME-2557

NEW



PA-039
EX PA-039EX



ET-1775



PA-683

A/NZ



ME-486

A/NZ



PA-390
EX PA-390EX

A/NZ



PA-320



ME-2558

NEW



PA-187
AR PA-187AR **EX** PA-187EX

A/NZ



PA-038
EX PA-038EX



ME-1224

A/NZ




PA-183
AR PA-183AR

A/NZ




PA-181
AR PA-181AR **EX** PA-181EX

A/NZ




ME-380

A/NZ



ME-1225

A/NZ




ME-1174

A/NZ



PA-389
AR PA-389AR **EX** PA-389EX

A/NZ



PA-185

A/NZ

A

B

C

D

E

F

G

H

Metal

Stone



1

2

3


4

5

6

7

1 AE-2506 2 AE-2503 3 ST-2533MT 4 VM-2361 5 ME-2562 6 PW-2322MT 7 ST-2534MT




ST-2530MT



ST-2531MT



ST-2535MT



ST-2538MT

NEW New design
MT Matte design

⊙ Use caution when applying to 3D compound curved surfaces to prevent damage to product

AR series: for high traffic applications
DG series: for applications behind glass

A/NZ Curated for Australia and New Zealand environments. Readily available from your local stockist.


Stone



ST-2530MT ⊙ **A/NZ** **NEW**



ST-2531MT ⊙ **NEW**




ST-1586




ST-2537MT ⊙ **A/NZ** **NEW**



ST-1914MT ⊙ **A/NZ**
ST-1914AR



ST-2532MT ⊙ **A/NZ** **NEW**




ST-2534MT ⊙ **A/NZ** **NEW**



ST-1587
ST-1587DG




ST-1920MT ⊙ **A/NZ**




ST-1831 **A/NZ**
ST-1831DG



ST-2533MT ⊙ **A/NZ** **NEW**



ST-2535MT ⊙ **A/NZ** **NEW**



ST-2538MT ⊙ **A/NZ** **NEW**



ST-1588



ST-1927MT ⊙



ST-2536MT ⊙ **A/NZ** **NEW**

A

B

C

D

E

F


G

Stone

Stone



ST-2539



ST-2541MT



ST-2542MT



ST-2171MT

1 ST-2540MT 2 VM-2364 3 AE-2504 4 PW-2322MT 5 ME-2384AR

NEW New design
MT Matte design

⊙ Use caution when applying to 3D compound curved surfaces to prevent damage to product

EX series: for exterior applications
AR series: for high traffic applications
TIL Series: for application to tile

A/NZ Curated for Australia and New Zealand environments. Readily available from your local stockist.

Stone



AE-1632 **A/NZ**
⚡ AE-1632AR ⚡ AE-1632EX ⚡ AE-1632TIL




ST-1911MT ⊙ **A/NZ**



ST-1828




ST-1829




ST-1919MT ⊙
⚡ ST-1919AR




ST-1915MT ⊙ **A/NZ**




ST-2541MT ⊙ **NEW**




ST-2170MT ⊙ **A/NZ**




ST-2539 **A/NZ** **NEW**




ST-2542MT ⊙ **NEW**



ST-1918MT ⊙




ST-2171MT ⊙ **A/NZ**



ST-2540MT ⊙ **NEW**




ST-2171AR ⊙ **A/NZ**




AE-1633 **A/NZ**




ST-2171MT ⊙ **A/NZ**



ST-2171MT ⊙ **A/NZ**



ST-2540MT ⊙ **NEW**



AE-1633 **A/NZ**

A

B

C

D

E

F

G

Stone




1

2


3

2

1 AE-2163MT 2 CN-2512 3 AE-2164MT



AE-2508



CN-1623



AE-2162MT



CN-1622

NEW New design
MT Matte design

☉ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

☐ PO Polyolefin Film

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.

Concrete / Mortar



CN-1958
☐ CN-1958PO



CN-1622



CN-2512

NEW



CN-1623



CN-1621
☐ CN-1621PO

A/NZ



AE-2508

A/NZ NEW



AE-2162MT
☐ AE-2162PO

☉ **A/NZ**




AE-1928MT

☉



AE-1930MT

☉ **A/NZ**



AE-1959MT

☉




AE-1913MT

☉ **A/NZ**




AE-1960MT

☉




AE-1944MT

☉ **A/NZ**



AE-1917MT

☉ **A/NZ**



AE-1921MT

☉ **A/NZ**

A

B

C

D

E

F

G

Concrete / Stucco
Others



1

2

3


1 AE-2161 2 CN-1621 3 ST-2171MT



AE-2154



AE-2511



AE-2513



AE-2153MT

NEW New design
MT Matte design

⊙ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

AR series: for high traffic applications
☐ PO Polyolefin Film

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.

Concrete / Mortar



AE-2149

A/NZ



AE-2154

A/NZ




AE-2509

A/NZ NEW



AE-2150

A/NZ



AE-2510

NEW



AE-2161

A/NZ



AE-2160

A/NZ



AE-2152MT

⊙ **A/NZ**



AE-2151

A/NZ



AE-2511

A/NZ NEW



AE-2513


A/NZ NEW



AE-2153MT

AR AE-2153AR ☐ AE-2153PO

⊙ **A/NZ**



AE-2155

A

B

C

D

E

F

G

Concrete / Stucco
Others



1

2

3

4

5

Fresco / Stucco



AE-2503

A/NZ NEW



AE-2504

NEW


A

B



AE-2505

NEW



AE-2506

A/NZ NEW



AE-2507

NEW

C

D

Concrete / Stucco
Others



AE-2156

A/NZ



AE-1637

A/NZ



AE-1717



AE-2158

A/NZ

E



AE-2157

A/NZ



AE-1639



AE-1719

A/NZ



AE-1638

A/NZ



AE-1640



AE-2159

A/NZ

F

G

Concrete / Stucco
Others



1

2


3

4

1 PS-3989MT 2 AE-2502 3 ME-2023 4 FW-1138AR




AE-2163MT



AE-2501MT



AE-2164MT



AE-2165MT

NEW New design
MT Matte design

⊙ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

EX series: for exterior applications
AR series: for high traffic applications

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.

Terracotta / Ceramic



AE-1955



AE-1634 **A/NZ**
AR AE-1634AR **EX** AE-1634EX



AE-2500MT ⊙ **A/NZ** **NEW**




AE-2163MT ⊙ **A/NZ**
AR AE-2163AR



PC-672



AE-2502 **A/NZ** **NEW**



AE-2501MT ⊙ **A/NZ** **NEW**




AE-2164MT ⊙




AE-1635
EX AE-1635EX




AE-2165MT ⊙




FA-592




AE-1636 **A/NZ**




PC-1179



AE-1646 **A/NZ**




AE-1645



FA-1530 **A/NZ**
EX FA-1530EX



AE-2167MT ⊙ **A/NZ**
AR AE-2167AR



FA-1531

A

B

C

D

E

F

G

Concrete / Stucco
Others



1 ME-2265 2 FA-2544 3 PS-3989MT



FA-1678



FA-2543



FA-2169



FA-1962

Brick / Tiled Design



FA-2544

NEW



FA-2543

NEW



FA-2169



FA-1678
FA-1678AR

A/NZ



FA-1962

A

B

C

D

Concrete / Stucco
Others



1 AE-2163MT 2 FA-2169 3 AE-2164MT

E

F

G

1

2

NEW New design
MT Matte design

⊗ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

EX series: for exterior applications

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.

Leather / Suède



LE-1105

A/NZ



LE-1552

⊗



LE-2782



LE-2128



SU-2232MT

⊗ **A/NZ**



SU-2232MT



SU-2231MT

⊗ **A/NZ**



AE-1932MT

⊗



LE-1106



SU-2233MT

⊗ **A/NZ**



SU-2234MT

⊗



SU-2235MT

⊗ **A/NZ**




LE-2703
(LE-703) **EX** LE-703EX

NEW



LE-1104



LE-1551

A/NZ



LE-1171

A

B

C

D

E

F

G

H

Leather / Suède

Textile



NEW New design
MT Matte design

⊗ Use caution when applying to 3D compound curved surfaces to prevent damage to product

DG series: for applications behind glass

A/NZ Curated for Australia and New Zealand environments. Readily available from your local stockist.



NU-2177



NU-2179



NU-2003

A/NZ



NU-2007



FE-1966

A/NZ



NU-2008

A/NZ



NU-2006

A/NZ



NU-2178



SI-1688



FA-1156

FA-1156DG



1 AE-2160 2 ME-2284AR 3 NU-2178 4 NU-2179 5 ME-2284AR

A

B

C

D

E

F


G

H


Textile



1 MW-1418 2 LZ-461



FE-1964



FA-1153



FA-1161




HS-1656

NEW New design
MT Matte design

AR series: for high traffic applications
DG series: for applications behind glass
TIL Series: for application to tile

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.

Abstract



FE-1964

AE-1953

A/NZ

LW-1081

FA-1963

LZ-461

A/NZ

FA-1153

PT-735

PT-346
TIL PT-364TIL

PT-345
AR PT-345AR

PG-197

FA-1166

FA-1164

FE-1967

PG-190

TE-1713

FA-688

FA-1161
DG FA-1161DG

HS-1656

A

B


C

D

E

F

Carbon



TE-1650

CA-419

CA-418

CA-422

CA-420

CA-421

A/NZ

CA-1170

G

H

Abstract / Carbon



1

5

7

8

2

6

9

3

1 ST-2532MT

2 PW-2325MT

3 PW-2327MT

4 ME-2353

5 ME-2564

6 PS-2401MTRC

7 AE-2508

8 ST-2536MT

9 ME-2551


Versatile wood grain series that expands design possibilities

You can choose the perfect color, design, texture, and function for your space from our extensive line of over 400 products.

Premium Wood **MT** P.54~

The highest grade Premium Wood Series expresses the realistic appearance and texture of natural wood. The controlled reflection of the matte coating is combined with both fine and deep wood grain embossing and high quality printing. This unique technology creates the optimum tone and texture of each species of wood.

Controlled Reflection Technology :




PW-2322MT

Dry Wood **MT** P.56~

The matte coating technology on the Dry Wood Series offers a smooth texture to the touch. The diffuse reflection without luster expresses the realistic appearance of high quality solid wood.


Matte Coating Technology :



DW-2215MT

Fine Wood P.62~

The Fine Wood Series provides the realistic expression of wood grain by variations high quality printing and embossing for each design. The grains in the wood are created by special printing coordinated with embossing.



FW-338

Wood Grain P.71~


The Wood Grain Series offers the appearance of a wide variety of wood species and colors at a reasonable price. The WG GN designs have a high quality gloss finish.



WG-2464

AR Series Abrasion Resistant **⚡** P.6~


The AR Series has an abrasion resistant top layer to reduce the visibility of scratches in high traffic areas and realistic wood grain embossing.



FW-338AR

EX Series for Exteriors **☀** P.8~

The EX Series wood grain designs are durable, dimensionally stable, and weather resistant for application to smooth, non porous exterior surfaces. They maintain a consistent finish and color, despite UV exposure and other conditions.



FW-651EX

MT Matte design

Premium Wood

A



PW-2305MT

☑ A/NZ



PW-2320MT

☑ NEW

B

C



PW-2326MT

☑ NEW




PW-2323MT

☑ NEW

D

E



PW-2309MT

☑ A/NZ



PW-2307MT

☑ A/NZ



PW-2306MT

☑ A/NZ




PW-2312MT

☑ A/NZ


F

G



PW-2327MT

☑ NEW



PW-2325MT

☑ A/NZ NEW

Wood

NEW New design
MT Matte design

⊗ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.



PW-2321MT

⊗ **NEW**




PW-2324MT

⊗ **NEW**




PW-2310MT

⊗



PW-2308MT


⊗



PW-2311MT

⊗

A/NZ



PW-2313MT

⊗

A/NZ



PW-2315MT

⊗

A/NZ



PW-2322MT

⊗

A/NZ


NEW



PW-2316MT

⊗

A/NZ



PW-2328MT

⊗ **NEW**



PW-2314MT

⊗

A/NZ



PW-2319MT

⊗

A/NZ

A

B

C

D


E

F

G

Wood

Dry Wood



NEW New design
MT Matte design

⊗ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

☐ PO Polyolefin Film

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.



DW-2478MT

⊗ **A/NZ** **NEW**




DW-2472MT

⊗ **NEW**



DW-2205MT

⊗ **A/NZ**



DW-2473MT

⊗ **A/NZ** **NEW**




DW-1897MT

⊗ **A/NZ**




DW-2206MT

⊗ **A/NZ**



DW-2204MT

⊗ **A/NZ**



DW-1901MT


⊗ **A/NZ**



DW-2207MT


⊗

☐ DW-2207PO



DW-1876MT

⊗




DW-1878MT

⊗ **A/NZ**



DW-2208MT

⊗ **A/NZ**




DW-1883MT

⊗ **A/NZ**




DW-2209MT

⊗



DW-1889MT

⊗



DW-1873MT

⊗ **A/NZ**

A

B

C

D


E

F

G

Wood

Dry Wood



NEW New design
H Horizontal woodgrain
MT Matte design

⊗ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

☐ PO Polyolefin Film

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.



DW-2219MT
☐ DW-2219PO

⊗ **A/NZ**



DW-2480MT

⊗ **NEW**



DW-2221MT

⊗ **A/NZ**




DW-1877MT

⊗ **A/NZ**




DW-2223MT

⊗ **A/NZ**



DW-1898MT

⊗




DW-2225MT

⊗




DW-1871MT

⊗




DW-2222MT

⊗




DW-1885MT

⊗



DW-1887MT

⊗ **A/NZ**



DW-2229MT

⊗ **A/NZ**

☐ DW-2229PO

A

B

C

D

E

F

G


Wood




FW-2426




WG-2078



FW-2425



FW-1306



FW-1735H

NEW New design
H Horizontal woodgrain
MT Matte design

⊗ Use caution when applying to
3D compound curved surfaces
to prevent damage to product

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.

Plank Design / Chipboard



FW-2425

NEW



FW-2426

NEW



WG-2078



AE-2168



FW-1306




WG-2076



DW-2210MT

⊗



FW-1735H

A

B

C

D

E

Metallic Wood



MW-1416



MW-1418



MW-1832

A/NZ



MW-1419



MW-777


A/NZ

F

G

Wood

Fine Wood



Wood



FW-1974



FW-1307



FW-1976



FW-1767

A



FW-1987




FW-1978

A/NZ



FW-2422

NEW



FW-1302

A/NZ

B



FW-1266

C



FW-1259

A/NZ



FW-1977

D



FW-1215

A/NZ



FW-337
FW-337AR

A/NZ



FW-1273

E



FW-1294
FW-1294AR

A/NZ

F




FW-1983

A/NZ



FW-1770




FW-1770

G

Wood

Fine Wood



NEW New design
H Horizontal woodgrain

EX series: for exterior applications
AR series: for high traffic applications
PO Polyolefin Film

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.



FW-1212



FW-1265



FW-1122
AR FW-1122AR **EX** FW-1122EX

A/NZ



FW-1755
PO FW-1755PO




FW-1023
EX FW-1023EX



FW-1296



FW-1805
EX FW-1805EX



FW-236
AR FW-236AR **EX** FW-236EX

A/NZ



FW-7011
AR FW-7011AR **EX** FW-7011EX

A/NZ



FW-502

A/NZ




FW-1257

A/NZ



FW-1286

A/NZ



FW-1021

A

B

C

D


E

F

G

Wood

Fine Wood



NEW New design
H Horizontal woodgrain

EX series: for exterior applications
AR series: for high traffic applications
PO Polyolefin Film

A/NZ Curated for Australia and New Zealand environments.
Readily available from your local stockist.



FW-1124
EX FW-1124EX

A/NZ



FW-1039H



FW-240




FW-886


A/NZ



FW-232




FW-510




FW-887
EX FW-887EX

A/NZ




FW-613



FW-650
EX FW-650EX




FW-677



FW-7006
EX FW-7006EX



FW-7008
EX FW-7008EX



FW-2427

NEW



FW-1744

A/NZ




FW-1022
AR FW-1022AR **EX** FW-1022EX

A/NZ



FW-1121H




FW-609H
EX FW-609HEX




FW-1113
EX FW-1113EX

A/NZ



FW-1801
EX FW-1801EX **PO** FW-1801PO

A/NZ



FW-332

A/NZ

A

B

C

D

E


F

G

Wood

Fine Wood

A



FW-1746



FW-625
 FW-625AR FW-625EX

A/NZ




FW-656




FW-606H

B



FW-338
 FW-338AR

A/NZ



FW-651
 FW-651EX




FW-607H

C




FW-1135




FW-1136H

D



FW-7009

A/NZ




FW-1282



FW-330
 FW-330EX

A/NZ




FW-7015

E



1 NU-2176MT 2 FW-7009

F



FW-627
 FW-627EX

A/NZ

G

Wood



FW-1216



FW-7007



FW-1986

A/NZ




FW-324
EX FW-324EX



1 FW-1751 2 AE-2150 3 ME-1685 4 ME-2261



FW-640
EX FW-640EX



FW-1975




FW-641




FW-1751

A/NZ




FW-1127

A/NZ



FW-1979

A/NZ



FW-1970



FW-1757

A

B

C

D

E

F

G

Wood



1

2

3

4

5

6

7

8

Wood

1 ME-2559 2 ST-2541MT 3 WG-2450 4 ST-2171AR 5 PS-2403MTRC 6 WG-2453 7 ST-1919AR 8 ME-2287AR

Wood Grain Palette

Oak

Straight Grain



WG-2442


Mixed Grain



WG-2432


Walnut

Straight Grain



WG-2463

Mixed Grain



WG-2453



WG-2440

NEW



WG-2430

NEW



WG-2460

NEW



WG-2450

NEW



WG-2441

NEW



WG-2431

NEW



WG-2461

NEW



WG-2451

NEW



WG-2442

NEW



WG-2432

NEW



WG-2462

NEW



WG-2452

NEW



WG-2443

NEW



WG-2433

NEW



WG-2463

NEW



WG-2453

NEW



WG-2444

NEW



WG-2434

NEW



WG-2464

NEW



WG-2454

NEW

A

B

C

D
































E

F

G

Wood

Wood Grain

A					
	WG-657 WG-657EX	WG-1365	WG-1709		
B					
		WG-1343	WG-1344	WG-247	WG-1705
C					
	WG-1846	WG-2049	WG-1340	WG-2083H	
D					
	WG-1046	WG-1339			WG-960 WG-960EX
E					
	WG-1067	WG-376	WG-1141		WG-1838
F					
	WG-467	WG-1220	WG-2085		WG-1840
G					
	WG-2073	WG-1144 WG-1144EX	WG-166	WG-1143 WG-1143EX	WG-1837
H					
			WG-964	WG-1710	WG-1337

Wood

NEW New design
H Horizontal woodgrain

W Wiping Woodgrain : Film surface has a special treatment. DO NOT use double-cut seams

EX series: for exterior applications

A/NZ Curated for Australia and New Zealand environments. Readily available from your local stockist.



WG-1219

A/NZ



WG-1221

A/NZ



WG-1812

W



WG-833




WG-832

A



WG-837




WG-2944




WG-2246

A/NZ


B




WG-835




WG-453



WG-256



WG-2944



WG-2839

C




WG-250



WG-453



WG-845




WG-846




WG-1814

D



WG-1346




WG-877



WG-845




WG-846




WG-2115

E




WG-1845




WG-699

A/NZ



WG-1358



WG-1815




WG-2115

F



WG-831


A/NZ



WG-709



WG-878



WG-2071



WG-1360

G

H

Wood


Wood Grain Gloss



WG-1711GN



WG-763GN




WG-364GN

WG-763GN


Wood Grain



WG-836




WG-841




WG-854

A/NZ



WG-1142

A/NZ




WG-1140

EX WG-1140EX PO WG-1140PO


A/NZ



WG-763




WG-879




WG-865

A/NZ



WG-2862




WG-697

A/NZ




WG-943




WG-1375

A/NZ




WG-7022

A/NZ



WG-364




WG-157


W A/NZ




WG-417




WG-1147



WG-1146



WG-693



WG-7024 EX WG-7024EX

Wood

Wood Grain



WG-1703

A/NZ



WG-696

A/NZ



WG-947



WG-1336

A/NZ




WG-2075




WG-1353




WG-2082H



WG-1342




WG-1368




WG-2042



WG-1708



WG-2084H



WG-1196

A/NZ



WG-1848



WG-1348




WG-695

EX WG-695EX


A/NZ




WG-1370




WG-1369




WG-1371




WG-2033




WG-1836




WG-1704




WG-1841




WG-2019



WG-1373




WG-1364




WG-156

W **A/NZ**




WG-1044


EX WG-1044EX




WG-2047




WG-2707



WG-664




WG-428



WG-1070


W



WG-2041



WG-1835



WG-1050

A/NZ

A

B

C

D

E

F

G

H

Wood



PS-3866MT



Photo : Daiki Morita Design:JOINT CENTER PS-3864MT

Solid Color

Solid Color

Matte Coating Technology :

The new Matte Series utilizes the latest technology available. With a new state of the art matte surface, the Matte Series offers realistic texture by converting incident light into diffuse reflection and suppressing specular reflection. This series also provides fingerprint resistance. Explore the new world of design possibilities with 3M Matte Series.



Diffuse Reflection

The new state of the art matte surface converts incident light into diffuse reflection, providing very low gloss and a deep, high quality matte texture.



Fingerprint Resistant


The matte texture provides fingerprint resistance, reducing the visibility of fingerprints with an easy to maintain surface.




Tactile Feature

A realistic matte texture is created by combining the matte coating technology with high definition embossing technology.

Experience the difference in texture between standard series and new Matte Series





































































Matte Series
PS-3870MT



Existing
 PS-999

PS-3989MT (PS-1989MT)	PS-3864MT (PS-1864MT)	PS-3863MT (PS-1863MT)	PS-3093MT (PS-2093MT)	PS-3101MT (PS-2101MT)
PS-3904MT (PS-1904MT)	PS-3866MT (PS-1866MT)	PS-3100MT (PS-2100MT)	PS-3094MT (PS-2094MT)	
PS-3865MT (PS-1865MT)	PS-3095MT (PS-2095MT)	PS-3098MT (PS-2098MT)	PS-3869MT (PS-1869MT)	PS-3870MT
PS-3091MT (PS-2091MT)	PS-3092MT (PS-2092MT)	PS-3096MT (PS-2096MT)	PS-3097MT (PS-2097MT)	PS-1870MT

Solid Color

A	 PS-959 PS-959EX	 PS-503	 PS-1188	 PS-957 PS-957EX	 PS-002AR	 PS-3989MT (PS-1989MT)
B	 HG-1205	 PS-3904MT (PS-1904MT)	 PS-001AR	 PS-975	 PS-1441	 PS-3865MT (PS-1865MT)
C	 PS-003AR	 PS-1187	 PS-976 PS-976EX	 PS-3864MT (PS-1864MT)	 PS-955	 PS-005AR
D	 PS-1186	 PS-998	 PS-982 PS-982TIL	 PS-1437	 PS-1184	 PS-954
E	 PS-004AR	 PS-090 PS-090EX	 PS-1185	 PS-1438	 PS-3091MT (PS-2091MT)	 PS-952
F	 PS-042	 PS-048	 PS-073	 PS-971	 PS-3866MT (PS-1866MT)	 PS-950
G	 PS-091	 PS-3863MT (PS-1863MT)	 PS-093	 PS-3092MT (PS-2092MT)	 PS-006AR	 PS-3093MT (PS-2093MT)
H	 PS-022	 PS-3095MT (PS-2095MT)	 PS-034	 PS-3096MT (PS-2096MT)	 PS-3100MT (PS-2100MT)	 PS-949
I	 PS-1005	 PS-1439	 PS-1440	 PS-3101MT (PS-2101MT)	 PS-992	 PS-3869MT (PS-1869MT)
J	 PS-3094MT (PS-2094MT)	 PS-3097MT (PS-2097MT)	 PS-007AR	 PS-885	 PS-948	 PS-504 PS-504DG
K	 PS-999	 PS-1183 (PS-1183MT)	 PS-3870MT	 PS-1870MT	 PS-008AR	 HG-1201
L						

Solid Color

NEW New design
MT Matte design
A/NZ Curated for Australia and New Zealand environments.
 Readily available from your local stockist.

⊗ DO NOT apply to 3D compound curved surfaces
 ⊙ Use caution when applying to 3D compound curved surfaces to prevent damage to product

EX series: for exterior applications
AR series: for high traffic applications
DG series: for applications behind glass

TIL Series: for application to tile



A
B
C
D
E
F
G
H
I

E-Series RC Recycled Content* Film

* E-Series Recycled Content Film has a base film layer made with 80% post-consumer recycled polyester and a colored layer made with 20% scallop shell powder as a bio-based filler.



J
K
L

Solid Color

Index

Product Code	page, column, row
--------------	-------------------

AE | Earth / Stone

AE-1632	35	A	1
AE-1633	35	F	4
AE-1634	43	A	2
AE-1635	43	D	4
AE-1636	43	E	4
AE-1637	41	E	2
AE-1638	41	G	2
AE-1639	41	F	2
AE-1640	41	G	3
AE-1643	21	C	4
AE-1645	43	G	1
AE-1646	43	F	4
AE-1717	41	E	3
AE-1719	41	F	3
AE-1913MT	37	F	2
AE-1917MT	37	G	1
AE-1921MT	37	G	4
AE-1928MT	37	E	3
AE-1930MT	37	E	4
	47	D	4
AE-1944MT	37	F	4
AE-1953	51	A	3
AE-1955	43	A	1
AE-1959MT	37	F	1
AE-1960MT	37	F	3
AE-2149	39	A	1
AE-2150	39	B	1
AE-2151	39	E	2
AE-2152MT	39	E	1
AE-2153MT	39	G	3
AE-2154	39	A	2
AE-2155	39	G	4
AE-2156	41	E	1
AE-2158	41	E	4
AE-2159	41	F	4
AE-2160	39	D	1
AE-2161	39	C	4
AE-2162MT	37	D	1
AE-2163MT	43	B	1
AE-2164MT	43	D	1
AE-2165MT	43	E	2
AE-2167MT	43	F	3
AE-2168	61	C	2
AE-2500MT	43	A	3
AE-2501MT	43	C	4
AE-2502	43	C	2
AE-2503	41	A	1
AE-2504	41	A	3
AE-2505	41	C	1
AE-2506	41	C	2
AE-2507	41	C	4
AE-2508	37	C	3
AE-2509	39	A	3
AE-2510	39	C	2
AE-2511	39	E	3
AE-2513	39	F	1

Product Code	page, column, row
--------------	-------------------

AM | Advanced Metallic

AM-1700	27	G	4
---------	----	---	---

Product Code	page, column, row
--------------	-------------------

AR | Abrasion Resistant

AE-1632AR	7	H	1
AE-1634AR	7	H	2
AE-2153AR	7	F	5
AE-2163AR	7	D	3
AE-2167AR	7	F	7
BW-1310AR	6	F	1
CH-1628AR	6	I	2
CH-1629AR	6	I	1
CH-1630AR	6	I	4
CH-1631AR	6	I	7
FA-1526AR	7	E	5

Product Code	page, column, row		
FA-1527AR	7	I	2
FA-1678AR	7	I	1
FW-233AR	6	D	6
FW-236AR	6	D	4
FW-337AR	6	E	3
FW-338AR	6	E	7
	53		

FW-625AR	6	D	7
FW-1022AR	6	E	6
FW-1122AR	6	E	2
FW-1129AR	6	D	2
FW-1138AR	6	D	1
FW-1280AR	6	D	5
FW-1293AR	6	D	3
FW-1294AR	6	E	5
FW-7011AR	6	E	4
FW-7017AR	6	E	1
ME-009AR	6	I	3
ME-396AR	6	G	4
ME-432AR	6	F	4
ME-433AR	6	F	3
ME-904AR	6	H	1
ME-1466AR	6	G	1
ME-1467AR	6	F	2
ME-1684AR	6	H	7
ME-1781AR	6	H	4
	6	K	1
ME-2281AR	28	G	1
	6	K	2
ME-2282AR	28	G	2
	6	K	3
ME-2283AR	28	G	3
	6	K	5
ME-2284AR	28	G	4
	6	K	4
ME-2285AR	29	G	1
	6	K	7
ME-2286AR	28	G	5
	6	K	6
ME-2287AR	29	G	2
	6	J	1
ME-2291AR	28	F	1
	6	J	2
ME-2292AR	28	F	2
	6	J	3
ME-2293AR	28	F	3
	6	I	5
ME-2294AR	28	F	4
	6	J	4
ME-2295AR	29	E	1
	6	J	7
ME-2296AR	28	F	5
	6	A	4
ME-2297AR	6	I	6
	29	E	2
	6	G	2
ME-2381AR	28	C	1
	6	G	3
ME-2383AR	28	C	3
	6	H	5
ME-2384AR	28	C	4
	6	H	6
ME-2386AR	28	C	5

PA-045AR	6	F	5
PA-180AR	6	F	6
PA-181AR	6	G	6
PA-183AR	6	F	7
PA-187AR	6	G	5
PA-389AR	6	G	7
	7	J	1
PS-001AR	78	B	3
	7	J	3
PS-002AR	78	A	5
	7	K	3
PS-003AR	78	C	1
	7	K	4
PS-004AR	78	E	1
	7	J	4
PS-005AR	78	C	6
	7	J	5
PS-006AR	78	G	5
	7	J	6
PS-007AR	78	J	3
	7	J	7
PS-008AR	78	K	5
	7	H	3
PS-051AR	7	H	3
PS-055AR	7	H	5
PS-057AR	7	H	6
PS-058AR	7	H	7
PT-345AR	7	D	6

Product Code	page, column, row		
SE-010AR	7	E	7
SE-567AR	7	D	7
SE-568AR	7	E	6
ST-736AR	7	D	5
ST-1914AR	7	D	1
ST-1919AR	7	F	1
ST-2171AR	7	F	3

Product Code	page, column, row
--------------	-------------------

CA | Carbon

CA-418	51	H	2
CA-419	51	G	2
CA-420	51	G	4
CA-421	51	H	4
CA-422	51	G	3
CA-1170	51	G	5

Product Code	page, column, row
--------------	-------------------

CH | Metallic Hairline

CH-1627	30	A	4
CH-1628	30	D	3
CH-1629	31	A	1
CH-1630	30	F	5
CH-1631	30	G	5
CH-1677	30	C	2
CH-2117	30	A	3

Product Code	page, column, row
--------------	-------------------

CN | Concrete / Mortar

CN-1621	37	C	2
CN-1622	37	A	2
CN-1623	37	B	1
CN-1958	37	A	1
CN-2512	37	A	3

Product Code	page, column, row
--------------	-------------------

DG | Glass Finishes

FA-1156DG	13	H	1
FA-1161DG	13	F	5
ME-379DG	13	H	2
ME-432DG	13	D	4
ME-1434DG	13	D	5
ME-1716DG	13	D	3
PA-180DG	13	E	3
PS-504DG	13	H	5
RT-1827DG	13	G	3
ST-1587DG	13	F	1
ST-1831DG	13	D	1

Product Code	page, column, row
--------------	-------------------

DW | Dry Wood

DW-1871MT	59	D	3
DW-1873MT	57	G	4
DW-1874MT	58	B	4
DW-1875MT	56	D	4
DW-1876MT	57	E	4
DW-1877MT	59	C	1
DW-1878MT	57	F	1
DW-1882MT	58	G	2
DW-1883MT	57	G	3
DW-1884MT	58	A	3
DW-1885MT	59	G	1
DW-1887MT	59	G	2
DW-1888MT	56	C	3
DW-1889MT	57	G	1
DW-1891MT	58	G	1
DW-1893MT	56	B	4
DW-1897MT	57	C	4
DW-1898MT	59	C	3
DW-1899MT	58	E	1
DW-1900HMT	58	E	2
DW-1901MT	57	E	2
DW-1902MT	56	G	2
DW-1993MT	56	G	3
DW-2197MT	56	C	1
DW-2198MT	56	D	2
DW-2199MT	56	C	2
DW-2200MT	56	C	4
DW-2201MT	56	D	3
DW-2202MT	56	G	1

Product Code	page, column, row		
DW-2203MT	56	G	4
DW-2204MT	57	E	1
DW-2205MT	57	C	1
DW-2206MT	57	D	1
DW-2207MT	57	E	3
DW-2208MT	57	F	2
DW-2209MT	57	F	4
DW-2210MT	61	D	3
	58	A	4
DW-2212MT	58	B	3
DW-2213MT	58	E	3
DW-2214MT	58	F	3
	53		
DW-2215MT	58	F	4
DW-2216MT	58	E	4
DW-2217MT	58	G	4
DW-2218MT	56	A	4
DW-2219MT	59	A	1
DW-2221MT	59	A	4
DW-2222MT	59	E	1
DW-2223MT	59	C	2
DW-2225MT	59	C	4
DW-2229MT	59	F	3
DW-2470MT	56	A	1
DW-2471MT	56	A	2
DW-2472MT	57	A	3
DW-2473MT	57	C	2
DW-2474MT	58	C	3
DW-2475MT	58	A	1
DW-2476MT	56	A	3
DW-2477MT	56	E	1
DW-2478MT	57	A	1
DW-2479MT	56	E	3
DW-2480MT	59	A	2
DW-2481MT	58	C	1

Product Code	page, column, row
--------------	-------------------

ET | Effect

ET-1772	31	B	5
ET-1775	31	B	4

Product Code	page, column, row
--------------	-------------------

EX | Exterior

AE-1632EX	9	J	3
AE-1634EX	9	J	4
AE-1635EX	9	J	5
FA-1530EX	9	G	6
FW-233EX	9	D	1
FW-236EX	9	B	4
FW-324EX	9	F	3
FW-330EX	9	F	4
FW-522EX	9	F	6
FW-609HEX	9	E	3
FW-618EX	9	F	7
FW-625EX	9	E	5
FW-627EX	9	F	5
FW-640EX	9	F	2
FW-643EX	9	E	7
FW-650EX	9	C	7
FW-651EX	9	E	6
FW-887EX	9	D	3
FW-1022EX	9	C	5
FW-1023EX	9	C	1
FW-1113EX	9	E	2
FW-1122EX	9	A	5
FW-1123EX	9	C	2
FW-1124EX	9	D	2
FW-1129EX	9	A	2
FW-1214EX	9	A	3
FW-1801EX	9	E	4
FW-1805EX	9	C	3
FW-7006EX	9	D	7
FW-7008EX	9	B	7
FW-7011EX	9	A	7
LE-703EX	9	K	6
ME-001EX	9	H	1
ME-002EX	9	G	5
ME-003EX	9	I	4
ME-004EX	9	G	1
ME-007EX	9	K	7
PA-038EX	9	G	2
PA-039EX	9	G	3
PA-181EX	9	H	5
PA-187EX	9	H	2
PA-389EX	9	I	5
PA-390EX	9	G	4

Product Code	page, column, row		
PA-1854EX	9	I	1
PS-090EX	9	K	2
PS-957EX	9	J	2
PS-959EX	9	J	1
PS			

Product Code	page, column, row
FW-1121H	67 F 2
FW-1122	65 A 3
FW-1123	66 D 1
FW-1124	67 A 1
FW-1125	66 D 3
FW-1127	69 F 1
FW-1129	64 C 1
FW-1130H	64 C 2
FW-1135	68 C 3
FW-1136H	68 C 4
FW-1138	62 C 3
FW-1207	62 D 4
FW-1208	62 B 4
FW-1211	64 A 2
FW-1212	65 A 1
FW-1214	64 F 1
FW-1215	63 E 1
FW-1216	69 A 1
FW-1217	62 F 2
FW-1255	62 D 1
FW-1256	64 B 1
FW-1257	65 F 1
FW-1258	64 E 1
FW-1259	63 D 1
FW-1261	62 G 1
FW-1262	64 F 2
FW-1265	65 A 2
FW-1266	63 C 4
FW-1272	64 F 4
FW-1273	63 D 3
FW-1279	64 F 3
FW-1280	66 C 2
FW-1282	68 D 2
FW-1283	66 A 3
FW-1285	64 C 4
FW-1286	65 F 2
FW-1291	64 B 2
FW-1293	64 G 2
FW-1294	63 D 4
FW-1296	65 C 3
FW-1302	63 B 4
FW-1306	61 C 3
FW-1307	63 A 2
FW-1331	66 E 2
FW-1683	62 A 4
FW-1735H	61 C 4
FW-1737	66 A 2
FW-1738	66 F 2
FW-1743	66 A 4
FW-1744	67 D 4
FW-1746	68 A 1
FW-1751	69 D 3
FW-1755	65 B 1
FW-1757	69 F 4
FW-1761	62 A 1
FW-1765	62 C 1
FW-1766	64 C 3
FW-1767	63 A 4
FW-1770	63 F 2
FW-1801	67 F 4
FW-1805	65 C 4
FW-1810	64 G 3
FW-1970	69 F 2
FW-1972	64 G 4
FW-1974	63 A 1
FW-1975	69 D 2
FW-1976	63 A 3
FW-1977	63 D 2
FW-1978	63 B 2
FW-1979	69 G 1
FW-1981	64 A 1
FW-1983	63 F 1
FW-1986	69 B 1
FW-1987	63 B 1
FW-1988	64 G 1
FW-2420	62 D 2
FW-2421	64 D 2
FW-2422	63 B 3
FW-2423	64 A 3
FW-2424	64 D 4
FW-2425	61 A 1
FW-2426	61 A 3
FW-2427	67 D 2
FW-7006	67 C 4
FW-7007	69 A 2
FW-7008	67 D 1
FW-7009	68 D 1
FW-7011	65 D 3
FW-7015	68 E 4
FW-7017	62 A 2

Product Code	page, column, row
HG High Gloss	
HG-1201	78 K 6
HG-1205	78 B 1
HG-1511	79 F 3
Product Code page, column, row	
HS Mono Contrast	
HS-1656	51 E 5
Product Code page, column, row	
LE Leather	
LE-1104	47 G 2
LE-1105	47 A 1
LE-1106	47 D 5
LE-1108	21 G 4
LE-1109	21 G 3
LE-1171	47 G 5
LE-1551	47 G 3
LE-1552	47 A 2
LE-2128	47 B 2
LE-2703	47 G 1
LE-2782	47 B 1
Product Code page, column, row	
LW Entertainment	
LW-1081	51 A 4
LW-1085	30 E 2
Product Code page, column, row	
LZ Abstract	
LZ-461	51 C 1
Product Code page, column, row	
ME Metallic	
ME-147	31 B 1
ME-377	30 D 2
ME-379	30 G 1
ME-380	31 H 1
ME-388	30 E 3
ME-391	30 E 1
ME-396	30 E 5
ME-431	30 G 4
ME-432	30 B 3
ME-433	30 B 2
ME-486	31 E 2
ME-904	30 C 5
ME-1174	31 H 3
ME-1175	30 H 3
ME-1223	31 B 3
ME-1224	31 G 1
ME-1225	31 H 2
ME-1434	30 E 4
ME-1435	30 C 3
ME-1466	30 A 1
ME-1467	30 A 2
ME-1469	25 G 4
ME-1684	30 H 2
ME-1685	30 H 4
ME-1716	30 B 1
ME-1781	30 F 2
ME-1961	21 A 2
ME-1997	31 B 2
ME-2020	23 G 1
ME-2022	23 E 1
ME-2023	23 G 2
ME-2024	21 C 3
ME-2025	21 D 4
ME-2026	21 A 1
ME-2027	25 G 2
ME-2172	21 B 1
ME-2173	23 E 2
ME-2174	25 E 4
ME-2261	28 A 1
ME-2262	28 A 2
ME-2263	28 A 3
ME-2264	28 A 4
ME-2265	29 A 1
ME-2271	28 B 1
ME-2273	28 B 3

Product Code	page, column, row
ME-2274	28 B 4
ME-2341	28 E 1
ME-2343	28 E 3
ME-2344	28 E 4
ME-2346	28 E 5
ME-2351	28 D 1
ME-2353	28 D 3
ME-2354	28 D 4
ME-2356	28 D 5
ME-2357	29 C 1
ME-2550	25 E 3
ME-2551	25 C 3
ME-2552	25 E 1
ME-2553	25 C 1
ME-2554	21 A 3
ME-2555	21 F 1
ME-2556	21 D 1
ME-2557	31 C 1
ME-2558	31 F 2
ME-2559	21 E 3
ME-2560	23 C 1
ME-2561	25 A 1
ME-2562	23 C 3
ME-2563	25 A 3
ME-2564	23 A 1
ME-2565	23 A 3
Product Code page, column, row	
MW Metallic Wood	
MW-777	61 F 4
MW-1416	61 F 1
MW-1418	61 G 1
MW-1419	61 F 3
MW-1832	61 F 2
Product Code page, column, row	
NU Nuno / Textile	
NU-1238	48 B 4
NU-1240	48 E 4
NU-1785	48 A 5
NU-1786	48 G 1
NU-1789	48 H 4
NU-1791	48 E 1
NU-1792	48 F 1
NU-1934MT	48 C 3
NU-1935MT	48 C 5
NU-1940MT	48 F 4
NU-1941MT	48 C 1
NU-2003	49 A 4
NU-2006	49 D 2
NU-2007	49 A 5
NU-2008	49 C 2
NU-2009	48 G 5
NU-2010	48 E 5
NU-2012	48 A 1
NU-2013	48 A 2
NU-2014	48 B 2
NU-2175MT	48 E 2
NU-2176MT	48 G 3
NU-2177	49 A 1
NU-2178	49 C 3
NU-2179	49 A 2
Product Code page, column, row	
OM Optical Mesh	
OM-2393	28 H 1
OM-2394	28 H 4
OM-2396	28 H 5
Product Code page, column, row	
PA Metallic	
PA-036	31 A 5
PA-038	31 F 5
PA-039	31 D 3
PA-045	30 C 4
PA-046	31 A 3
PA-175	31 A 4
PA-178	30 D 1
PA-180	31 A 2
PA-181	31 G 5
PA-183	31 G 4
PA-184	30 D 5

Product Code	page, column, row
PA-185	31 H 5
PA-187	31 F 4
PA-320	31 F 1
PA-389	31 H 4
PA-390	31 E 3
PA-683	31 E 1
Product Code page, column, row	
PC Sand	
PC-672	43 B 2
PC-1179	43 F 1
Product Code page, column, row	
PG Abstract	
PG-190	51 E 1
PG-197	51 D 1
Product Code page, column, row	
PO Polyolefin Film	
AE-2153PO	15 C 4
AE-2162PO	15 C 2
CN-1621PO	15 C 3
CN-1958PO	15 C 1
DW-1875PO	15 A 1
DW-2207PO	15 A 3
DW-2212PO	15 A 4
DW-2213PO	15 B 4
DW-2218PO	15 B 1
DW-2219PO	15 B 2
DW-2229PO	15 C 5
FW-1256PO	15 A 2
FW-1755PO	15 B 3
FW-1801PO	15 B 5
WG-1140PO	15 A 5
Product Code page, column, row	
PS Single Color	
PS-022	78 H 1
PS-027	79 B 6
PS-034	78 H 3
PS-042	78 F 1
PS-048	78 F 2
PS-073	78 F 3
PS-074	79 D 6
PS-075	79 A 6
PS-090	78 E 2
PS-091	78 G 1
PS-093	78 G 3
PS-107	79 H 3
PS-110	79 H 6
PS-112	79 A 3
PS-116	79 A 5
PS-121	79 C 2
PS-134	79 E 4
PS-135	79 D 5
PS-140	79 E 1
PS-141	79 F 4
PS-281	79 A 2
PS-292	79 E 6
PS-293	79 F 6
PS-294	79 G 6
PS-503	78 A 2
PS-504	78 J 6
PS-506	79 D 1
PS-665	79 F 5
PS-668	79 F 1
PS-713	79 A 1
PS-885	78 J 4
PS-900	79 D 3
PS-910	79 C 3
PS-912	79 C 4
PS-914	79 E 5
PS-920	79 C 1
PS-948	78 J 5
PS-949	78 H 6
PS-950	78 F 6
PS-952	78 E 6
PS-954	78 D 6
PS-955	78 C 5
PS-957	78 A 4
PS-959	78 A 1
PS-971	78 F 4

Product Code	page, column, row
PS-975	78 B 4
PS-976	78 C 3
PS-982	78 D 3
PS-992	78 I 5
PS-998	78 D 2
PS-999	78 K 1
PS-1005	78 I 1
PS-1008	79 E 3
PS-1009	79 G 3
PS-1010	79 C 5
PS-1183	78 K 2
PS-1184	78 D 5
PS-1185	78 E 3
PS-1186	78 D 1
PS-1187	78 C 2
PS-1188	78 A 3
PS-1437	78 D 4
PS-1438	78 E 4
PS-1439	78 I 2
PS-1440	78 I 3
PS-1441	78 B 5
PS-1442	79 A 4
PS-1443	79 B 4
PS-1444	79 D 4
PS-1446	79 B 5
PS-1447	79 G 5
PS-1450	79 B 1
PS-1454	79 B 2
PS-1455	79 D 2
PS-1457	79 F 2
PS-1459	79 B 3
PS-1821	79 G 4
PS-1823	79 E 2
PS-1825	79 G 1
PS-1826	79 H 1
PS-1870MT	77 H 5
	78 K 4
	19 D 3
PS-2400MTRC	79 K 2
	19 D 1
PS-2401MTRC	79 K 3
	19 D 2
PS-2402MTRC	79 K 4
	19 F 1
PS-2403MTRC	79 K 5
	19 D 4
PS-2404MTRC	79 K 1
	19 F 2
PS-2405MTRC	79 K 6
	19 F 3
PS-2406MTRC	79 L 6
	77 H 1
PS-3091MT	78 E 5
	77 H 2
PS-3092MT	78 G 4
	77 D 4
PS-3093MT	78 G 6
	77 E 5
PS-3094MT	78 J 1
	77 F 2
PS-3095MT	78 H 2
	77 H 3
PS-3096MT	78 H 4
	77 H 4
PS-3097MT	78 J 2
	77 F 3
PS-3098MT	79 C 6
	77 H 5
PS-3100MT	78 H 5
	77 D 5
PS-3101MT	78 I 4
	77 E 2
PS-3863MT	78 G 2
	77 D 2
PS-3864MT	78 C 4
	77 G 1
PS-3865MT	78 B 6
	77 D 3
PS-3866MT	78 F 5
	77 G 4
PS-3869MT	78 I 6
	77 F 5
PS-3870MT	78 K 3
	77 E 1
PS-3904MT	78 B 2
	77 D 1
PS-3989MT	78 A 6

Product Code	page, column, row		
PT Abstract			
PT-345	51	C	5
PT-346	51	C	4
PT-735	51	C	3

Product Code	page, column, row		
PW Premium Wood			
PW-2305MT	54	A	1
PW-2306MT	54	E	3
PW-2307MT	54	E	2
PW-2308MT	55	C	2
PW-2309MT	54	E	1
PW-2310MT	55	C	1
PW-2311MT	55	C	3
PW-2312MT	54	E	4
PW-2313MT	55	C	4
PW-2314MT	55	F	3
PW-2315MT	55	D	1
PW-2316MT	55	D	4
PW-2319MT	55	F	4
PW-2320MT	54	A	3
PW-2321MT	55	A	1
PW-2322MT	55	D	2
PW-2323MT	54	C	3
PW-2324MT	55	A	3
PW-2325MT	54	F	3
PW-2326MT	54	C	1
PW-2327MT	54	F	1
PW-2328MT	55	F	1

Product Code	page, column, row		
PWF Whiteboard			
PWF-500	12		

Product Code	page, column, row		
RT Aged Metal			
RT-1111	25	G	3
RT-1112	23	F	1
RT-1827	25	G	1

Product Code	page, column, row		
SI Silk			
SI-1686	48	A	3
SI-1688	49	C	5

Product Code	page, column, row		
ST Stone			
ST-1586	33	E	1
ST-1587	33	F	2
ST-1588	33	A	4
ST-1828	35	A	3
ST-1829	35	A	4
ST-1831	33	A	3
ST-1911MT	35	A	2
ST-1914MT	33	A	2
ST-1915MT	35	B	2
ST-1918MT	35	E	1
ST-1919MT	35	B	1
ST-1920MT	33	G	2
ST-1927MT	33	B	4
ST-2170MT	35	C	1
ST-2171MT	35	F	1
ST-2530MT	33	A	1
ST-2531MT	33	C	1
ST-2532MT	33	B	2
ST-2533MT	33	B	3
ST-2534MT	33	D	2
ST-2535MT	33	D	3
ST-2536MT	33	D	4
ST-2537MT	33	F	1
ST-2538MT	33	F	3
ST-2539	35	D	2
ST-2540MT	35	F	2
ST-2541MT	35	B	3
ST-2542MT	35	D	3

Product Code	page, column, row		
SU Suede			
SU-2231MT	47	D	3
SU-2232MT	47	C	1
SU-2233MT	47	E	1
SU-2234MT	47	E	3
SU-2235MT	47	E	5

Product Code	page, column, row		
TE Advanced Metallic			
TE-1650	51	G	1
TE-1713	51	E	2

Product Code	page, column, row		
TIL For Tile Application			
AE-1632TIL	11	B	1
AE-1634TIL	11	B	2
AE-1913TIL	11	B	4
AE-2152TIL	11	A	5
AE-2153TIL	11	C	5
FA-020TIL	11	C	3
FA-021TIL	11	C	2
PS-009TIL	11	A	1
PS-010TIL	11	A	2
PS-012TIL	11	A	3
PS-982TIL	11	A	4
PT-346TIL	11	C	1
ST-024TIL	11	D	1
ST-736TIL	11	D	3
ST-737TIL	11	E	3
ST-1195TIL	11	B	3
ST-1831TIL	11	D	2
ST-1914TIL	11	E	2
ST-1920TIL	11	D	5
ST-2171TIL	11	D	4

Product Code	page, column, row		
VM Premium Metal			
VM-305	27	F	3
VM-1487	27	E	3
VM-1488	27	E	5
VM-1489	27	G	5
VM-1691	27	E	1
VM-1692	27	F	1
VM-1693	27	G	1
VM-1694	27	E	4
VM-1695	27	E	2
VM-2035	27	G	2
VM-2036	27	H	4
VM-2037	27	H	2
VM-2090	27	G	3
VM-2360	27	A	1
VM-2361	27	A	3
VM-2362	27	A	5
VM-2363	27	C	1
VM-2364	27	C	2
VM-2365	27	C	4
VM-2366	27	C	5

Product Code	page, column, row		
WG Wood Grain			
WG-156	75	F	5
WG-157	74	G	5
WG-166	72	G	3
WG-247	72	A	4
WG-250	73	D	1
WG-256	73	C	3
WG-364	74	G	4
WG-364GN	74	C	2
WG-376	72	E	2
WG-417	74	H	1
WG-428	75	G	5
WG-453	73	C	2
WG-467	72	F	1
WG-629	73	H	2
WG-657	72	A	1
WG-664	75	G	4
WG-693	74	H	4
WG-695	75	D	3
WG-696	75	A	2
WG-697	74	F	5
WG-699	73	F	2

Product Code	page, column, row		
WG-709	73	G	2
WG-763	74	F	1
WG-763GN	74	C	1
WG-831	73	G	1
WG-832	73	A	5
WG-833	73	A	4
WG-835	73	C	1
WG-836	74	E	1
WG-837	73	B	3
WG-841	74	E	2
WG-845	73	D	3
WG-846	73	D	4
WG-854	74	E	3
WG-865	74	F	3
WG-877	73	E	2
WG-878	73	G	3
WG-879	74	F	2
WG-943	74	G	1
WG-947	75	A	3
WG-960	72	C	5
WG-964	72	H	3
WG-1044	75	G	1
WG-1046	72	D	1
WG-1050	75	H	5
WG-1058	73	H	4
WG-1067	72	E	1
WG-1070	75	H	2
WG-1140	74	E	5
WG-1141	72	D	3
WG-1142	74	E	4
WG-1143	72	F	4
WG-1144	72	G	2
WG-1146	74	H	3
WG-1147	74	H	2
WG-1196	75	C	5
WG-1219	73	A	1
WG-1220	72	F	2
WG-1221	73	A	2
WG-1336	75	A	4
WG-1337	72	H	5
WG-1339	72	D	2
WG-1340	72	C	3
WG-1342	75	B	4
WG-1343	72	B	2
WG-1344	72	B	3
WG-1346	73	E	1
WG-1348	75	D	2
WG-1353	75	B	1
WG-1358	73	F	3
WG-1360	73	G	5
WG-1364	75	F	4
WG-1365	72	A	2
WG-1368	75	C	1
WG-1369	75	E	1
WG-1370	75	D	5
WG-1371	75	E	2
WG-1373	75	F	3
WG-1375	74	G	2
WG-1703	75	A	1
WG-1704	75	E	5
WG-1705	72	A	5
WG-1708	75	C	3
WG-1709	72	A	3
WG-1710	72	H	4
WG-1711GN	74	A	1
WG-1812	73	A	3
WG-1814	73	D	5
WG-1815	73	F	4
WG-1835	75	H	4
WG-1836	75	E	4
WG-1837	72	G	5
WG-1838	72	E	5
WG-1840	72	F	5
WG-1841	75	F	1
WG-1845	73	F	1
WG-1846	72	C	1
WG-1848	75	D	1
WG-2019	75	F	2
WG-2033	75	E	3
WG-2041	75	H	3
WG-2042	75	C	2
WG-2047	75	G	2
WG-2049	72	C	2
WG-2071	73	G	4
WG-2073	72	G	1
WG-2075	75	A	5
WG-2076	61	D	1
WG-2078	61	C	1
WG-2082H	75	B	3
WG-2083H	72	C	4

Product Code	page, column, row		
WG-2084H	75	C	4
WG-2085	72	F	3
WG-2115	73	E	5
WG-2246	73	B	5
WG-2430	71	C	2
WG-2431	71	D	2
WG-2432	71	E	2
WG-2433	71	F	2
WG-2434	71	G	2
WG-2440	71	C	1
WG-2441	71	D	1
WG-2442	71	E	1
WG-2443	71	F	1
WG-2444	71	G	1
WG-2450	71	C	4
WG-2451	71	D	4
WG-2452	71	E	4
WG-2453	71	F	4
WG-2454	71	G	4
WG-2460	71	C	3
WG-2461	71	D	3
WG-2462	71	E	3
WG-2463	71	F	3
WG-2464	53		
	71	G	3
WG-2707	75	G	3
WG-2839	73	C	5
WG-2862	74	F	4
WG-2944	73	B	4
WG-7022	74	G	3
WG-7024	74	H	5

Product Code	page, column, row		
WH Whiteboard			
WH-111	12		

Index

Wood Species

Product Code	page, column, row
Alder	
WG-841	74 E 2
Anigre	
FW-232	67 B 2
FW-888	66 C 4
Ash	
DW-1885MT	59 G 1
DW-1898MT	59 C 3
DW-2201MT	56 D 3
FW-336	62 F 1
FW-337 (AR)	63 E 2
FW-1258	64 E 1
FW-1259	63 D 1
FW-1293 (AR)	64 G 2
FW-1294 (AR)	63 D 4
FW-1296	65 C 3
FW-1972	64 G 4
WG-156	75 F 5
WG-467	72 F 1
WG-947	75 A 3
WG-960 (EX)	72 C 5
WG-1143 (EX)	72 F 4
WG-1343	72 B 2
WG-1344	72 B 3
WG-1346	73 E 1
WG-1348	75 D 2
WG-1353	75 B 1
WG-2073	72 G 1
WG-2075	75 A 5
WG-2839	73 C 5
Beech	
DW-2198MT	56 D 2
FW-327	66 A 1
Birch	
FW-1211	64 A 2
FW-1212	65 A 1
Bird's Eye Maple	
WG-763	74 F 1
WG-763GN	74 C 1
Black Limba	
WG-1196	75 C 5
Bubingha	
WG-364	74 G 4
WG-364GN	74 C 2
Camphor Tree	
DW-2209MT	57 F 4
DW-2216MT	58 E 4
FW-7011 (AR, EX)	65 D 3
Cedar	
DW-2229MT	59 F 3
WG-846	73 D 4
Cherry	
DW-1901MT	57 E 2
DW-2202MT	56 G 1
DW-2476MT	56 A 3
FW-234	66 B 1
FW-612	66 C 3
FW-655	66 F 1
FW-1279	64 F 3
FW-1280 (AR)	66 C 2
FW-1282	68 D 2
FW-1283	66 A 3
FW-1737	66 A 2
FW-1738	66 F 2
WG-629	73 H 2
WG-865	74 F 3
WG-877	73 E 2
WG-878	73 G 3
WG-1058	73 H 4
WG-1142	74 E 4
WG-1360	73 G 5
WG-1364	75 F 4
WG-1375	74 G 2
WG-1815	73 F 4
WG-1845	73 F 1
WG-1846	72 C 1
Chestnut	
DW-1875MT	56 D 4
DW-1876MT	57 E 4
DW-2207MT	57 E 3
DW-2479MT	56 E 3
FW-1217	62 F 2
FW-1810	64 G 3
FW-1976	63 A 3
FW-1977	63 D 2
FW-1988	64 G 1
PW-2306MT	54 E 3
WG-2071	73 G 4
Design Wood	
FW-1757	69 F 4
FW-1761	62 A 1
MW-1416	61 F 1
WG-417	74 H 1
WG-428	75 G 5
WG-657 (EX)	72 A 1
Ebony	
MW-777	61 F 4
WG-664	75 G 4
WG-1070	75 H 2
Elm	
DW-1871MT	59 D 3

Product Code	page, column, row
DW-2477MT	56 E 1
FW-1214 (EX)	64 F 1
FW-1215	63 E 1
FW-1216	69 A 1
FW-1265	65 A 2
FW-1266	63 C 4
FW-1746	68 A 1
FW-2422	63 B 3
PW-2316MT	55 D 4
WG-1044 (EX)	75 G 1
WG-1046	72 D 1
Hawaiian Koa	
PW-2327MT	54 F 1
Hickory	
FW-1978	63 B 2
FW-1979	69 G 1
PW-2305MT	54 A 1
Hinoki	
FW-1981	64 A 1
WG-453	73 C 2
WG-845	73 D 3
Ipe	
FW-1974	63 A 1
FW-1975	69 D 2
Magnolia	
FW-1138 (AR)	62 C 3
Mahogany	
DW-2481MT	58 C 1
FW-677	67 C 3
FW-886	67 A 4
FW-887 (EX)	67 B 4
PW-2328MT	55 F 1
WG-1146	74 H 3
Maple	
DW-1873MT	57 G 4
DW-1874MT	58 B 4
DW-2200MT	56 C 4
FW-1261	62 G 1
FW-1262	64 F 2
WG-831	73 G 1
WG-832	73 A 5
WG-833	73 A 4
WG-835	73 C 1
WG-836	74 E 1
WG-837	73 B 3
WG-879	74 F 2
WG-1814	73 D 5
Oak	
DW-1877MT	59 C 1
DW-1878MT	57 F 1
DW-1883MT	57 G 3
DW-1884MT	58 A 3
DW-1887MT	59 G 2
DW-1888MT	56 C 3
DW-1893MT	56 B 4
DW-1897MT	57 C 4
DW-1993MT	56 G 3
DW-2199MT	56 C 2
DW-2204MT	57 E 1
DW-2205MT	57 C 1
DW-2206MT	57 D 1
DW-2208MT	57 F 2
DW-2210MT	61 D 3
DW-2223MT	59 C 2
DW-2225MT	59 C 4
DW-2470MT	56 A 1
DW-2471MT	56 A 2
DW-2472MT	57 A 3
DW-2473MT	57 C 2
DW-2478MT	57 A 1
FW-236 (AR, EX)	65 D 1
FW-237	66 C 1
FW-625 (AR, EX)	68 A 2
FW-627 (EX)	68 F 3
FW-788	62 C 2
FW-1127	69 F 1
FW-1129 (AR, EX)	64 C 1
FW-1130H	64 C 2
FW-1255	62 D 1
FW-1256	64 B 1
FW-1257	65 F 1
FW-1285	64 C 4
FW-1286	65 F 2
FW-1291	64 B 2
FW-1306	61 C 3
FW-1765	62 C 1
FW-1766	64 C 3
FW-1767	63 A 4
FW-1770	63 F 2
FW-1986	69 B 1
FW-1987	63 B 1
FW-2420	62 D 2
FW-2421	64 D 2
FW-2423	64 A 3
FW-2424	64 D 4
FW-2426	61 A 3
FW-7017 (AR)	62 A 2
MW-1832	61 F 2
PW-2307MT	54 E 2
PW-2308MT	55 C 2
PW-2309MT	54 E 1
PW-2310MT	55 C 1
PW-2311MT	55 C 3
PW-2323MT	54 C 3
PW-2324MT	55 A 3
PW-2326MT	54 C 1
WG-166	72 G 3
WG-256	73 C 3
WG-376	72 E 2
WG-695 (EX)	75 D 3
WG-696	75 A 2
WG-697	74 F 5
WG-854	74 E 3
WG-943	74 G 1

Product Code	page, column, row
WG-964	72 H 3
WG-1050	75 H 5
WG-1144 (EX)	72 G 2
WG-1219	73 A 1
WG-1220	72 F 2
WG-1221	73 A 2
WG-1339	72 D 2
WG-1340	72 C 3
WG-1342	75 B 4
WG-1358	73 F 3
WG-1710	72 H 4
WG-1835	75 H 4
WG-1838	72 E 5
WG-2047	75 G 2
WG-2049	72 C 2
WG-2076	61 D 1
WG-2085	72 F 3
WG-2115	73 E 5
WG-2430	71 C 2
WG-2431	71 D 2
WG-2432	71 E 2
WG-2433	71 F 2
WG-2434	71 G 2
WG-2440	71 C 1
WG-2441	71 D 1
WG-2442	71 E 1
WG-2443	71 F 1
WG-2444	71 G 1
WG-2944	73 B 4
Padauk	
FW-240	67 A 3
WG-1147	74 H 2
WG-7024 (EX)	74 H 5
Paldao	
FW-324 (EX)	69 B 2
Pear	
WG-699	73 F 2
WG-2246	73 B 5
Pine / Larch	
DW-2219MT	59 A 1
FW-641	69 E 2
FW-1307	63 A 2
FW-1970	69 F 2
FW-2425	61 A 1
WG-2078	61 C 1
Plum	
WG-1067	72 E 1
Primavera	
WG-693	74 H 4
Redwood	
MW-1418	61 G 1
MW-1419	61 F 3
Rosewood	
FW-1135	68 C 3
FW-1136H	68 C 4
Silver Heart	
WG-250	73 D 1
Sina	
WG-1812	73 A 3
Sycamore	
WG-247	72 A 4
WG-709	73 G 2
WG-171GN	74 A 1
Teak	
DW-1902MT	56 G 2
DW-2475MT	58 A 1
FW-1039H	67 A 2
FW-1124 (EX)	67 A 1
FW-1125	66 D 3
FW-1272	64 F 4
FW-1273	63 D 3
FW-1302	63 B 4
FW-1805 (EX)	65 C 4
FW-7007	69 A 2
FW-7015	68 E 4
PW-2325MT	54 F 3
WG-157	74 G 5
WG-1140 (EX)	74 E 5
WG-1141	72 D 3
WG-7022	74 G 3
Tineo	
WG-1336	75 A 4
WG-1337	72 H 5
Tong	
FW-640 (EX)	69 D 1
Walnut	
DW-1882MT	58 G 2
DW-1889MT	57 G 1
DW-1891MT	58 G 1
DW-1899MT	58 E 1
DW-1900HMT	58 E 2
DW-2197MT	56 C 1
DW-2203MT	56 G 4
DW-2211MT	58 A 4
DW-2212MT	58 B 3
DW-2213MT	58 E 3
DW-2214MT	58 F 3
DW-2215MT	58 F 4
DW-2217MT	58 G 4
DW-2218MT	56 A 4
DW-2221MT	59 A 4
DW-2222MT	59 E 1
DW-2474MT	58 C 3
DW-2480MT	59 A 2
FW-233 (AR, EX)	66 F 3
FW-330 (EX)	68 D 3
FW-332	67 G 4

Product Code	page, column, row
FW-338 (AR)	68 B 1
FW-502	65 D 4
FW-510	67 B 3
FW-608H	66 D 2
FW-609H (EX)	67 G 2
FW-613	67 C 1
FW-650 (EX)	67 C 2
FW-651 (EX)	68 B 3
FW-795	66 B 3
FW-1021	65 F 3
FW-1022 (AR, EX)	67 F 1
FW-1023 (EX)	65 B 2
FW-1113 (EX)	67 F 3
FW-1121H	67 F 2
FW-1122 (AR, EX)	65 A 3
FW-1123 (EX)	66 D 1
FW-1207	62 D 4
FW-1208	62 B 4
FW-1331	66 E 2
FW-1683	62 A 4
FW-1735H	61 C 4
FW-1743	66 A 4
FW-1744	67 D 4
FW-1751	69 D 3
FW-1755	65 B 1
FW-1801 (EX)	67 F 4
FW-1983	63 F 1
FW-2427	67 D 2
FW-7006 (EX)	67 C 4
FW-7008 (EX)	67 D 1
FW-7009	68 D 1
PW-2312MT	54 E 4
PW-2313MT	55 C 4
PW-2314MT	55 F 3
PW-2315MT	55 D 1
PW-2319MT	55 F 4
PW-2320MT	54 A 3
PW-2321MT	55 A 1
PW-2322MT	55 D 2
WG-1365	72 A 2
WG-1368	75 C 1
WG-1369	75 E 1
WG-1370	75 D 5
WG-1371	75 E 2
WG-1373	75 F 3
WG-1703	75 A 1
WG-1704	75 E 5
WG-1705	72 A 5
WG-1708	75 C 3
WG-1709	72 A 3
WG-1836	75 E 4
WG-1837	72 G 5
WG-1841	75 F 1
WG-1848	75 D 1
WG-2019	75 F 2
WG-2033	75 E 3
WG-2041	75 H 3
WG-2042	75 C 2
WG-2082H	75 B 3
WG-2083H	72 C 4
WG-2084H	75 C 4
WG-2450	71 C 4
WG-2451	71 D 4
WG-2452	71 E 4
WG-2453	71 F 4
WG-2454	71 G 4
WG-2460	71 C 3
WG-2461	71 D 3
WG-2462	71 E 3
WG-2463	71 F 3
WG-2464	71 G 3
WG-2862	74 F 4

Zebra Wood	
FW-606H	68 A 4
FW-607H	68 B 4
FW-656	68 A 3
WG-2707	75 G 3

Ready to create your masterpiece?

See and feel our surface finishes.
Request for your free sample.

[Request a Sample ▶](#)

Have questions or need help in
choosing the right surface finishes?

[Contact a 3M Expert ▶](#)



3M, Comply, and DI-NOC are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycled. © 3M 2024. All rights reserved.



Cover made from 100% recycled paper and pages made from 70% recycled paper, all printed with vegetable oil based ink.



Ver.1

UU-0128-5505-0
7100319221
DIN-403-A