



# 3M™ PPS™ Series 2.0 Adapters by Spray Gun Manufacturer

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Accuspray	07	S7	26008
Accuspray	07HS	S7	26008
Accuspray	10g	S7	26008
Accuspray	10gp	S7	26008
Accuspray	10	S18	26054
Accuspray	12s	S18	26054
Accuspray	19	S18	26054
Accuspray	19c	S18	26054
Accuspray	12sz	S3	26131
Accuspray	PerforMax 05-100 Primer	S9	26016
Accuspray	PerforMax 05-300 Mini	S21	26105
ADIR	Gravity Series	S2	26003
Advantage	90115	S2	26003
Aerometal	Super Fura 34	S6	26007
Aerometal	2100 ECO&T	S6	26007
Aerometal	Victoria 92	S6	26007
Aerometal	2015 ECO&T	S6	26007
Aerometal	2016	S6	26007
AES	150	S2	26003
AirGunsa	AZ3 HV	S6	26007
AirGunsa	AZ3 HTE	S6	26007
AirGunsa	AZ3 HTE 2	S43	26139
AirVerter	CT-100 Mini	S21	26105
AirVerter	GG-100	S2	26003
AirVerter	MF-3100	S18	26054
American Turbine	223xx series	S18	26054
American Turbine	225xx series	S33	26128
AmPro	AR6025	S2	26003
AmPro	AR6029 Mini	S21	26105
ANI	F1-s HPS	S15	26046
ANI	R1 Mini	S12	26022
Apollo	A5011	S18	26054
Apollo	A5125	S18	26054
Apollo	A5510	S18	26054
Apollo	A5610	S18	26054
Apollo	A7500	S18	26054
Apollo	A5520 Mini	S23	26109
Apollo	A8200	S10	26017
Apollo	A8400	S10	26017
Astro	Euro HE 103	S9	26016
Astro	Euro HE 105	S9	26016
Astro	Euro HE 107	S9	26016
Astro	Euro HE 109	S9	26016
Astro	Euro HV 103	S9	26016
Astro	Euro HV 105	S9	26016
Astro	Euro HV 107	S9	26016
Astro	Euro HV 109	S9	26016
Astro	EVO 4014	S2	26003
Astro	EVO 4018	S2	26003
Astro	M-Star	S2	26003
Astro	Quantum Ultra Light	S2	26003
Astro	Star QUL	S2	26003

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Astro	Euro Pro	S27	26119
Astro	4020 Mini	S21	26105
Astro	GF6S Mini	S21	26105
Astro	GF6S Mini HVLP	S21	26105
Asturo	ECO/SSP	S18	26054
Asturo	ECO/SX	S2	26003
Asturo	ECO/S	S2	26003
Asturo	Gravity Series	S6	26007
Asturomec	9011 Series	S8	26015
ATD	Gravity Series	S2	26003
ATD	Leonardo 6865	S9	26016
ATD	Leonardo 6872	S9	26016
ATD	Leonardo 6913	S9	26016
ATD	Leonardo 6914	S9	26016
ATD	Leonardo 6915	S9	26016
ATD	Leonardo 6918	S9	26016
ATD	Leonardo 6910 Mini	S6	26007
ATD	6845 Mini	S21	26105
ATD	6900 Series	S2	26003
ATD	6900 Series Mini	S21	26105
Balkamp (NAPA)	Mini	S23	26109
Binks	MGI 1.8 Primer	S15	26046
Binks	115 Mini Siphon	S23	26109
Binks	630	S15	26046
Binks	95G	S15	26046
Binks	95	S18	26054
Binks	95 SL	S18	26054
Binks	95 SLV	S18	26054
Binks	BBR	S15	26046
Binks	BHV	S27	26119
Binks	Cub SL Mini Siphon	S23	26109
Binks	Cub SLG Mini Gravity	S14	26053
Binks	M1-G	S15	26046
Binks	Mach 1	S18	26054
Binks	Mach 1SL	S18	26054
Binks	Mach 1 Featherlite	S18	26054
Binks	Model 2001	S18	26054
Binks	Model 2001 SS	S18	26054
Binks	Model 2001 V	S18	26054
Binks	Model 7	S18	26054
Binks	SV-100 Gravity	S11	26018
Binks	SV-100 Siphon	S18	26054
Binks	SV-50 Pro Series	S27	26119
C.A. Technologies	Jaguar J100H	S2	26003
C.A. Technologies	Jaguar SLP	S2	26003
C.A. Technologies	Jaguar 100C	S2	26003
C.A. Technologies	Jaguar 300C	S2	26003
C.A. Technologies	Panther P100G	S18	26054
C.A. Technologies	Techline T3	S2	26003
C.A. Technologies	Techline TJR	S21	26105
C.A. Technologies	CAT X Gravity Series	S27	26119
Campbell Hausfeld	DH-6500	S2	26003



# 3M™ PPS™ Series 2.0 Adapters by Spray Gun Manufacturer

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Campbell Hausfeld	DH-7800	S2	26003
Campbell Hausfeld	DH-7900	S2	26003
Campbell Hausfeld	Mini Siphon	S23	26109
CAPspray	Maxum Elite II Bottom Feed	S18	26054
CAPspray	Maxum Elite II Gravity Feed	S7	26008
CAPspray	CS 3100	S18	26054
CAPspray	CS 5100	S18	26054
CAPspray	CS 8100	S18	26054
CAPspray	CS 9100	S18	26054
CAPspray	CS 9900	S18	26054
CAPspray	3100H Siphon Series	S18	26054
CAPspray	3100C Siphon Series	S18	26054
CAPspray	3100 Gravity Series	S2	26003
CAPspray	Mini	S21	26105
CarQuest	ProValue 2304-PV	S2	26003
CarQuest	ProValue 2305-PV	S2	26003
Central Pneumatic	Gravity Series	S2	26003
Central Pneumatic	Mini	S21	26105
Central Pneumatic	Professional	S27	26119
Central Pneumatic	Professional Mini	S8	26015
Cornwell	PSG-1200 Mini	S21	26105
Cornwell	PSG-1400	S2	26003
Craftsman	9-15002 Mini	S23	26109
Craftsman	9-15519	S18	26054
Craftsman	9-15531	S2	26003
Craftsman	9-15535 Siphon	S18	26054
Dart Products	AB17G	S2	26003
Dart Products	H827A	S2	26003
Dart Products	H881A	S2	26003
Dart Products	H2000MG Mini	S21	26015
Defynik	Gravity Series	S5	26006
DeVilbiss	Compact Mini HVLP	S14	26053
DeVilbiss	Compact Mini Trans Tech	S14	26053
DeVilbiss	Compact 506 gravity	S15	26046
DeVilbiss	Compact 506 siphon/pressure	S18	26054
DeVilbiss	Compact 507	S18	26054
DeVilbiss	Compact 510 Trans Tech Gravity	S15	26046
DeVilbiss	Compact 510 Trans Tech Siphon	S18	26054
DeVilbiss	CVi 522G	S15	26046
DeVilbiss	CVi 620G	S15	26046
DeVilbiss	CVi 620GW	S15	26046
DeVilbiss	dRd	S15	26046
DeVilbiss	DV1	S15	26046
DeVilbiss	DVIS Smart Repair Gun	S14	26053
DeVilbiss	EGA-503 Mini Siphon	S23	26109
DeVilbiss	EXL 620G	S15	26046
DeVilbiss	Finishline NTL-1261	S4	26005
DeVilbiss	Finishline FLG4 gravity models	S15	26046
DeVilbiss	Finishline FLG4 siphon models	S18	26054
DeVilbiss	Finishline FLG-635	S15	26046
DeVilbiss	Finishline FLG-615	S15	26046
DeVilbiss	Finishline FLG-647-WB	S15	26046

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
DeVilbiss	Finishline FLG-648	S15	26046
DeVilbiss	Finishline FLG-606	S18	26054
DeVilbiss	Finishline FLG-626	S18	26054
DeVilbiss	Finishline FLG-651G	S15	26046
DeVilbiss	Finishline FLG-695	S15	26046
DeVilbiss	Finishline FLG-653G	S15	26046
DeVilbiss	Finishline FLG-643	S15	26046
DeVilbiss	Finishline FLG-645	S15	26046
DeVilbiss	Finishline FLG-654	S15	26046
DeVilbiss	Finishline FLG-691	S15	26046
DeVilbiss	Finishline FLG-693	S18	26054
DeVilbiss	Finishline FLG-694	S18	26054
DeVilbiss	FinishLine Master Kit Mini	S26	26118
DeVilbiss	FinishLine Master Kit Std.	S27	26119
DeVilbiss	StartingLine Mini	S26	26118
DeVilbiss	StartingLine Std.	S27	26119
DeVilbiss	FUN, Gravity	S10	26017
DeVilbiss	FUN, Siphon	S25	26116
DeVilbiss	GFG-5	S15	26046
DeVilbiss	GFG-516	S15	26046
DeVilbiss	GFG-517	S15	26046
DeVilbiss	GFG-618	S15	26046
DeVilbiss	GFG-670 PLUS	S15	26046
DeVilbiss	GFHV-510	S15	26046
DeVilbiss	GTI 600G	S15	26046
DeVilbiss	GTI 625G Waterborne	S15	26046
DeVilbiss	GTI Millennium 620G	S15	26046
DeVilbiss	GTI Millennium 620S	S18	26054
DeVilbiss	GTI Millennium 2000	S15	26046
DeVilbiss	GTI Pro Base	S15	26046
DeVilbiss	GTI Pro Clear	S15	26046
DeVilbiss	GTI Pro Digital	S15	26046
DeVilbiss	GTIW Waterborne	S15	26046
DeVilbiss	JGA-510-57D	S18	26054
DeVilbiss	JGA-510-57DE	S18	26054
DeVilbiss	JGA-535G	S15	26046
DeVilbiss	JGA-635G	S15	26046
DeVilbiss	JGA-636	S18	26054
DeVilbiss	JGA-644	S18	26054
DeVilbiss	JGA-504	S18	26054
DeVilbiss	JGA-670 PLUS	S18	26054
DeVilbiss	JGX-501	S10	26017
DeVilbiss	JGX-502	S10	26017
DeVilbiss	PRI 601G Primer	S15	26046
DeVilbiss	Sri Mini	S14	26053
DeVilbiss	SRIW Mini	S14	26053
DeVilbiss	Sri Pro Mini	S14	26053
DeVilbiss	TEKNA	S15	26046
DeVilbiss	TEKNA Clearcoat	S15	26046
DeVilbiss	TEKNA ProLite	S15	26046
DeVilbiss	TEKNA QuickClean	S15	26046
DeVilbiss	TEKNA Copper	S15	26046



# 3M™ PPS™ Series 2.0 Adapters by Spray Gun Manufacturer

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
DeVilbiss	TGHV530	S18	26054
DeVilbiss	EXL 520S	S18	26054
DeVilbiss	EGHV-531 Mini	S23	26109
DeVilbiss	TGHV-635 Mini	S10	26017
DeVilbiss	VTX	S18	26054
Dura-Block	AF900K	S2	26003
Dura-Block	007 Extreme Performance	S2	26003
Dura-Block	Mini	S21	26105
Durr	EcoGun 119	S44	26141
Durr	EcoGun 910	S44	26141
DUX	Gravity Series	S5	26006
Earlex	HV5000	S18	26054
Earlex	Sprayport Pro-8 GrAVITY Feed HVLP	S15	26046
Ecco	652-S	S15	26046
Eclipse	8200	S18	26054
Eminent	E13	S6	26007
Evercraft (NAPA)	BK7703758	S2	26003
Fuji	T-70	S18	26054
Fuji	XPC	S18	26054
Fuji	M-Model	S18	26054
Fuji	MPX-30 Siphon	S18	26054
Fuji	LX-20 Pressure	S18	26054
Fuji	XT	S18	26054
Fuji	XT-2	S18	26054
Fuji	T75G	S2	26054
Fuji	MPX-30 Gravity	S2	26003
Fuji	LX-20 Gravity	S2	26003
Fuji	Touch Uyp Spray Gun (9622)	S23	26109
Fuji	G-XPC	S24	26110
Fuji	GT-X2	S24	26110
Goni	321	S2	26003
Graco	600 Side Cup Mount	S10	26017
Graco	AirPro Gravity	S37	26132
Graco	AirPro Siphon	S18	26054
Graco	Delta GF	S15	26046
Graco	LT100 Mini	S21	26105
Graco	LT200	S2	26003
Graco	LT300	S2	26003
Graco	FinishPro HVLP Edge	S18	26054
Grip	H827W	S2	26003
Grip	Mini	S21	26105
Grizzly	H7669	S2	26003
Husky	HDS-540 Mini	S23	26109
Husky	HDS-550 Mini	S23	26109
Husky	HDS-650	S18	26054
Husky	HDS-780	S2	26003
Husky	HDS-790	S2	26003
Husky	HDS-890 Pro	S2	26003
Ingersol Rand	200G	S21	26105
Ingersol Rand	210G	S2	26003
Ingersol Rand	270G	S2	26003
Ingersol Rand	9115	S30	26126

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Ingersol Rand	PF260 PowerForce	S30	26126
Iwata	LPA-94	S2	26003
Iwata	LPH-100	S10	26017
Iwata	W-100G	S10	26017
Iwata	W101 Gravity Side Mount	S45	26140
Iwata	LPH-300	S6	26007
Iwata	LPH440 Primer	S2	26003
Iwata	LPH-50 Mini	S10	26017
Iwata	LPH-80 Mini	S31	26127
Iwata	LPSI	S19	26103
Iwata	RG3L Mini Air Brush	S10	26017
Iwata	VX929	S2	26003
Iwata	VXL949 Primer	S2	26003
Iwata	W100 Siphon	S25	26116
Iwata	W101 Siphon	S19	26103
Iwata	W200 Siphon	S19	26103
Iwata	W300	S6	26007
Iwata	W300LV	S6	26007
Iwata	W400	S2	26003
Iwata	W400LV	S2	26003
Iwata	W71 Gravity Side Mount	S10	26017
Iwata	W71 Siphon	S25	26116
Iwata	W71 Pressure	S25	26116
Iwata	W77 Gravity Side Mount	S42	26138
Iwata	W77 Siphon	S19	26103
Iwata	W77 Pressure	S19	26103
Iwata	LPH101 LVS	S25	26116
Iwata	WR-400	S2	26003
Iwata	LPH400 LV	S2	26003
Iwata	LPH400 LVB	S2	26003
Iwata	LPH400 LVX	S2	26003
Iwata	Supernova LS-400	S43	26139
Iwata	Supernova WS-400	S43	26139
Iwata	AZ3 HTE 2	S43	26139
Jafe (Spain)	Activa 5500G	S2	26003
Jafe (Spain)	Activa 4400G	S5	26006
Jafe (Spain)	Prima 60G	S5	26006
Jafe (Spain)	Prima 100G	S5	26006
Jet	Jat-500	S2	26003
Jet	Jat-500	S2	26105
Jobsmart	HVLP	S2	26129
Jonnesway	JA-6111	S2	26003
Kobalt (Lowe's)	KC-566CG	S2	26003
Kobalt (Lowe's)	KC-577HG	S2	26003
Kobalt (Lowe's)	SGY-AIR86	S2	26003
Kobalt (Lowe's)	SGY-AIR88	S2	26003
Kobalt (Lowe's)	SGY-AIR87	S24	26110
Kobalt (Lowe's)	KC-588CSCG	S24	26110
Kobalt (Lowe's)	KC-599CS Siphon	S18	26054
Krautzberger	HS-25	S28	26120
Krautzberger	SM-901	S28	26120
Krautzberger	Mignon 3	S5	26006



# 3M™ PPS™ Series 2.0 Adapters by Spray Gun Manufacturer

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Kremlin	M21-G	S6	26007
Kremlin	M22	S6	26007
Kremlin	Hti-G	S6	26007
Kremlin	S3G HPA	S6	26007
Lex-Aire	Pro Series RS gravity	S35	26130
Lex-Aire	Pro Series RS bottom	S18	26054
Mac	SG1100-10 Mini	S21	26105
Mac	SG1250 Series	S2	26003
Mac	SG1300 Series	S2	26003
Mac	SG610K	S15	26046
Mac	Econocoat	S2	26003
Mark I	AF7002 Mini	S21	26105
Mark I	AF7003	S2	26003
Matco	Gravity Series	S2	26003
Matco	MTPG14	S35	26130
Matco	MTPGHE13	S9	26016
Matco	MTPGHE15	S9	26016
Matco	MTDPGHV1 Detail Gun	S21	26105
Matco	MTDPGHV8 Detail Gun	S21	26105
Matco	MTPGHV13	S35	26130
Matco	MTPGHV15	S35	26130
Matco	MTPGHV17	S35	26130
Matco	MTPGHV19	S35	26130
Matco	RL-75 Mini	S21	26105
Matco	MTHVLP 13	S27	26119
Matco	MTHVLP 14	S27	26119
Max Air	W98	S2	26003
Mechanics	M576DB	S18	26054
Meiji	FSA Mini	S10	26017
Meiji	F410	S15	26046
Mountain	Mtn 4007	S18	26054
Mountain	Mtn 4008	S18	26054
Mountain	Star Mini	S21	26105
MSB	Gravity Series	S2	26003
M-Star	Gravity Series	S2	26003
NAPA (Evercraft)	#BK7703758	S2	26003
NESCO	808 Mini	S21	26105
NESCO	840	S2	26003
NESCO	868	S2	26003
NESCO	870	S2	26003
NESCO	880	S9	26016
NESCO	NP 802 Mini Siphon	S23	26109
Nikota	HVLP-G	S2	26003
Optima	500	S7	26008
Optima	550i	S7	26008
Optima	650i	S44	26141
Optima	800	S7	26008
Optima	700	S18	26054
Optima	800i	S18	26054
Optima	800C	S7	26008
Optima	800L	S7	26008
Optima	Euro 900/900L	S7	26008

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Optima	910	S1	26043
Porter-Cable	PSH-1	S2	26003
Porter-Cable	PSH-3	S2	26003
Porter-Cable	PSH2 Mini	S21	26105
Powerfist	PR100 HVLP Gravity	S2	26003
PRO-TEK	2500 Mini	S21	26105
PRO-TEK	2550 Mini	S21	26105
PRO-TEK	2600	S2	26003
PRO-TEK	4000GH	S2	26003
PRO-TEK	764x	S2	26003
ProValue (Carquest)	2304-PV	S2	26003
ProValue (Carquest)	2305-PV	S2	26003
Sagola	403-G	S5	26006
Sagola	433-G	S5	26006
Sagola	434-G	S5	26006
Sagola	444-G	S5	26006
Sagola	3300-G	S5	26006
Sagola	4600	S32	26136
Sagola	4100-G	S5	26006
Sagola	4200-G	S5	26006
Sagola	Classic Pro	S5	26006
Sagola	Mini Xtreme	S5	26006
Sagola	4400 Xtreme	S32	26136
Sagola	4500 Xtreme	S32	26136
Sagola	4100 GTO	S32	26136
Sagola	Junior G	S13	26043
Sagola	Classic LUX	S6	26007
Sagola	475 Mini	S12	26022
SATA	Dekor 2000	S12	26022
SATA	KLC-B	S9	26016
SATA	KLC-P	S9	26016
SATA	KLC-RP	S9	26016
SATA	KL-Primer	S5	26006
SATA	LM 2000 B	S9	26016
SATA	LM 2000 K	S9	26016
SATA	LM 2000 H RP	S18	26054
SATA	LM-92	S9	26016
SATA	MCB Primer	S9	26016
SATA	MCB-90	S9	26016
SATA	MCB-93	S5	26006
SATA	Minijet 1	S12	26022
SATA	Minijet 2	S12	26022
SATA	Minijet 3	S12	26022
SATA	Minijet 4 HVLP QCC	S41	26137
SATA	Minijet 4400 B HVLP QCC	S40	26135
SATA	Minijet 4400 B RP QCC	S40	26135
SATAjet	100 BF HVLP QCC	S40	26135
SATAjet	100 BF RP QCC	S40	26135
SATAjet	100 BP QCC	S40	26135
SATAjet	2000 HVLP QCC	S40	26135
SATAjet	2000 RP QCC	S40	26135
SATAjet	1000 B HVLP QCC	S40	26135



# 3M™ PPS™ Series 2.0 Adapters by Spray Gun Manufacturer

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
SATAjet	1000 B RP QCC	S40	26135
SATAjet	3000 HVLP QCC	S40	26135
SATAjet	3000 B HVLP QCC	S40	26135
SATAjet	3000 RP QCC	S40	26135
SATAjet	3000 B RP QCC	S40	26135
SATAjet	4000 B HVLP QCC	S40	26135
SATAjet	4000 RP QCC	S40	26135
SATAjet	5000 B HVLP QCC	S40	26135
SATAjet	5000 RP QCC	S40	26135
SATAjet	5000 B Phaser	S40	26135
SATAjet	5000 B Phaser RP	S40	26135
SATAjet	90-2 HVLP	S9	26016
SATAjet	90-2 RP	S9	26016
SATAjet	B	S2	26003
SATAjet	B NR-92	S2	26003
SATAjet	B NR-95	S2	26003
SATAjet	H	S18	26054
SATAjet	NR2000 HVLP	S9	26016
SATAjet	NR 2000 RP	S9	26016
SATAjet	90	S9	26016
SATAminijet	3000 B HVLP QCC	S41	26137
SEM	71001 Pro-TEX Truck Bed Liner Gun	S15	26046
Sharpe (Graco)	555 Mini Siphon	S23	26109
Sharpe (Graco)	775 Siphon	S18	26054
Sharpe (Graco)	Cobalt HVLP (Euro)	S15	26046
Sharpe (Graco)	Cobalt HVLP (USA)	S11	26018
Sharpe (Graco)	Finex FX1000 Mini	S27	26119
Sharpe (Graco)	Finex FX2000 Conventional	S27	26119
Sharpe (Graco)	Finex FX3000 HVLP	S27	26119
Sharpe (Graco)	FX-100 Mini	S21	26105
Sharpe (Graco)	FX-200 Conventional	S2	26003
Sharpe (Graco)	FX-300 HVLP	S2	26003
Sharpe (Graco)	MFG Mini	S20	26104
Sharpe (Graco)	MPF Mini	S20	26104
Sharpe (Graco)	Platinum HVLP	S11	26018
Sharpe (Graco)	Razor (Chrome finish gun body)	S37	26132
Sharpe (Graco)	Razor Primer (blue finish gun body)	S11	26018
Sharpe (Graco)	Razor Compliant Waterborne	S37	26132
Sharpe (Graco)	Razor HVLP for Metallics	S37	26132
Sharpe (Graco)	Razor HVLP Waterborne	S37	26132
Sharpe (Graco)	Razor LVLP	S37	26132
Sharpe (Graco)	Razor Siphon	S18	26054
Sharpe (Graco)	SGF-98	S11	26018
Sharpe (Graco)	Titanium T-1 CG COMPLIANT	S11	26018
Sharpe (Graco)	Titanium T-1 HVLP	S11	26018
Smart (Finishmaster)	Spray Gun Kit (Mini)	S21	26105
Smart (Finishmaster)	Spray Gun Kit (Std)	S2	26003
Snap-On	BF900EXC14	S11	26018
Snap-On	BF700HPG15	S11	26018
Snap-On	BF900EXC3	S11	26018
Snap-On	EXC6	S11	26018
Snap-On	EXCG3	S11	26018

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Snap-On	Blue Point BF325 Mini	S21	26105
Snap-On	Blue Point BF350	S11	26018
Snap-On	Blue Point BF813	S11	26018
Snap-On	Blue Point BF815	S11	26018
Snap-On	Blue Point BLP10	S27	26119
Snap-On	Blue Point BLP13	S27	26119
Snap-On	Blue Point BLP14	S27	26119
Snap-On	Blue Point BLP15	S27	26119
Snap-On	Blue Point BLP16	S27	26119
Snap-On	Blue Point BLP18	S27	26119
Snap-On	Blue Point BLPK 14	S44	26141
Snap-On	Saber II BF814A	S11	26018
Snap-On	BF400 Mini	S23	26109
Snap-On	BF515 Mini	S20	26104
Snap-On	BF515 R-Angle Mini	S24	26110
Snap-On	BF590 Siphon	S18	26054
Snap-On	BF595 Siphon	S18	26054
Spanesi	Slim	S8	26105
Spectrum	Professional SP-HTE	S2	26103
Spectrum	Professional SP-HVLP	S2	26103
Spectrum	Black Widow HVLP	S9	26016
Spectrum	Black Widow HTE Compliant	S9	26016
Spitznagel	W2000A	S2	26003
Spray-It	522	S2	26003
Star	SV-106T/J Mini	S21	26105
Star	III	S2	26003
Sunex	9002A	S2	26003
Sunex	9004A	S2	26003
Titan	Vaper 1.0mm Mini	S21	26105
Titan	Vaper 1.4mm Base/Clear	S2	26003
Titan	Vaper 1.7mm Primer	S2	26003
TranStar	6613	S2	26003
TranStar	6614	S2	26003
TranStar	6617	S2	26003
TranStar	6618 Mini	S21	26105
TranStar	7713	S27	26119
TranStar	7714	S27	26119
TranStar	7718	S27	26119
TranStar	Series 2	S7	26008
Trem Pro	Gravity Series	S2	26003
U-Pol	Maximum	S2	26003
U-Pol	Maximum Mini	S21	26105
Wagner	NBC	S18	26054
Walcom	Genesi	S9	26016
Walcom	GEO F/X	S8	26015
Walcom	Geo THE	S9	26016
Walcom	EGO HVLP Detail Gun	S8	26015
Walcom	Slim Combat	S9	26016
Walcom	STM Mini	S2	26106
Walther Pilot	Pilot IV	S6	26007
Walther Pilot	Pilot Mini HD	S6	26007
Walther Pilot	Pilot Mini MD	S6	26007



# 3M™ PPS™ Series 2.0 Adapters by Spray Gun Manufacturer

Spray Gun Manufacturer	Model	PPS™ 2.0 Adapter	PN
Walther Pilot	Pilot Maxi	S6	26007
Warwick	827-C	S9	26016
Warwick	878	S9	26016
Warwick	828-C	S2	26105
Warwick	Mini	S2	26105
Warwick	861-C	S2	26003
Warwick	863	S2	26003
Warwick	H881W	S2	26003
Warwick	881H	S2	26003
Warwick	904H	S2	26003
Warwick	980 HVLP	S3	26132
Warwick	980 WB HVLP	S3	26132

For more information contact your  
3M representative or authorized distributor,  
or visit [go.3M.com/collision\\_pps\\_au](https://go.3M.com/collision_pps_au)

**3M Automotive Aftermarket Division**  
Building A, 1 Rivett Rd,  
North Ryde, NSW, 2113  
Phone: 136-136  
Web: [go.3M.com/3mCollision\\_AU\\_PPS](https://go.3M.com/3mCollision_AU_PPS)

By registering your email address, you will be the first to receive information on new automotive repair products, webinars, and more. Sign up here



[go.3M.com/4YC4](https://go.3M.com/4YC4)

**Warranty and Limited Remedy:** 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted.

3M Accuspray and PPS are trademark of 3M Company. All other trademarks are properties of their respective owners. ©3M 2024 All rights reserved.