

| Application | Product | Film | Adhesive | Key Overlaminate | Expected Performance Life ¹ | Product Advantages |
|----------------------------------|----------------------|--------------|---|--|--|--|
| Windows | IJ67 | Perforated | Removable | 8518, 8914, 8418G | 1 year | 60/40 perforation pattern |
| | 40C 40C-114R | Opaque/Clear | Removable with non-visible air release channels | 8508, 8509, 8510M | 7 years | Excellent printability with slide, and snap-up; available in opaque or dry-apply clear |
| | 48C-20R | Opaque | Removable with non-visible air release channels | 8048G, 8050M | 5 years | Non-PVC with all the versatility of Film 40C |
| | IJ8150 | Transparent | Ultra Removable | 8914, 8518, 8418G | 7 years | Optical clarity with excellent printability in a durable and conformable film; print unique effects with white ink, even see-through images |
| | 8170-P50 8170-P40 | Perforated | Removable | 8914, 8518, 8418G | 3 years | As a cast vinyl, offers excellent lifting resistance and durability; offered with 50/50 or 60/40 perforation pattern |
| Walls ² | IJ39 ● | Opaque | Not Removable, high tack | 8508, 8509, 8510M | 5 years | For hard-to-stick surfaces, including low-surface energy plastics; smooth walls |
| | 40C 40C-114R | Opaque/Clear | Removable with non-visible air release channels | 8508, 8509, 8510M | 7 years | Excellent printability with slide, and snap-up; available in opaque or dry-apply clear; smooth walls |
| | 48C-20R | Opaque | Removable with non-visible air release channels | 8048G, 8050M | 5 years | Non-PVC with all the versatility of Film 40C; smooth walls |
| | LX480mC SV480mC | Opaque | Removable with non-visible air release channels | 8548G, 8549L, 8550M, 8518, 8519, 8520, 8915, 8600 | 11 years | All that IJ180mC offers and more; non-PVC; excellent for installation in extreme temps; film conforms to textured walls |
| | IJ180mC | Opaque | Removable with non-visible air release channels | 8518, 8519, 8520, 8915, 8600 | 10 years | For smooth walls; conformable; slideability, air release and snap-up |
| | 780mC-10R ▲ | Reflective | Removable with non-visible air release channels | 8518, 8418G, 8519, 8548G, 8549L | 9 years | Robust, reflective film conforms to textured walls |
| Floors ³ and Sidewalk | 40C 40C-114R | Opaque/Clear | Removable with non-visible air release channels | 8509, 8510M, 8520, 3645, 8050M, 8550M | 3 months (carpet) 12 months (floor) | Indoor, short-term promotional or wayfinding programs |
| | 48C-20R | Opaque | Removable with non-visible air release channels | 8509, 8050M, 3645 | 3 months (carpet) 12 months (floor) | Non-PVC for indoor, short-term promotional or wayfinding programs |
| | 3662 ● | Opaque | Not Removable | 3647 | 3 months (sidewalk) | Exterior; unsealed; high traffic surfaces |
| Vehicle Graphics | 40C 40C-114R | Opaque/Clear | Removable with non-visible air release channels | 8518, 8519, 8520 | 5 years | For flat or simple curves; slide, tack and snap-up for quick application |
| | IJ280 | Opaque | Removable with non-visible Cv4 air release channels | 8428G, 8418G, 8548G, 8518 | 10 years | Highly conformable; high resistance to lifting; backed globally by 3M™ MCS™ Warranty |
| | LX480mC SV480mC | Opaque | Removable with non-visible air release channels | 8548G, 8549L, 8550M, 8518, 8519, 8520, 8528 | 11 years | All that Film IJ180mC offers and more; non-PVC; conformable; excellent for installation in extreme temps; horizontal warranty with correct overlaminates |
| | IJ180mC IJ180Cv3 | Opaque | Removable with non-visible air release channels | 8518, 8519, 8520, 8528, 8418G, 8548G, 8549L, 8550M | 10 years | Industry standard for wraps; medium/higher tack; conformable; slideability, air release and snap-up; horizontal warranty with correct overlaminates |
| | IJ175Cv3 | Opaque | Removable with non-visible air release channels | 8518, 8519, 8520, 8528, 8418G, 8548G, 8549L, 8550M | 10 years | Industry standard for wraps; low initial tack for easy snap up; conformable; slideability, air release; horizontal warranty with correct overlaminates |
| | 780mC-10R ▲ | Reflective | Removable with non-visible air release channels | 8518, 8519, 8528, 8418G, 8548G, 8549L | 9 years | Robust, reflective film conforms to compound curves, corrugations, and rivets; heals itself with heat recovery |

[3M.com/graphics](https://www.3m.com/graphics)

3M Commercial Branding & Transportation Division
3M Center, Bldg 223-3N-30
St. Paul, MN 55144-1000 USA

Refer to 3M Product Bulletins to learn more about these films, warranties and printer compatibility.

- 1 Maximum expected outdoor performance life of unprocessed base film.
 - 2 Due to wide variability of smooth indoor walls, the user is responsible for determining product's suitability for adhesion or removal.
 - 3 When used with appropriate overlaminates that provide slip resistance.
- Not removable adhesive.
 - ▲ This film is not recommended for cut, weeded, or pre spaced letters/decals.