


3M Science.
Applied to Life.™



Presenting

3M™ Clean Sanding System

Designed with technicians and shop owners in mind.






Smarter. Faster. Cleaner.

A clean shop can mean less rework, better cycle times, and the peace of mind that you are doing what you can to improve the shop environment. For you, your technicians and your customers.



New 3M™ Clean Sanding System

The 3M™ Clean Sanding System is a complete sanding solution for efficiently moving through your essential surface preparation and finishing work. The system includes our dust extractor, pneumatic and/or electric random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.

-  Designed to reduce dust in the air from sanding for a cleaner workspace.
-  Helps shops boost productivity and efficiency by helping to reduce rework and cleanup time.
-  Compact and mobile. Designed for easy, flexible use around the shop.
-  Compatible with pneumatic and/or electric sanders.
-  Tech-friendly design including auto on/off, antistatic hose, rubber wheels, brake locks, and LED indicator lights.





Dust Extractors

33756	3M™ Dust Extractor, 33756, 30 Liter, 230V, Plug Type G, L Class, 1/Case
33787	3M™ Dust Extractor, 33787, 30 Liter, 230V, Plug Type G, M Class, 1/Case
33761	3M™ Dust Extractor, 33761, 45 Liter, 230V, Plug Type G, L Class, 1/Case
33762	3M™ Dust Extractor, 33762, 45 Liter, 230V, Plug Type G, M Class, 1/Case

Random Orbital Sanders

38505	3M™ Precision Random Orbital Sander, 38505, 75 mm, 5 mm (3/16) Orbit, Vacuum-Ready, 1 per box
33632	3M™ Precision Random Orbital Sander, 33632, 150 mm, 2.5 mm (3/32) Orbit, Vacuum-Ready, 1 per box
33633	3M™ Precision Random Orbital Sander, 33633, 150 mm, 5 mm (3/16) Orbit, Vacuum-Ready, 1 per box
33634	3M™ Precision Random Orbital Sander, 33634, 150 mm, 8 mm (5/16) Orbit, Vacuum-Ready, 1 per box
33794	3M™ Electric Random Orbital Sander, 33794, 150 mm, 5 mm (3/16) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box



Dust Extractor Accessories

33645	3M™ Antistatic Pneumatic Hose, 33645, 5 m, 1 per box
33783	3M™ Antistatic Pneumatic Hose, 33783, 8 m, 1 per box
33790	3M™ Antistatic Pneumatic Hose, 33790, 10m, 1 per box
33646	3M™ Antistatic Electric Hose, 33646, 5 m, 1 per box
33648	3M™ Dust Extractor Filter Bag, 33648, 5/Pack
33647	3M™ Dust Extractor Filter, 33647, 2/Pack
33652	3M™ Dust Extractor Y-Connector, 33652
33765	3M™ Dust Extractor Handle Extension, 33765, 1 per box
33784	3M™ Abrasives Organizer, 33784
33770	3M™ Random Orbital Sander Adaptor for Hose Assembly 57 mm, 33770, 1 per carton, 4 per case
33771	3M™ Dust Extractor Straight Adaptor 38 mm, 33771, 1 per carton, 4 per case
33772	3M™ Dust Extractor Adaptor 29 mm, 33772, 1 per carton, 4 per case
33653	3M™ Clean Sanding System Workstation, 33653, 1 per box
33654	3M™ Clean Sanding System Workstation Extension, 33654, 1 per box

Accessories

30160	3M™ Hookit™ Low Profile Disc Back-up Pad 30160, 53 Holes, Red Foam, 10/Case
30062	3M™ Hookit™ Clean Sanding Multi-Connection Disc Pad 30062, 150 mm, 53 Holes, 5 ea/Case
05777	3M™ Hookit™ Soft Interface Pad, 05777, 150 mm x 10 mm, 10 pads per case
20446	3M™ Hookit™ Clean Sanding Disc Pad Hook Saver 20446, 150 mm, 20 ea/Case
35826	3M™ Hookit™ Dust Extraction Flexible Sanding Block 35826, 178 mm x 67 mm, 24/Case
35828	3M™ Hookit™ Dust Extraction Flexible Sanding Block 35828, 406 mm x 67 mm, 8/Case
35825	3M™ Hookit™ Dust Extraction Flexible Sanding Block 35825, 133 mm x 67 mm, 24/Case



3M United Kingdom PLC
Automotive Aftermarket
3M Centre
Cain Road
Bracknell, RG12 8HT
+44 (0)161 237 6391
aadenquiries@mmm.com

3M Ireland Limited
Automotive Aftermarket
The Iveagh Building
The Park
Carrickmines, Dublin 18
+353 12160301
aadenquiries@mmm.com



For more information on warranty please go to:
<https://multimedia.3m.com/mws/media/24199220/warranty-statement-for-extended-warranty-2-in-clean-sanding-system-in-english.pdf>

For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3m.co.uk/aad-info

3M, Cubitron and Hookit are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle.
© 3M 2024. All rights reserved.

For more information, visit us at www.3Mbodyshop.co.uk