


OEM Match Made Easy

Help save time and effort with the 3M OEM Match Family of seam sealer solutions



The 3M OEM Match family of seam sealing products is designed to help technicians more easily to replicate the look and function of a vehicle's original factory seam seal.

The system includes our line of seam sealer matching tips and the 1K 3M™ OEM Match Seam Sealer in different colors – allowing you to replicate the most common OEM seams with one simple application.

3M™ OEM Match Wing Tip

Helps technicians quickly replicate OEM seams on door skins and hem flanges.

Tip and wing can be trimmed to adjust the size and position of the seam sealer.




 Part No.	Product Name	Fitting	Packed As
33992	3M™ OEM Match Wing Nozzle 1K Tip	1K Seam Sealer Cartridges (MS or Polyurethane)	10 Nozzles / Pack 5 Packs / Case

3M™ OEM Match Ripple Tip

Helps technicians quickly replicate OEM seam sealer textures including robot applied rippled beads.

Width, texture, and height can be controlled by angling nozzle and adjusting air pressure during application.



 Part No.	Product Name	Fitting	Packed As
33994	3M™ OEM Match Ripple 1K Tip	1K Seam Sealer Cartridges (MS or Polyurethane)	10 Nozzles / Pack 5 Packs / Case

3M™ OEM Match Wide Stream Tip

Helps technicians quickly match OEM seams for smooth or wide applications.

Tip can be trimmed to the required size to match the look of factory-applied materials.



Part No.	Product Name	Fitting	Packed As
33993	3M™ OEM Match Wide Stream 1K Tip	1K Seam Sealer Cartridges (MS or Polyurethane)	10 Nozzles / Pack 5 Packs / Case

3M™ OEM Match Spray Tip

Spray multiple patterns to help match OEM seams with simple applicator adjustments.

The 3M™ OEM Match Air Supply Kit, paired with the OEM Match Sprayable Tip, allows technicians to convert pneumatic applicators to spray 1K seam sealer products.



Part No.	Product Name	Fitting	Packed As
33991	3M™ OEM Match Sprayable 1K Tip	1K MS Seam Sealer Cartridges	10 Nozzles / Pack 5 Packs / Case



33999	3M™ OEM Match Air Supply Kit	Can be fitted to all 3M™ Pneumatic Applicators to allow spray application of seam sealers	10 Kits / Case
-------	------------------------------	---	----------------

3M OEM Match Family Overview

3M offers professional grade seam sealers, nozzles, tips and applicators to allow technicians to easily replicate OEM seams. The OEM Match family joins the full line of 3M™ Seam Sealers to give shops a full toolset to meet the demands of OEM procedures.

	Part No.	Product Name	Packed as	Use with/for
Applicators	08012	3M™ Pneumatic Guns for Cartridges	1 per case	3M™ Pneumatic Guns for Cartridges, Applicator for 310 ml Cartridges
	08014	3M™ Manual Gun for Cartridge and Sachet	1 per case	3M™ Manual Gun for Cartridge and Sachet, High Power Version

1K Polyurethane Sealer	08365	3M™ Polyurethane Seam Sealer, Beige, 310 ml, Cartridge	12 per case	<ul style="list-style-type: none"> • 1-part high solids polyurethane material ideal for sealing seams and joints
	08694	3M™ Polyurethane Seam Sealer, Black, 310 ml, Cartridge	12 per case	<ul style="list-style-type: none"> • adheres well to bare metal, primed metal and painted surfaces
	08684	3M™ Polyurethane Seam Sealer, Grey, 310 ml, Cartridge	12 per case	<ul style="list-style-type: none"> • can be smoothed to a featheredge and/or brushed • tack free and paintable after 30-45 minutes
	08689	3M™ Polyurethane Seam Sealer, White, 310 ml, Cartridge	12 per case	<ul style="list-style-type: none"> • permanently flexible

1K MS Sealers	08855	3M™ MS Caulkable Sealer, White, 290 ml, Cartridge	12 per case	<ul style="list-style-type: none"> • isocyanate free heavy-bodied, general purpose seam sealer for interior and exterior body joints
	50740	3M™ Multi-Purpose Seam Sealer, Beige, 310 ml, Cartridge	9 per case	<ul style="list-style-type: none"> • adheres well to properly prepared primer, paint, and bare metal surfaces (except acrylic lacquer)
	08851	3M™ MS Sprayable Seam Sealer, Grey, 290 ml, Cartridge	12 per case	<ul style="list-style-type: none"> • can be caulked or sprayed, allows for painting almost immediately after being applied (wet-on-wet)

	Part No.	Product Name	Packed as	Fitting
OEM Match Nozzles	33992	3M™ OEM Match Wing Nozzle 1K Tip	10 Nozzles / Pack 5 Packs / Case	1K Multi-Purpose Seam Sealer, MS Caulkable Sealer or Polyurethane Seam Sealer in Cartridge
	33993	3M™ OEM Match Wide Stream 1K Tip	10 Nozzles / Pack 5 Packs / Case	
	33994	3M™ OEM Match Ripple 1K Tip	10 Nozzles / Pack 5 Packs / Case	
	33991	3M™ OEM Match Sprayable 1K Tip	10 Nozzles / Pack 5 Packs / Case	1K Multi-Purpose Seam Sealer and MS Sprayable Seam Sealer in Cartridge
	33999	3M™ OEM Match Air Supply Kit	10 Kits / Case	Fits to 3M™ Pneumatic Guns for Cartridges to allow spray application of seam sealers



3M United Kingdom PLC
Automotive Aftermarket
3M Centre
Cain Road
Bracknell, RG12 8HT
+44 (0)161 237 6391
aadukenquiries@mmm.com

3M Ireland Limited
Automotive Aftermarket
The Iveagh Building
The Park
Carrickmines, Dublin 18
+353 12160301
aadukenquiries@mmm.com



For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3M.co.uk/aad-info

3M and RepairStack are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle.
© 3M 2024. All rights reserved.

Find out more about 3M OEM Match Family: