



3M Science.
Applied to Life.™

3M Protective Solutions for
Fire and Emergency Services

Fight safer.

Anywhere, anytime.

From structural firefighting to vehicle extrication, complex special operations, and medical response, 3M offers a holistic portfolio of high-quality personal protective solutions to help firefighters perform their best.

Created to go the distance, our line of products helps ensure you have the technology and protection you need to take on today's challenging missions.

Protective Communications. 3M offers a broad selection of protective communication equipment to help professionals stay protected, connected, and provide effective communication in dynamic noise environments.

Click below to explore
[all protective communications solutions](#)



► **Recommended for:** Incident Command, Crew Communications, Vehicle Extrication, Special Operations



3M™ PELTOR™ WS™ LiteCom Plus Headset

Hearing protector with built-in analog two-way communication radio, a level-dependent function for ambient listening, Bluetooth® Multipoint connectivity and external connection jack.

- Built-in analog two-way communication radio
- Bluetooth® Connectivity
- External Connection Jack
- Stainless Steel Wire Headband
- Hearing Protection
- Level-dependent Technology
- Voice Operated Transmission

► **Recommended for:** Incident Command, Vehicle Extrication, Pump Operations, Confined Space



3M™ PELTOR™ CH-3 FLX2 Headset with PTT

CH-3 FLX2 Headset with PTT (Push-to-Talk) is the solution when you want a smooth and easy to use set-up with fewer cables and easy access to the PTT on your left side of the headset

- Detachable down lead FLX2 connector for major 2 way radios (-111)
- Improved speaker efficiency to fit today's digital device
- Newly designed headband featuring a waterproof microphone (IP68)
- Testable with the 3M™ E-A-Rfit™ Dual-Ear Validation System



Respiratory Solutions. 3M respiratory products are designed to help minimize exposure to hazardous materials, chemical leaks, airborne particles, toxic substances, and more. We offer safety solutions that help keep firefighters and first responders protected, focused, and confident.

Click below to explore
[Powered Air Purifying Respirator solutions](#)
[Reusable Respirator solutions](#)
[Disposable Respirator solutions](#)

► **Recommended for:** Overhaul, Arson Investigation, EMS



3M™ Versaflo™ TR-600 Powered Air Purifying Respirator

The 3M™ Versaflo™ Powered Air Turbo TR-600 is a beltmounted air purifying device. When combined with one of the 3M approved headtops, it forms a power-assisted system for respiratory protection against particles, nuisance odours (where applicable) and gases and vapours.

- **User-Friendly Design:** Audible and visual alarms alert you to filter load and low battery.
- **Customizable:** Features multiple airflow rates and adjustable belts for extra convenience.
- **Convenient:** Works with particulate filters or gas and vapor combination cartridges for protection in many hazardous environments.



3M™ Rugged Comfort Quick Latch Half Facepiece Reusable Respirator 6500QL Series

Rugged comfort, durability, and low profile design.

The 6500QL Series Respirator is compatible with a wide variety of AS/NZS 1716 compliant 3M respirator cartridges and filters to help protect firefighters and first responders from a variety of particulates, gases and vapors, while ensuring optimal fit with the use of adjustable head cradle and straps.

- **Drop-Down Mechanism:** The quick latch design allows the user to raise and lower the respirator while moving in and out of contaminated areas.
- **Easy Breathing:** 3M™ Cool Flow™ Exhalation Valve allows for easy breathing.



3M™ Aura™ Disposable Respirator 9332+, FFP3, Valved

The 3M™ Aura™ Disposable Respirator 9332+ provides comfort and style without compromising performance. Protects against dusts and mists found in a wide variety of industrial applications and other work situations requiring FFP3 protection.

Flat fold disposable P3 respirator offering reliable, effective protection against higher levels of fine dust, mists and metal fume

- **Low breathing resistance:** filter technology for easier breathing through your shift
- **Ingenious 3-panel design:** that accommodates greater facial movement during speech so much more comfortable to wear
- **A sculpted nose panel:** for improved compatibility with eyewear

Eye Protection. Eye protection is essential to safeguard your sight from flying debris, lass, dust, biohazards, and other potentially contaminated materials at the scene. 3M's protective eyewear combines rugged design, reliable protection, and convenient features to enhance your comfort.

Click below to explore
[all eye protection solutions](#)

► **Recommended for:** Overhaul, Arson Investigation, Vehicle Extrication, EMS, USAR



3M™ GoggleGear™ Protective Goggle 500 Series

Fog-resistant safety goggles designed to seal to the face.

A fogged lens can be frustrating and dangerous. Removing eyewear to wipe away fog can expose eyes to impact hazards and debris. The Scotchgard™ Anti-Fog Coating resists fogging longer than traditional anti-fog coatings to help responders operate effectively in hot and humid conditions or climate-controlled areas.

- **Comfortable Design:** Features a low-profile design with an adjustable strap and indirect ventilation.
- **3M™ Scotchgard™ Protector Anti-Fog Coating:** Helps minimize lens fogging, even after washing multiple times with water, and provides scratch resistance in tough environments.
- **Standard Compliance:** Eyewear meets the requirements of AS/NZS 1337.1:2010 medium impact.

► **Recommended for:** Overhaul, Arson Investigation, Vehicle Extrication, EMS



3M™ SecureFit™ Protective Eyewear 500 Series

Safety glasses with a streamlined lens shape and sleek profile.

3M™ SecureFit™ 500 Series provides a comfortable fit with a slim standout style. Available in different lens colors and lens coatings, these lightweight safety glasses feature a rimless polycarbonate lens available with anti-fog and anti-scratch protection for extra convenience.

- **3M™ Pressure Diffusion Temple Technology:** Provides comfortable pressure equalization. The temples flex and self-adjust to the size of your head.
- **3M™ Scotchgard™ Protector Anti-Fog Coating:** Helps minimize lens fogging and provides scratch resistance in tough environments (select models).
- **Standard Compliance:** Eyewear certified to the requirements of AS/NZS 1337.1:2010 medium impact.

Respiratory Protection. 3M Scott offers a range of facepieces and accessories for the professional fire service including the innovative Scott Sight thermal vision system and EPIC 3 range of electronic communication devices

Click below to explore
[Propak SCBA Range](#)



► **Recommended for:** Structural firefighters across a wide range of body types and sizes, ideal for confined spaces




3M™ Scott™ SCBA Facepiece Options

3M™ Scott™ offer 3 families of positive-pressure SCBA facepieces all certified to EN 137 and AS/NZS 1716 as a firefighting rated masks. The AV3000HT facepiece comes in 3 sizes and features a conical visor while Vision 3 also comes in 3 sizes and both feature excellent all-round vision. Promask PP comes in 2 sizes and features a robust butyl-rubber chassis and is CBRN rated.

- A choice of 3 mask styles and 8 sizes to offer improved face-fit
- Vision 3 and Promask available across the ProPak SCBA range
- AV3000HT available with ProPak-f and fx EZ-Flo models

► **Recommended for:** Structural firefighting, search & rescue teams



3M™ Scott™ Sight Thermal Vision System

The 3M™ Scott™ Sight Thermal Vision System gives firefighters back the use of their hands while providing thermal vision in complete darkness or smoke-filled environments with a mask mounted camera and miniature in-mask display screen.

- Compatible with AV3000HT facepieces
- Available in standard or Pro-Package edition
- Standard and Pro-Package include;
 - Angle-adjustable line-of-sight display
 - Auto timer power-off
 - Standby mode to save batteries
 - Colourised temperature display
 - Battery level display
- Pro-Package adds;
 - Hot & cold-spot tracking
 - Video recording



Respiratory Protection. 3M Scott offers ProPak SCBA provides a range of EN 137 Type 2 and AS/NZS 1716 certified SCBA designed for the professional fire service with a range of accessories and options to support standard operating procedures

Click below to explore
[Air-Supplied Respirators | SCBA](#)



► **Recommended for:** Structural firefighters across a wide range of body types and sizes, ideal for confined spaces



3M™ Scott™ ProPak-fx Type 2 SCBA

The 3M™ Scott™ ProPak-fx SCBA is certified to EN 137 and AS/NZS 1716 as a firefighting rated SCBA with non-absorbent waistbelt and shoulder padding, light-reflective stitching, and tool-free removable pneumatics. ProPak-fx incorporates a swivel and 3-position height adjustable waistbelt for improved personnel fit and maneuverability

- Pyrogard & Kevlar® blend webbing with reflective stitching
- Pivoting, 3-position height-adjustable waistband
- Low-profile, compact, first-breath activated demand valve
- Corrosion resistant stainless-steel webbing adjusters
- Large waistbelt buckles for operation with gloved hands
- Over-shoulder mounted luminescent pressure gauge & whistle

► **Recommended for:** Incident Command, Vehicle Extrication, Pump Operations, Confined Space



3M™ Scott™ ProPak-EZ Flo Type 2 SCBA

The 3M™ Scott™ ProPak-EZ Flo range includes the ProPak-f and fully height adjustable ProPak-fx SCBA equipped with the EZ-Flo regulator supporting the EN 136 Class 3 and AS/NZS 1716 certified AV3000HT facepiece

- Large diameter EZ-Flo regulator for easy handling with gloves
- Available in standard or CBRN certified configurations
- Supports AV3000HT facepiece and Scott Sight in-mask thermal vision system and EPIC 3 Bluetooth communications
- AV3000HT features large conical high-temperature & scratch resistant visor with dual-reflex face seal for improved face fit
- Supports optional air-line, rescue and fast-fill pneumatics



3M India Private Limited
56D, Wipro Ave, Electronics City Phase 1
Electronic City, Bengaluru,
Karnataka 560100
1800 425 3030
3mpersonalsafety.in@mmm.com

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.