



## Technical Data Sheet

### 3M™ Scotch® Performance Paper Box Sealing Tape 570



[Product Details](#)

#### Product Description

Scotch® Performance Paper Box Sealing Tape 570 is an ideal alternative to conventional box sealing tapes when sustainability is a priority. This product is optimal for palletized and lightweight, single-parcel shipments. This construction has a strong paper backing and solvent-free hot melt adhesive designed to provide a secure seal on cartons containing high levels of recycled content.

#### Product Features

- Recycle-compatible when left on the box according to Western Michigan University (WMU) Recyclability testing.
- Comprised of a solvent-free hot melt adhesive and a strong backing made from FSC®-certified paper (C009378)\*.
- Reliably adheres to various surfaces, including cartons with high levels of recycled content.
- Equally applicable for manual use and machine/automated processes.

#### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Typical Physical Properties

Attribute Name	Test Method	Value
Color		Brown
Adhesive Type		Pressure sensitive hot melt rubber-resin
Backing		Kraft Paper
Backing Thickness	ASTM D3652	0.09 mm (3.6 mil)
Total Tape Thickness	ASTM D3652	0.119 mm (4.7 mil)

#### Typical Performance Characteristics

Attribute Name	Test Method	Dwell Time	Temperature	Test Condition	Substrate	Value
Elongation at Break	ASTM D3759					3 %
Tensile Strength	ASTM D3759			Machine Direction		754 N/100mm (43 lb/in)
Holding Power	ASTM D3654				Fiberboard	620+ min
180° Peel Adhesion	ASTM D3330	1 min	23 °C (73 °F)		Stainless Steel	104 N/100mm (95.0 oz/in) <sup>1</sup>

<sup>1</sup> 300 mm/min (12 in/min)

## **Handling/Application Information**

### **Application Techniques**

An extensive line of application equipment including hand-held manual dispensers and semi-automatic and fully automatic equipment is available. Application of Scotch® Performance Paper Box Sealing Tape 570 is most easily accomplished at room temperature. At colder temperatures, approaching 32°F (0°C), the adhesive becomes more firm. Once applied, Scotch® Performance Paper Box Sealing Tape 570 performs well throughout the normal temperature ranges typically encountered by packaged products in shipping and storage environments.

### **Storage and Shelf Life**

Store under normal conditions of 4° to 27°C (40° to 80°F) and 40 to 50% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 12 months from date of manufacture.

### **Available Sizes**

Attribute Name	Value
Core Size (ID)	76.2 mm (3 in)
Standard Roll Length	50, 500 m (55, 547 yd)
Standard Width	48, 72 mm (1.9, 2.8 in)

### **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

\*The paper backing for Scotch® Performance Paper Box Sealing Tape 570 is FSC-certified, but the overall product does not have FSC chain of custody certification.

### **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Specialties Division  
3M Center, St. Paul, MN 55144-1000  
[www.3M.com](http://www.3M.com)

Scotch is a registered trademark of 3M.  
©3M 2025 (6/25)