

3M™ High Shear Pressure Sensitive Cover Tape 2668

Product Description

3M™ High Shear Pressure Sensitive Cover Tape 2668 is a transparent, polyester film tape with a synthetic, room temperature, pressure sensitive adhesive (PSA) zone along each edge. 3M cover tape 2668 seals electrical and electronic components into 3M's family of polycarbonate carriers. It also works well with certain other embossed carrier tapes.

Product Construction/Material Description

Backing	Adhesive	Inner face
Transparent polyester film	Pressure-sensitive synthetic polymer	Transparent, static dissipative, polyester film

Available Widths

3M cover tape 2668 is available in the standard sizes listed below, with adhesive exposed only along the edges. All 3M cover tape 2668 is supplied in 500 meter, splice-free rolls.

Standard Sizes	Widths (mm)						
Carrier tape	8	12	16	24	32	44	56
Cover tape	5.4	9.3	13.3	21.3	25.5	37.4	49.4
Adhesive exposure on each edge*	0.7	0.7/0.8/1.1	1.0	1.0/1.3	1.0/1.3/1.4	1.0/1.4	1.0/1.4
Roll length (m)	500	500	500	500	500	500	500

* Other cover tape and adhesive exposure widths may be available. Please consult your 3M representative for information.

Standard Packaging Format

3M cover tape 2668 is provided on a plastic core, packaged with high density paper wafer inserts and a centering core in a single polyethylene bag and is placed between two end-caps with corrugated pads in a cardboard carton.



Initial Adhesion and Aging Data

3M cover tape 2668 has a simple process window. Desirable initial peel force values can be achieved with the application of adequate pressure to the non-adhesive surface of the cover tape over the adhesive stripes with a reciprocating shoe, or compliant roller mechanism. The following charts depict the typical room temperature and aging characteristics of 3M cover tape 2668 after sealing to 3M™ Polycarbonate Carrier 3000 and 3M™ Clear Polycarbonate Carrier 2703.

Typical Removal Force Results



Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M™ High Shear Pressure Sensitive Cover Tape 2668



Sealing Parameters

Cover tape: 3M™ High Shear Pressure Sensitive Cover Tape 2668, 5.4 mm
 Carrier tape: 3M™ Polycarbonate Carrier 3000, 8 mm
 Sealing mode: Reciprocating
 Pressure: 1.0 bar
 Speed/Dwell time: 100 ms
 Temperature: Room temperature ≈23°C (73°F)



Sealing Parameters

Cover tape: 3M™ High Shear Pressure Sensitive Cover Tape 2668, 5.4 mm
 Carrier tape: 3M™ Clear Polycarbonate Carrier 2703, 8 mm
 Sealing mode: Reciprocating
 Pressure: 1.0 bar
 Speed/Dwell time: 100 ms
 Temperature: Room temperature ≈23°C (73°F)

Graph Notes

The graphs in this document represent sealing performance attained under the conditions specifically stated in the sealing parameters section of the charts. Pressure is the indicated gauge pressure used to achieve the seals, and may vary among sealing equipment manufacturers. The use of a different sealing mechanism, i.e., reciprocating vs. roller, may have an effect upon the performance obtained under otherwise identical conditions due to differences in pressure or pressure distribution. The use of heat is specifically not recommended.

All data presented are representative of peeling studies conducted according to the requirements of the current ANSI/EIA481-E Standard. Sealed samples used in these studies were stored under the conditions noted, wound on 180 mm diameter reels to simulate typical production use. Samples being tested at elevated temperature and humidity were permitted a minimum equilibration period of four hours at room temperature prior to testing to simulate actual use conditions.

3M™ High Shear Pressure Sensitive Cover Tape 2668

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Final product specifications and testing methods will be outlined in the product's Certificate of Analysis (COA) that is provided once the product is approved by 3M for general commercialization and development work is completed.

Description	Type	Units	Typical Performance	Test Notes	Test Method
Material Properties	Backing type Adhesive type Sealing temp		Polyester PSA Ambient room	1	
Physical Properties	Tensile strength Elongation Haze Clarity Transmission Thickness Shear strength @50°C Shear strength @40°C Shear strength @23°C	N/mm Width % % % % mm (in) minutes minutes minutes	7.0 90 6.0 91.4 85.0 0.061 (0.0024) >100 >1,000 >4,000	2 2 3 3 3 2 4 4 4	Modified ASTM-D3759 Modified ASTM-D3759 ASTM-D1003 ASTM-D1003 ASTM-D1003 Modified ASTM-D3759 Modified ASTM-D3654 Modified ASTM-D3654 Modified ASTM-D3654
Electrical Properties	Resistance (back side) Resistance (component side)	Ohms Ohms	Non-conductive 1.0x10 ⁷	5	ANSI/ESD S541
Product Format	Core type Core inner diameter Roll diameter Roll length	Material mm (in) mm (in) m (yd)	Plastic 76.45 (3.0) 220 (8.6) 500 (546)		

Test Notes

1. The application of heat to seal PSA cover tapes is specifically not recommended. Pressure in the range of 10 to 50 psig is sufficient to seal PSA adhesives.
2. Tensile tests and thickness measurements are conducted at 21°C (70°F), 70% RH, in the machine direction of the polyester film.
3. Optical properties are measured using the BYK-Gardner Haze-Gard Plus Transmission Meter.
4. 0.5" x 0.5" adhesive secured to polycarbonate substrate with 1,000 g load.
5. Resistance is measured at room temperature using a resistance meter.

Typical adhesive properties

The synthetic adhesive used in the construction of 3M™ High Sheer Pressure Sensitive Cover Tape 2668 has been engineered to provide long term resistance to thermal degradation, even when exposed to environmental extremes such as the storage conditions depicted in the charts in this publication.

Storage and Shelf Life

3M cover tape 2668 should be stored indoors, in its original packaging, in a controlled climate environment ranging 22°C - 28°C (72°F - 82°F) and not exceeding 70% relative humidity. The product should be protected from direct sunlight and should be used on a "first-in, first-out" basis.

The shelf life of 3M cover tape 2668 is two years from the date of manufacture when stored according to the recommended storage conditions.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and deemed commercially available from 3M. The COA contains the 3M test methods, specifications limits and test results for the

3M™ High Shear Pressure Sensitive Cover Tape 2668

product's performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

This technical data sheet may contain preliminary data and may not match the COA specification limits and/or test methods that may be used for COA purposes.

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specifications on the Certificate of Analysis, which is established when the product is manufactured and deemed commercially available and is provided at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.** If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.



Electronics Materials Solutions Division
3M Center, Building 223-3S-32
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle.
©3M 2024. All rights reserved.
80-6111-0135-5