



Technical Data Sheet

3M™ Adhesive Transfer Tape 9626

Product Description

Finite Element Analysis (FEA) data is available for this product at: [3m.com/FEA](https://www.3m.com/FEA)

3M™ Adhesive Transfer Tapes with 3M™ Quick Bonding Adhesive 360 provides high bond strength to most surfaces, including many low surface energy plastics such as polypropylene and powder coated paints.

Product Features

- Excellent adhesion to difficult to bond to surfaces such as HDPE, LDPE, and PP.
- Super quick stick.
- Higher adhesion from a thinner tape.
- Excellent solvent resistance.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Adhesive Type		Acrylic
Total Tape Thickness	ASTM D3652	0.05 mm
Liner		60# Glassine
Liner Thickness		0.08 mm
Primary Liner Color		Natural

Typical Performance Characteristics

180° Peel Adhesion

Temperature: 23 °C

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Test Condition	Substrate	Value
30 s	Faceside	Polypropylene (PP)	12 N/cm ¹
30 s	Backside	Polypropylene (PP)	11 N/cm ¹
15 min	Faceside	Polypropylene (PP)	12 N/cm ¹
15 min	Backside	Polypropylene (PP)	12 N/cm ¹
72 h	Faceside	ABS	13 N/cm ¹
72 h	Backside	ABS	11 N/cm ¹
72 h	Faceside	Polycarbonate (PC)	14 N/cm ¹
72 h	Backside	Polycarbonate (PC)	13 N/cm ¹
72 h	Faceside	Polyethylene (PE)	8 N/cm ¹
72 h	Backside	Polyethylene (PE)	7 N/cm ¹
72 h	Faceside	Polypropylene (PP)	13 N/cm ¹
72 h	Backside	Polypropylene (PP)	12 N/cm ¹

Dwell Time	Test Condition	Substrate	Value
72 h	Faceside	Stainless Steel	14 N/cm ¹
72 h	Backside	Stainless Steel	13 N/cm ¹

¹ 304 mm/min (12 in/min)

Temperature: 23 °C

Test Condition: 1000 g

Attribute Name	Test Method	Value
Static Shear	ASTM D3654	>10,000 min ¹

¹ 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	177 °C ¹
Long Term Temperature Resistance	93 °C ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Characteristics

Environmental Resistance

Humidity Resistance: High humidity has minimal effect on adhesive performance.

No significant reduction in bond strength is observed after exposure for 72hrs at 150°F (65°C) and 90% relative humidity.

UV Resistance: When properly applied, nameplates and decorative trim parts are not adversely affected by exposure.

Water Resistance: Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

Temperature Cycling Resistance: High bond strength is maintained after cycling six times through:

8 hours at -4°F (-20°C)

8 hours at 150°F (65°C) /90% RH

Chemical Resistance: When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids, and alkalis.

Handling/Application Information

Application Examples

- Foam to powder coated painted surfaces.
- Low surface energy plastic adhesion.

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application will assist the adhesive in developing intimate contact with the bonding surface.

To obtain optimum adhesion, the bonding surfaces must be clean, dry, and well unified. Typical surface cleaning solvents are methyl ethyl ketone for metals or isopropyl alcohol for plastics.*

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

*When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturers precautions and directions for use. These cleaning recommendations may not be compliant with the rules of certain Air Quality Management Districts in California; consult applicable rules before use.

Application Equipment

To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality. To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, 3M™ Lamination Techniques for Converters of Laminating Adhesives (70-0704-1430-8).

For additional dispenser information, contact your local 3M office.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Precautionary Information: Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information, please contact your local 3M Office. You can click or scan QR code to see contact detail or visit www.3M.com Important Information: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law. Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Centre
Cain Rd, Binfield, Bracknell RG12 8HT, United Kingdom
3m.co.uk/iatd

3M is a trademark of 3M Company.
©3M 2024 (9/24)