



## Technical Data Sheet

### 3M™ High Strength Double Coated Tape 93015LE

#### Product Description

Finite Element Analysis (FEA) data is available for this product at: [3m.com/FEA](https://3m.com/FEA)

3M™ Double Coated Tapes with 3M™ High Strength Acrylic Adhesive 300LSE provides a high bond strength to most surfaces, including many low surface energy plastics such as polypropylene and powder coated paints. The acrylic adhesive also provides excellent adhesion to surfaces contaminated with oil typically used with machine parts.

#### Product Features

- This tape has a film carrier which can add dimensional stability to foams and other substrates and also makes it easier to handle the tape during slitting and die-cutting.
- The bond strength of 3M™ Acrylic Adhesive 300LSE increases as a function of time and temperature, and has very high initial adhesion.

#### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

#### Typical Physical Properties

Attribute Name	Test Method	Test Condition	Value
Adhesive Type			300LSE Acrylic
Adhesive Carrier			Clear Polyester
Adhesive Thickness		Faceside	0.069 mm <sup>1</sup>
Carrier Thickness			0.012 mm
Adhesive Thickness		Backside	0.069 mm <sup>2</sup>
Total Tape Thickness	ASTM D3652		0.15 mm
Liner			58# Polycoated Kraft Paper (PCK)
Liner Print			300LSE
Liner Thickness			0.11 mm
Primary Liner Color			Tan

<sup>1</sup> Faceside adhesive is on the interior of the roll, exposed when unwound and liner removed.

<sup>2</sup> Backside adhesive is on the exterior of the roll, exposed when liner is removed.

#### Typical Performance Characteristics

##### 180° Peel Adhesion

Temperature: 23 °C

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Dwell Time	Substrate	Value
15 min	ABS	9.3 N/cm <sup>1</sup>
15 min	Polycarbonate (PC)	14.2 N/cm <sup>1</sup>
15 min	Polypropylene (PP)	11.5 N/cm <sup>1</sup>
15 min	Stainless Steel	10.9 N/cm <sup>1</sup>
72 h	ABS	13.7 N/cm <sup>1</sup>

Dwell Time	Substrate	Value
72 h	Polycarbonate (PC)	18.1 N/cm <sup>1</sup>
72 h	Polypropylene (PP)	14.8 N/cm <sup>1</sup>
72 h	Stainless Steel	13.7 N/cm <sup>1</sup>

<sup>1</sup> 304 mm/min (12 in/min)

Temperature: 23 °C  
Test Condition: 1000 g

Attribute Name	Test Method	Value
Static Shear	ASTM D3654	>10,000 min <sup>1</sup>

<sup>1</sup> 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	149 °C <sup>1</sup>
Long Term Temperature Resistance	93 °C <sup>2</sup>

<sup>1</sup> Short Term (minutes, hour)

<sup>2</sup> Long Term (day, weeks)

## Typical Environmental Characteristics

### Environmental Resistance

**Humidity Resistance:** High humidity has minimal effect on adhesive performance. No significant reduction in bond strength is observed after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

**UV Resistance:** When properly applied, nameplates and decorative trim parts are not adversely affected by exposure.

**Water Resistance:** Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength is maintained.

**Temperature Cycling Resistance:** High bond strength is maintained after cycling four times through:  
4 hours at 158°F (70°C)  
4 hours at -20°F (-29°C)  
4 hours at 73°F (22°C)

**Chemical Resistance:** When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids, and alkalis.

## Electrical and Thermal Properties

Attribute Name	Value
Breakdown Voltage	6,900 V

## **Handling/Application Information**

### **Application Examples**

- Foam to powder coated painted surfaces.
- Low surface energy plastic adhesion.

### **Application Techniques**

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength. To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.\*

\*Note: Carefully read and follow the manufacturer's precautions and directions for use when using solvents. Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

## **Industry Specifications**

### **FDA Statement**

This product might be suitable for use in indirect food contact applications. Please see the applicable Regulatory Data Sheet for more information relating to FDA compliance.

## **Storage and Shelf Life**

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

## **Available Sizes**

<b>Attribute Name</b>	<b>Width</b>	<b>Value</b>
Core Size (ID)		76.2 mm
Maximum Length	1 in to 3 in	329 m
Maximum Length	1/2 in to 63/64 in	164 m
Maximum Length	3 in to 48 in	329 m
Maximum Length	48 in to 54 in	329 m
Normal Slitting Tolerance		± 0.8 mm
Note		Subject to Minimum Order Requirements

## **Automotive Disclaimer**

### **Select Automotive Applications:**

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

## **Information**

Precautionary Information: Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information, please contact your local 3M Office. You can click or scan QR code to see contact detail or visit [www.3M.com](http://www.3M.com) Important Information: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law. Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

## **ISO Statement**

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Centre  
Cain Rd, Binfield, Bracknell RG12 8HT, United Kingdom  
3m.co.uk/iatd

3M is a trademark of 3M Company.  
©3M 2024 (9/24)