



Technical Data Sheet

3M™ Scotch-Weld™ Acrylic Adhesive DP8410NS Green

Product Description

3M™ Scotch-Weld™ Acrylic Adhesives are high performance, two-part acrylic adhesives that offer excellent shear, peel, and impact performance. These toughened products provide improved adhesion to many plastics and metals, including those with slightly oily surfaces. These durable products feature a fast rate of strength build, providing structural strength in minutes.

Review UL File QQQW2. MH17478 and Sign Components Manual (SAM) File E464624 for certification of these adhesive systems in electrical equipment.

DP8410NS Green has been tested for surface flammability, smoke, toxic gas generation, and caloric content per ASTM E162, ASTM E662, ASTM E1354, Bombardier SMP 800-C, and Boeing BSS 7239 test methods. DP8405NS Green and DP8425NS Green should yield similar results.

Product Features

- Toughened
- Variety of open times available
- Excellent shear strength
- Increased cure speed with applied heat
- Outstanding peel and impact strength
- Contain glass beads (0.010" diameter) to control bond line thickness
- 10:1 mix ratio control bond line thickness

Note: Unless otherwise indicated, all properties measured at 72°F (22°C).

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Environmental aging tests have shown that these adhesives may accelerate the corrosion of certain bare metals (such as cold rolled steel, copper, brass, and bronze), leading to low bond strength values and early bond failure. These adhesives also have relatively low adhesion to low surface energy plastics (such as polypropylene, polyethylene, TPO, and PTFE). Applications involving any of these materials should be carefully evaluated by the end user for suitability.

Typical Uncured Physical Properties

Attribute Name	Value
Mix Ratio by Volume (B:A)	10:1
Mix Ratio by Weight (B:A)	9.5:1

Attribute Name	Temperature	Value
Base Color		Brown
Accelerator Color		Blue
Base Density		1.02 g/cm ³ ¹
Accelerator Density		1.07 g/cm ³ ¹
Base Viscosity	23 °C	65,000 cP ²
Accelerator Viscosity	23 °C	30,000 cP ²

¹ Density measured using pycnometer.

² Viscosity measured using cone-and-plate viscometer; reported viscosity at 3.8 sec⁻¹ shear rate.

Typical Mixed Physical Properties

Attribute Name	Temperature	Value
Density (mixed)		1.03 g/cm ³
Viscosity		60,000 cP
Open Time		8 min ¹
Worklife	23 °C	10 – 12 min ²
Set Time (min)	23 °C	26 – 30 min ³
Time to Structural Strength		34 – 38 min ⁴
Time to Full Cure	23 °C	24 h ⁵

¹ Max time allowed after applying adhesive to a substrate before bond must be closed and fixed. Cure times approximate and depend on adhesive temperature. Hotmelts: The approx. bonding range of a 3.2 mm (1/8 in) bead of molten adhesive on a non-metallic surface.

² Maximum time that adhesive can remain in a static mixing nozzle and still be expelled without undue force on the applicator. Cure times are approximate and depend on adhesive temperature.

³ Minimum time required to achieve 0.3 MPa (50 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

⁴ Minimum time required to achieve 6.9 MPa (1,000 psi) of overlap shear strength. Cure times are approximate and depend on adhesive temperature.

⁵ The cure time is defined as that time required for the adhesive to achieve a minimum of 80% of the ultimate strength as measured by aluminum-aluminum OLS.

Typical Physical Properties

Attribute Name	Value
Cured Color	Green
Mixed Color	Green

Typical Cured Characteristics

Attribute Name	Test Method	Temperature	Value
Modulus	ASTM D638, ISO 527	23 °C	1300 MPa ¹
Tensile Strain at Break			6 % ²

¹ 3 mm (1/8") thick Type I test specimens; samples pulled at 5 mm/min (0.2 in/min). 2 week dwell at 22 °C (72 °F)

² 3 mm (1/8 in) thick Type I test specimens; samples pulled at 5 mm/min (0.2 in/min)

Typical Performance Characteristics

Overlap Shear Strength

Temperature: 23 °C

Dwell Time: 24 h

Test Method: ASTM D1002, ISO 4587

Test Condition	Substrate	Surface Prep	Value
23 °C	ABS	Light Abrasion and Solvent Clean	7.6 MPa ¹
23 °C	Acrylic (PMMA)	Light Abrasion and Solvent Clean	9 MPa ¹
23 °C	Epoxy Resin (fiber-reinforced)	Light Abrasion and Solvent Clean	29 MPa ¹
23 °C	Polycarbonate (PC)	Light Abrasion and Solvent Clean	9 MPa ¹
23 °C	Polyester (PET)	Light Abrasion and Solvent Clean	6.9 MPa ¹

Test Condition	Substrate	Surface Prep	Value
23 °C	Polystyrene (HIPS)	Light Abrasion and Solvent Clean	3.8 MPa ¹
23 °C	Polyvinyl chloride (PVC)	Light Abrasion and Solvent Clean	11.7 MPa ¹
23 °C	Stainless Steel	Light Abrasion and Solvent Clean	24.1 MPa ¹
23 °C	Aluminum	Etched	26.9 MPa ¹
-40 °C (-40 °F)	Aluminum	Light Abrasion and Solvent Clean	24.8 MPa ¹
82 °C (180 °F)	Aluminum	Light Abrasion and Solvent Clean	8.6 MPa ¹

¹ 25 mm (1") wide, 12.7 mm (1/2") overlap samples, 25 mm (1") x 102 mm (4") substrates, bondline thickness: 0.13-0.20 mm (5-8 mil)
Separation rate 2.5 mm/min (0.1 in/min) metal, 51 mm/min (2 in/min) plastic, 510 mm/min (20 in/min) rubber.
Substrate thickness: steel 1.5 mm (60 mil), other metal 1.3-1.6 mm (50-64 mil), rubber and plastic 3.2 mm (125 mil)
Cohesive Failure (CF), Adhesive Failure (AF), Mixed Failure (MF), Substrate Failure (SF)

Substrate: Aluminum
Surface Prep: Etched
Temperature: 23 °C
Test Condition: 23 °C

Attribute Name	Test Method	Value
Bell Peel	ASTM D3167	105 N/cm ¹

¹ Floating roller peel; adhesives allowed to cure for 24 hours @RT; 25 mm (1 in) wide samples;
Samples pulled at 15 mm/min (6 in/min)
Cohesive (CF), Adhesive (AF) and Substrate (SF) Failure

Attribute Name	Value
Tensile Strength	15.2 MPa ¹

¹ 3 mm (1/8 in) thick Type I test specimens; samples pulled at 5 mm/min (0.2 in/min)

Attribute Name	Value
Additional Test notes	Environmental aging tests have shown that these adhesives may accelerate the corrosion of certain metals (such as bare steel, copper, brass, and bronze), leading to low bond strength values and early bond failure. These adhesives also have relatively low adhesion to low surface energy plastics (such as polypropylene, polyethylene, TPO, and PTFE). Applications involving any of these materials should be carefully evaluated by the end user for suitability.

Typical Environmental Performance

Overlap Shear Strength

Substrate: Aluminum

Dwell Time: 1,000 h

Test Method: ASTM D1002, ISO 4587

Temperature	Environmental Condition	Value
-40 °C		95 % ¹
149 °C		100 % ¹
49 °C	80%RH	85 % ¹
66 °C	80%RH	60 % ¹
85 °C	85%RH	40 % ¹
23 °C	100%RH	90 % ¹
32 °C	100%RH	85 % ¹
49 °C	100%RH	50 % ¹
23 °C	Salt water (5 wt% in water)	95 % ¹
23 °C	Antifreeze (50 wt% in water)	100 % ¹
23 °C	Oil 10W30	100 % ¹
23 °C	Bleach (10 wt% in water)	95 % ¹
23 °C	Isopropyl Alcohol (IPA)	90 % ¹
23 °C	Diesel Fuel	100 % ¹
23 °C	Gasoline	75 % ¹

¹ Performance % to control sample @RT, tested after 24hr dwell @RT.

Cured adhesives can handle short contact to most chemicals or env. cond. Avoid long exposure to:

Temp >100 °F + water

Ketone-type solvents (acetone, MEK)

Gasoline and similar liquids

Overlap Shear Strength

Substrate: Polyvinyl chloride (PVC)

Dwell Time: 1,000 h

Test Method: ASTM D1002, ISO 4587

Temperature	Environmental Condition	Value
-40 °C		100 % ¹
49 °C		95 % ¹
66 °C		100 % ¹
85 °C	85%RH	100 % ¹
23 °C	100%RH	100 % ¹
23 °C	Hydrochloric acid (16 wt% in water)	95 % ¹
23 °C	Salt water (5 wt% in water)	100 % ¹
23 °C	Sodium hydroxide (10 wt% in water)	95 % ¹

¹ Performance % to control sample @RT, tested after 24hr dwell @RT.

Cured adhesives can handle short contact to most chemicals or env. cond. Avoid long exposure to:

Temp >100 °F + water

Ketone-type solvents (acetone, MEK)

Gasoline and similar liquids

Dispense Properties

Attribute Name	Value
200-400ml Cartridge Nozzle	Helical (Orange), 18 element, 222mm, 13.0ml, #7100304367
200-400ml Cartridge Low Waste Nozzle	Helical (Green), 24 element, 137mm, 6.3ml, #7100066351
45-50ml Cartridge Nozzle	Quadro (Orange), 16 element, 90mm, 1.7ml, #7100202930

Handling/Application Information

Directions for Use

1. To obtain the highest strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. The amount of surface preparation depends on the required bond strength and environmental aging resistance desired by user. For suggested surface preparations on common substrates, see the section on surface preparation.

Mixing For Duo-Pak Cartridges

Store cartridges with cap end up to allow any air bubbles to rise towards the tip. To use, simply insert the cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Then remove the cap and expel a small amount of adhesive to ensure material flows freely from both sides of cartridge. For automatic mixing, attach an EPX mixing nozzle to the cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after obtaining a uniform color.

For Bulk Containers

Mix thoroughly by weight or volume in the proportion specified on the product label or in the typical uncured properties section. Mix approximately 15 seconds after obtaining a uniform color.

3. Apply adhesive and join surfaces within the open time listed for the specific product. Larger quantities and/or higher temperatures will reduce this working time.

4. Allow adhesive to cure at 60°F (16°C) or above until completely firm. Applying heat up to 150°F (66°C) will increase cure speed.

5. Keep parts from moving during cure. Apply contact pressure or fixture in place if necessary. Optimum bond line thickness ranges from 0.005 to 0.020 inch; shear strength will be maximized with thinner bond lines, while peel strength reaches a maximum with thicker bond lines.

6. Excess uncured adhesive can be cleaned up with ketone-type solvents.*

*Note: When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

Surface Preparation

3M™ Scotch-Weld™ Acrylic Adhesives are designed to be used on painted or coated metals, most plastics, and some bare metals. The following cleaning methods are suggested for common surfaces:

Painted/coated metals:

1. Wipe surface free of dust and dirt with clean cloth and pure isopropyl alcohol.
2. Sandblast or lightly abrade using clean fine grit abrasives. Do not completely remove the paint layer or coating down to bare steel.
3. Wipe again with clean cloth and pure isopropyl alcohol to remove loose particles.

Aluminum/stainless steel:

1. Wipe surface free of dust and dirt with clean cloth and pure acetone.
2. Sandblast or lightly abrade using clean fine grit abrasives.
3. Wipe again with clean cloth and pure acetone to remove loose particles.

Plastics:

1. Wipe surface free of dust and dirt with clean cloth and pure isopropyl alcohol.
2. Lightly abrade using fine grit abrasives.
3. Wipe again with clean cloth and pure isopropyl alcohol to remove loose particles.

Note:When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

Industry Specifications

[NFPA 130 test report for details \(ASTM E1354\)](#)

[NFPA 130 test report for details \(ASTM E162, ASTM E662, SMP 800-C, BSS 7239\)](#)

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. Refrigeration at 4°C (40°F) will help extend shelf life. Do not freeze. Allow product to reach room temperature prior to use. For best performance, use this product within 24 months from date of manufacture.

Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Precautionary Information: Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information, please contact your local 3M Office. You can click or scan QR code to see contact detail or visit www.3M.com Important Information: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law. Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Centre
Cain Rd, Binfield, Bracknell RG12 8HT, United Kingdom
3m.co.uk/iatd

3M, Scotch-Weld and EPX are trademarks of 3M Company.
© 3M 2016. All rights reserved.