


3M Science.
Applied to Life.™

**Cut through the
complexity of today's
vehicle repairs.**



Choosing high-quality
abrasives can help maximise
labour hours from the start.



Our featured abrasive lineup

Premium abrasives that can help you get to the finish line faster.

3M™ Cubitron™ II Abrasives

features 3M™
Precision-Shaped Grain,
triangular-shaped grains
that cut faster and
last longer than other
traditional ceramic
abrasives.


Cut Rate



Disc Life




Dust Extraction



3M Precision-Shaped Grain

3M pioneered the first precision-shaped grain using 3M microreplication technology to form consistent sharp peaks that easily "slice" through metal—cutting cooler, faster, and lasting longer than conventional abrasive grain.




Traditional ceramic abrasive

Traditional ceramic abrasive grain tends to "plow" through metal, causing heat to build up in the workpiece and abrasive, resulting in a slower cut and shorter abrasive life compared to our latest precision-shaped grain.

		40+	80+	120+	150+	180+	220+	240+	320+	400+	500+	600+	800+	1000+
	3M™ Cubitron™ II Hookit™ Clean Sanding Abrasive Discs 737U													
		*25 Discs / Carton												
	75 mm	-	31361	31362	31363	31364	31461	31462	31463	31464	31465	31466	31467	31468
	125 mm	-	31366	31367	31368	31369	31471	31472	31473	31474	31475	31476	31477	31478
	150 mm	31370*	51369	51370	51421	51422	51423	51424	51426	51428	31485	31486	31487	31491
	203 mm	31375	31376	-	-	-	-	-	-	-	-	-	-	-
	3M™ Cubitron™ II Net Abrasive Discs													
	75 mm	-	31679	31680	31681	31682	31683	31684	31685	-	-	-	-	-
	150 mm	-	31650	31651	31652	31653	31654	31655	31656	-	-	-	-	-
	203 mm	-	31641	31642	31643	31644	31645	31646	31647	-	-	-	-	-
	3M™ Cubitron™ II Hookit™ Clean Sanding Abrasive Sheet Rolls 737U													
		*115 mm x 8 m												
	70 mm x 12 m	-	51430	51431	51432	51433	51434	51435	51436	51437	34451	34452	34453	34454
	80 mm x 12 m	-	35501	35502	35503	35504	35505	31488	31489	31490	-	-	-	-
	115 mm x 12 m	34460*	34462	34464	34465	34466	34467	34468	34469	34470	34471	34472	34473	34474
	3M™ Cubitron™ II Net Sheet Rolls													
	70 mm x 10 m	-	34561	34562	34563	34564	34565	34566	34567	-	-	-	-	-
	115 mm x 10 m	-	34572	34573	34574	34575	34576	34577	34578	-	-	-	-	-

Recommended grades for use



Abrasive Discs



Abrasive Sheet Rolls

40+, 80+	Coarse sanding	Coarse sanding
120+, 150+, 180+	Paint removal or strip Preparation for dent repair	Filler shaping or sanding
220+, 240+	Filler final sanding Featheredging	Filler initial sanding and shaping
320+, 400+	Surface preparation for primer E-Coat sanding	Block sanding primer
500+, 600+, 800+	Primer final sanding Surface preparation for paint	Primer final sanding Surface preparation for paint
1000+	Blend panel preparation Coarse defect removal	Pre-paint defect removal

Our featured abrasive lineup

High-quality abrasives for every stage of the repair.

		P40	P80	P120	P150	P180	P220	P240	P320	P400	P500	P600	P800
	3M™ Hookit™ Blue Abrasive Discs (Multi-Hole)												
	150 mm	-	51371	51373	51374	51375	51376	51377	51379	51381	51382	51383	-
	3M™ Blue Net Abrasive Discs												
	150 mm	-	36420	36421	36422	36423	36424	36425	36426	-	-	-	-
	3M™ Blue Net Abrasive Sheet Roll												
	70 mm x 10 m	-	36462	36463	36464	36465	36466	36467	36468	-	-	-	-
	115 mm x 10 m	-	36470	36471	36472	36473	36474	36475	36476	-	-	-	-



3M™
Blue Abrasives
feature an
engineered ceramic
mineral blend for
**best-in-class
performance**
at a mid-tier price point.

Cut Rate**Disc Life****Dust Extraction**

Discs available in multi-hole pattern for excellent dust extraction or in no-hole format



Anti-loading coating prevents dust and debris from clogging the cutting surface



Hook-and-loop feature makes disc attachment, removal, and re-attachment clean and easy

		P400	P600	P800	P1000	P1200	P1500	P2000
	3M™ Flexible Foam Abrasive Discs							
	77 mm	-	-	33550	33551	33552	33553	33554
	125 mm	-	-	33545	33546	33547	33548	33549
	150 mm	33538	33539	33540	33541	33542	33543	33544



Flexible foam backed abrasive which conforms to irregular surfaces



Can be used wet or dry and by hand or machine for blending applications



Dust and water control to ensure a clean sanding environment

3M™
**Flexible Foam
Abrasives**

Cut Rate**Disc Life****Dust Extraction**

The supporting line

Additional products and tools to help power up your day-to-day productivity.

Body Repair and Paint Preparation

Product	Part No.	Grade	Size
Cut and Grind Abrasives			
3M™ Cubitron™ II File Belts 786F	33437	36+	10 mm x 330 mm
	33439	60+	
	33440	80+	
	33443	36+	12.7 mm x 457.2 mm
	33445	60+	
	33446	80+	
	33449	36+	20 mm x 520 mm
	33451	60+	
	33452	80+	
3M™ Cubitron™ II Roloc™ Fibre Disc	33377	36+	50 mm
	33379	60+	
	33380	80+	75 mm
	33389	36+	
	33391	60+	
3M™ Cubitron™ II Abrasive Fibre Discs	33392	80+	115 mm x 22 mm
	33407	36+	
	33409	60+	180 mm x 22 mm
	33410	80+	
	33431	36+	75 mm x 1 mm x 9.53 mm
3M™ Cubitron™ 3 Cut-Off Wheels	33457	-	
	33458	-	75 mm x 1 mm x 9.53 mm
	33459	-	
	33463	-	100 mm x 1 mm x 9.53 mm

Product	Part No.	Size
Body Repair Tools		
3M™ File Belt Sander	33575	457 mm
3M™ Mini File Belt Sander	33573	457 mm
3M™ Pistol Grip Disc Sander	33577	-
3M™ Cut-Off Wheel Tools	33579	75 mm
	33581	100 mm

Product	Part No.	Size	Orbit
3M™ Clean Sanding System (Dust Extraction)			
3M™ Precision Random Orbital Sander	38505	75 mm	5 mm
	33632	150 mm	2.5 mm
	33633	150 mm	5 mm
	33634	150 mm	8 mm
3M™ Electric Random Orbital Sander	33794	150 mm	5 mm
3M™ Dust Extractor, 45L, L Class	33761	-	-
3M™ Dust Extractor, 30L, L Class	33756	-	-
3M™ Dust Extractor, 45L, M Class	33762	-	-
3M™ Dust Extractor, 30L, M Class	33787	-	-

Product	Part No.	Size
Sanding Accessories		
3M™ Dry Guide Coat	09560	50 g
3M™ Hookit™ Dust Extraction Flexible Sanding Block	35825	133 mm x 67 mm
	35826	178 mm x 67 mm
	35828	406 mm x 67 mm

Paint Finishing

Product	Part No.	Grade	Size
Fine Abrasive Discs			
3M™ Hookit™ Purple Finishing Film Abrasive Disc	51156	P600	150 mm
	51155	P800	
	51157	P1000	
	51158	P1200	
	51154	P1500	
	51304	P2000	75 mm
	51263	P600	
	51264	P800	
	51265	P1000	
	51266	P1200	
3M™ Trizact™ Hookit™ Foam Abrasive Disc	51267	P1500	150 mm
	02085	P3000	
	30662	P5000	
	30806	P8000	75 mm
	02087	P3000	
	30362	P5000	
	30804	P8000	

For more information, please visit us at
go.3m.com/abrasives-collision-repair



3M United Kingdom PLC
Automotive Aftermarket
3M Centre
Cain Road
Bracknell, RG12 8HT
+44 (0)161 237 6391
aadukenquiries@mmm.com

3M Ireland Limited
Automotive Aftermarket
The Iveagh Building
The Park
Carrickmines, Dublin 18
+353 12160301
aadukenquiries@mmm.com

For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3m.co.uk/aad-info

3M and Cubitron are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle.
© 3M 2024. All rights reserved.